



NOTES

- 1 - 3X 6-32 UNC PRESSURE PLATE TERMINAL SCREWS
 2 FURNISHED UNASSEMBLED
 3 SWITCH WILL OPERATE AND RELEASE WITHIN
 THIS TRAVEL




ROLLER LEVER MAY BE POSITIVELY
LOCKED AT INTERVALS OF APPROXIMATELY
0.2° WITHIN A RANGE OF 225°
(1238 POSITIONS)



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE38 OZ MAX	CONTACT ARRANGEMENT
TOTAL TRAVEL $\triangle 3$.370 MIN	S P D T
DIFFERENTIAL TRAVEL065 NOM	L156
	11A 1/3HP 125, <u>250</u> , 277 VAC
	1/2A 125 VDC, 1/4A 250 VDC
	4A 125 VAC "L"
	 

THIRD ANGLE PROJECTION



SCALE	FULL
-------	------

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) ±.015

THREE PLACE (.000) $\pm .005$

NAME	DATE	PERIOD	PAGE
ANGLES			†

ANGLES	

WEIGHT

ANSI Y14.5M-1982 APPLIES