

Customer Information Sheet

DRAWING No.: M80-5C1XXXXB1 SHEET 2 OF 2

IF IN DOUBT - ASK


(C)

NOT TO SCALE




THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm


SPECIFICATIONS:
MATERIAL:
MOULDING = GLASS-FILLED PPS, UL94V-0, BLACK
CONTACT = BRASS
PANEL MOUNT & NUT = STAINLESS STEEL
BACKSHELL = ALUMINIUM ALLOY
FINISH:
CONTACT = 0.75µ GOLD ALL OVER
BACKSHELL = NICKEL
ELECTRICAL:
RF ATTENUATION = 10 kHz TO 400MHz @ >30 dBs
IN GENERAL ACCORDANCE WITH MIL STD 1377 (1971)
CURRENT RATING AT 25°C = 3.0A MAX
CURRENT RATING AT 85°C = 2.2A MAX
WORKING VOLTAGE = 120V AC/DC
VOLTAGE PROOF = 360V AC/DC
CONTACT RESISTANCE = 25 mΩ MAX
INSULATION RESISTANCE = 100 MΩ MIN
MECHANICAL:
DURABILITY = 500 OPERATIONS
ENVIRONMENTAL:
TEMPERATURE RANGE = -55°C TO +121°C
PACKING:
SEE NOTES
FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C005XX (LATEST ISSUE) AND C042XX
(LATEST ISSUE)



- NOTES:**
- SUPPLIED AS A KIT OF PARTS, CONNECTORS SHOWN ASSEMBLED FOR INFORMATION PURPOSES ONLY.
 - CONNECTORS WITH JACKSCREWS ASSEMBLED, SLOTTED NUTS AND CONTACTS WILL BE SUPPLIED LOOSE IN A BAG, BACKSHELLS WILL BE INDIVIDUALLY BAGGED. KITS WILL BE BULK PACKED INTO BOXES
 - FOR EXTRA CONTACTS, USE PART No: M80-1950005 FOR M80-5C1XX05B1
 - FOR M80-5C1XX05B1 RECOMMENDED WIRE TYPE = BS 3G 210 TYPE A, PTFE INSULATED 24-28 AWG. MAX INSULATION DIAMETER = Ø1.10mm, STRIP WIRE BY 2.00mm.
 - RECOMMENDED HAND CRIMP TOOL FOR ALL CONTACTS = M22520/2-01 WITH POSITIONER Z80-193
 - CONTACT INSERTION AND EXTRACTION TOOL = Z80-280.
 - INSTRUCTION SHEETS ARE AVAILABLE.




RECOMMENDED PCB LAYOUT



ORDER CODE: **M80-5C1XXXXB1**
TOTAL No. OF CONTACTS
06, 10, 14, 20, 26
FINISH CODE
05 - ALL OVER GOLD

ASSEMBLED CONNECTOR
SHOWN FOR ILLUSTRATION
PURPOSES ONLY



EXAMPLE ORDER CODE: CONNECTOR WITH 20 SMALL BORE
CONTACTS, ALL OVER GOLD CONTACT.
M80-5C12005B1

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE: DATAMATE J-TEK DIL
MALE CRIMP (SMALL BORE) ASSY
WITH METAL BACKSHELL

DRAWING NUMBER: **M80-5C1XXXXB1**

SB	4	14.03.11	11172
NAME	ISS.	DATE	C/NOTE
APPROVED:	S.BENNETT		
CHECKED:	S.FLOWER		
DRAWN:	S.FLOWER		
CUSTOMER REF.:			
ASSEMBLY DRG:			

SHT
2
OF
2