


C4 - SERIES

1.5" DIAMETER 0.5 AMP @ 28 VDC

SPECIFICATIONS AND ORDERING INFORMATION

The C4 Series provides a versatile, fully enclosed design, that helps keep dirt and moisture out of the contact area while locking in life time lubricants. IP67 Rating Available.



SPECIFICATIONS

ELECTRICAL

Current and Voltage Rating: Make and break resistive load 0.5 amp @ 28 VDC; 0.3 amp @ 125 VAC.

Current Carrying Capacity: 15 amps.

Dielectric Strength: 1,000 VAC between current carrying parts and ground.

Contact Resistance: Average initial 3 milliohms.

Insulation Resistance: In excess of 10,000 megohms.

Hardware: Mounting nut and lockwasher are shipped assembled.

MECHANICAL

Materials and Finishes: All parts utilize non-corrosive materials as standard.

Terminals and Contacts: Brass with silver plate as standard.

Insulation: Diallyl phthalate.

Index: Dual-ball, hill and valley.

Index Life: 25,000 cycles minimum.

Index Torque: Switches have lowest practical torque consistent with crisp detenting and smooth, reliable operation.

Index Angles: 30° standard, 36°, 45°, 60°, and 90° available.

Index Stops: Fixed standard, adjustable or continuous available.

Stop Strength: 15 in. lbs. minimum.

STANDARD PART NUMBER

SOLDER LUG - ADJUSTABLE STOPS

SWITCHES - 30° INDEXING - STOPS SET @ 2 POS.



POLES	ACTIVE POSITIONS	POLES/ DECK	NO. OF DECKS	SHORTING	NON-SHORTING	FIG. *
01	02-12	1	1	C4D0112S - A	C4D0112N - A	CA
02	02-06	2	1	C4D0206S - A	C4D0206N - A	CH
02	02-12	1	2	C4D0212S - A	C4D0212N - A	CA
03	02-12	1	3	C4D0312S - A	C4D0312N - A	CA
03	02-04	3	1	C4D0304S - A	C4D0304N - A	CK
04	02-12	1	4	C4D0412S - A	C4D0412N - A	CA
04	02-06	2	2	C4D0406S - A	C4D0406N - A	CH
05	02-12	1	5	C4D0512S - A	C4D0512N - A	CA

POLES	ACTIVE POSITIONS	POLES/ DECK	NO. OF DECKS	SHORTING	NON-SHORTING	FIG. *
06	02-06	2	3	C4D0606S - A	C4D0606N - A	CH
06	02-04	3	2	C4D0604S - A	C4D0604N - A	CK
06	02-12	1	6	C4D0612S - A	C4D0612N - A	CA
08	02-06	2	4	C4D0806S - A	C4D0806N - A	CH
09	02-04	3	3	C4D0904S - A	C4D0904N - A	CK
10	02-06	2	5	C4D1006S - A	C4D1006N - A	CH
12	02-04	3	4	C4D1204S - A	C4D1204N - A	CK
15	02-04	3	5	C4D1504S - A	C4D1504N - A	CK


* FIGURES ARE SHOWN ON PAGE 55.

DIMENSIONS


C4D STANDARD CONSTRUCTION



- NOTE:
- ONE DECK EQUALS TWO WAFERS.
 - ADD .284\"



Q



ELECTROSWITCH • ELECTRONIC PRODUCTS
UNIT OF ELECTRO SWITCH CORP.

2010 Yonkers Road
Raleigh, NC 27604

Telephone: (888) ROTARYS or (919) 833-0707
Fax: (800) 909-9171 or (919) 833-8016

How to Order Additional Options:

2 DIGIT SERIES	INSULATION TYPE	TOTAL POLES	ACTIVE POSITIONS	CONTACT TYPE
C4	D - DIALLYL	01 - MIN.	12 - MAX @ 30° 10 - MAX @ 36° 08 - MAX @ 45° 06 - MAX @ 60° 04 - MAX @ 90°	S - SHORTING N - NON SHORTING

TERMINAL TYPE	INDEX ANGLE	STOP TYPE	SHAFT/BUSHING	SHAFT FLAT
L - SOLDER LUG	30°	F - FIXED	D	J
P - FRONT P.C. (NOT IN 45°)	36°	A - A		
R - REAR P.C. (30° & 36° ONLY)	45° 60°	(30°, 60°, 90° ONLY)	SEE CHART "A"	SEE CHART "B"
Q - QUICK CONNECT	90°	C - CONT.		

CUSTOMERS SPECIFIED ORDER NUMBER FOR STANDARD OPTIONS

C4D

(SPECIFY)

(SPECIFY)

(SPECIFY)

(SPECIFY)

(SPECIFY)

(SPECIFY)



(SPECIFY)

(SPECIFY)


(SPECIFY)

ADDITIONAL OPTIONS


PRINTED CIRCUIT BOARD HOLE PATTERNS



SHAFT, BUSHING, AND FLAT OPTIONS



PRINTED CIRCUIT BOARD TERMINAL OPTIONS



CUSTOM SWITCHES ARE AVAILABLE. CONTACT THE FACTORY WITH YOUR COMPLETE SPECIFICATIONS.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Electroswitch:

[C4D0204S-60](#) [C4D0406N-A](#) [C4D0103N-60](#) [C4D0412N-A](#) [C4D1204N-A](#) [C4D0312S-A](#) [C4D0806N-A](#) [C4D0606N-A](#)
[C4D0304N-A](#) [C4D0206N-A](#) [C4D2704N](#) [C4D0312N-A](#) [C4D0206S-A](#) [C4D0604N-A](#) [C4D0212N-A](#) [C4D0904N-A](#)
[C4D0112N-A](#) [C4D2005S](#) [C4D0210N-9585](#) [C4D0112S-A](#) [C4D1504S-A](#) [C4D0103N-90](#) [C4D0402N-60W](#) [C4D0806S-](#)
[A](#) [C4D0116N22C](#) [C4D0412S-A](#) [C4D0604S-A](#) [C4D0104S-Q6010U](#) [C4D0212S-A](#) [C4D0406S-A](#) [C4D0216N-4326](#)
[C4D0304S-A](#) [C4D0103N-9912](#) [C4D0115N-4471](#)