

301A511-51/164-0

✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Transition
- Family Name = 301A5
- Transition Type = Slimline T
- 2 Branches/Legs
- Military Application

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings: • Slimline Transition, T (PDF, English)	Additional Information: • Product Line Information
Catalog Pages/Data Sheets: • Wire and Cable, Harnessing and Protection Products (PDF, English)	Related Products: • Tooling
Product Specifications: • None Available	
Application Specifications: • None Available	
Instruction Sheets: • None Available	
CAD Files: • None Available	
List all Documents	

Product Type Features: • Product Type = Transition • Size = 11 • Material = Polymer Blend Flexible Elastomeric (EPB) • Comment = Use only with -51 molded parts and NT-FR tubing. Body Related Features: • Transition Type = Slimline T • Number of Branches/Legs = 2 • 1st Branch/Leg Range (mm [in]) = 6.60 – 13.20 [0.260 – 0.520] • 2nd Branch/Leg Range (mm [in]) = 6.60 – 13.20 [0.260 – 0.520] Contact Related Features: • Family Name = 301A5 • Approved Standards = SC-X-15112 Housing Related Features: • Material Systems Code = 20 • Adhesive Pre-Coating = With • Adhesive Description = High Melt Point Pre-Coat Adhesive • Max. Inside Diameter of Part (mm [in]) = 6.60 – 19.80 [0.260 – 0.780]	Configuration Related Features: • Material Code = 51 • Adhesive Code = 164 Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: • Operating Temperature (°C) = -55 – +105 Operation/Application: • Application = Military Other: • Brand = Raychem
---	--