

Description

- Fast Acting Surface Mount Fuse
- Solid matrix design encapsulated in a 94V-O thermoplastic body
- Copper Leads with a tin/lead finish
- Fuses marked with catalog symbol, ampere rating, and voltage rating

ELECTRICAL CHARACTERISTICS	
% of Amp Rating	Opening Time
100%	4 Hours Minimum
200%	60 Seconds Maximum
250%	5 Seconds Maximum

Agency Information

- UL Recognition Guide and File numbers: JDYX2 & E19180 (0-10A, 12.5A AC only)
- CSA Certification Record No: Class #1422-01, File #53787

Environmental Data


- Resistance to Solder Heat: MIL-STD-202F, Method B
- Vibration: MIL-STD-202F, Method 204 Test Condition A

Soldering Method


- Wave Immersion: 260°C, 10 sec max
- IR Reflow: 260°C, 30 sec max

Ordering


- Specify product code and packaging code



Dimensional Data



Trace Geometry



Electrical Characteristics

Product Code	Rated Voltage		Interrupting Rating ¹		Pre-arcing I ² T (A ² sec)		Typical Total Clearing ³ I ² T (A ² sec)		Typical Voltage Drop ² Volts at 100% Rated Current
	AC (Max.)	DC (Max.)	AC	DC	AC	DC	AC	DC	
SFT-63mA	125V	125V	50A	300A					
SFT-125mA	125V	125V	50A	300A					
SFT-250mA	125V	125V	50A	300A	7.49 x 10 ⁻⁵	5.1 x 10 ⁻⁶	2.0 x 10 ⁻⁴	6.29 x 10 ⁻⁶	.8
SFT-375mA	125V	125V	50A	300A	3.17 x 10 ⁻⁴	2.18 x 10 ⁻⁵	4.18 x 10 ⁻⁴	2.67 x 10 ⁻⁵	.75
SFT-500mA	125V	125V	50A	300A	4.46 x 10 ⁻⁴	3.8 x 10 ⁻⁵	5.74 x 10 ⁻⁴	4.63 x 10 ⁻⁵	.66
SFT-750mA	125V	125V	50A	300A	1.72 x 10 ⁻³	2.27 x 10 ⁻⁴	2.59 x 10 ⁻³	2.77 x 10 ⁻⁴	.525
SFT-1	125V	125V	50A	300A	.0099	.0069	.0114	.0076	.12
SFT-1.5	125V	125V	50A	300A	.0302	.0204	.0345	.0246	.20
SFT-2	125V	125V	50A	300A	.0784	.0651	.0891	.0811	.170
SFT-2.5	125V	125V	50A	300A	.1775	.1390	.2383	.1574	.145
SFT-3	125V	125V	50A	300A	.3355	.2419	.4359	.2664	.130
SFT-3.5	125V	125V	50A	300A	.4980	.3812	.6355	.4696	.155
SFT-4	125V	125V	50A	300A	.8855	.6785	1.0740	.7829	.135
SFT-5	125V	125V	50A	300A	1.7264	1.2912	2.3779	1.3556	.125
SFT-7.0A	60V	90V	50A	300A	1.64	.518	1.97	.573	.114
SFT-10.0A	60V	90V	50A	300A	3.79	1.06	3.92	1.67	.130
SFT-12.5A	48V	60V†	50A	300A	15	4.04	20	4.28	.090

† NOTE: SFT 12.5A is UL recognized on AC Only.


1. Interrupting ratings were measured at 100% power factor on AC, and a time constant less than 1ms on DC.

2. Voltage drop was measured at 25°C ± 3°C ambient temperature at rated current with device mounted on a circuit trace.

3. I²t measured at 50 amp, 125 VAC, .95PF, random closing angle; 300 amps, 125 VDC, TC<1ms.

4. Device designed to carry 100% of rated current for four hours minimum. An operating current of 80% or less of rated current is recommended, with further derating required at elevated ambient temperatures.

Time-Current Characteristic Curves—Average Melt
(Full Size Curves Available)



PACKAGING CODE	
Packaging Code	Description
Blank	10 pieces
TR	500 pieces of fuses on 16mm tape-and-reel on a 7 inch reel per EIA Standard 481

North America

Cooper Electronic Technologies
3601 Quantum Boulevard
Boynton Beach, FL 33426-8638
Tel: 1-561-752-5000
Fax: 1-561-742-0134
Toll Free: 1-888-414-2645

Cooper Bussmann
P.O. Box 14460
St. Louis, MO 63178-4460
Tel: 1-636-394-2877
Fax: 1-800-544-2570

Europe

Cooper Electronic Technologies
Cooper (UK) Limited
Burton-on-the-Wolds
Leicestershire • LE12 5TH UK
Tel: +44 (0) 1509 882 737
Fax: +44 (0) 1509 882 786

Asia Pacific

Cooper Electronic Technologies
1 Jalan Kilang Timor
#06-01 Pacific Tech Centre
Singapore 159303
Tel: +65 278 6151
Fax: +65 270 4160

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[TR/SFT-1](#) [TR/SFT-3](#) [TR/SFT-4_](#) [TR1/SFT-1.5](#) [TR/SFT-5](#) [SFT-3](#) [SFT-7](#) [SFT125MA](#) [SFT-10](#) [TR/SFT-2_](#) [SFT-5](#)
[SFT-500MA](#) [TR/SFT-375MA](#)