


9 73 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

K	ADDED .712 DIM. FLANGE	10/9/78	mm
L	REV PER OH14-0192-05	1-06	PY

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	A	REV. 1 REDRAWN	4-2-73	RE Fm
	B	DELETED 872 & ADDED .938	4-4-73	RE Fm
	C	ADDED TIN & GOLD PLATED FLANGES TO 1 & 2	7-13-73	RE Fm
B-2	D	ADDED NOTE - 2	1/23/74	M. A.
	E	REV. - 2	2/6/74	RE Fm
	F	ADDED .312 DIA., .38, .020, .954, 1.687, ECN 8041, D.S.	5-19-75	M. S.
	G	REMOVED - 2	10-14-76	M. S.
	H	.692/.688 WAS .712	7/1/78	M. S.
C-4	J	ADDED .712 DIA.	9/22/78	M. S.



NOTES:

1. THIS IS A HERMETICALLY SEALED RECEPTACLE
2. SCREW THREAD MEASUREMENT IN ACCORDANCE WITH H28 HANDBOOK. (3 WIRE METHOD). USING WIRE .02887 DIA. - MEASUREMENT OVER WIRE SHALL BE .510/.497

5-861255-1	TIN PLATED PIN AND FLANGE	WITH MARKING
861255-1	TIN-LEAD PLATED PIN AND FLANGE	WITH MARKING

				861255-1	TIN-LEAD PLATED PIN AND FLANGE	WITH MARKING
QTY REQD	QTY REQD	ITEM NO.	DWG SIZE	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION	SYMBOL
-2	-1				PARTS LIST	

				UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES .00 = ± .01 ANGLES ± 1° .000 = ± .005	CONTRACT NO.	AMP INCORPORATED CAPITRON DIVISION ELIZABETHTOWN, PENNSYLVANIA		
				MATERIAL: MOLDED GLASS EPOXY	DR 2/27/73	NAME FLANGED RECEPTACLE ASSEMBLY LGN-1L		
				FINISH: BLACK	CHK			
					APPD REF 3-27-73			
					APPD			
					DSGN APPD	SIZE B	CODE IDENT NO. 00779	NUMBER 861255
NEXT ASSY	FINAL ASSY	NEXT ASSY	USED ON		OTHER APPD	SCALE	WT	SHEET
QTY REQD		APPLICATION						