

AV series

Snap action security pushbutton switches •
Ø 16 mm • momentary (NO)



DISTINCTIVE FEATURES

Momentary (NO)
Compact
Long life
Marking available



ENVIRONMENTAL SPECIFICATIONS

- Optional front panel sealing : IP65 according to IEC 60529
- Operating temperature : -30 °C to +70 °C (-22 °F to +158 °F)



ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
200 mA 48 VDC - 100 mA 48 VDC
- Initial contact resistance : 50 mΩ max.
- Insulation resistance : 1,000 MΩ min. at 500 VDC
- Dielectric strength : 2,000 Vrms 50 Hz min.
between terminals and frame
- Electrical life : 50,000 cycles at 200 mA 48 VDC
100,000 cycles at 100 mA 48 VDC



GENERAL SPECIFICATIONS

- Travel : 1.60 mm (.063) ± 0.3 mm (.011)
- Torque : 5 Nm min. - 14 Nm max. applied to nut
- Panel thickness : 1 (.039) to 6 mm (.236) max.
- Low level or mechanical life : 1,000,000 cycles



MATERIALS

- Case : PBT
- Contacts : brass, silver plated (C)
- Bushing and actuator : see next page

The company reserves the right to change specifications without notice.




AV series

Snap action security pushbutton switches •
Ø 16 mm • momentary (NO)



ELECTRICAL FUNCTIONS



Function 3 (NO)



MOUNTING

- Panel cut-out : Ø 16.2 mm (.637)
- Min. pitch for matrix mounting :
24 mm x 24 mm (.944 x .944)
(AV6P & AV6B : 20 mm x 20 mm)

AV series

Snap action security pushbutton switches •
Ø 16 mm • momentary (NO)



BUILD YOUR PART NUMBER

SERIES		BUSHING/ACTUATOR CONFIGURATIONS		FUNCTION		CASE		CONTACTS		TERMINALS	
AV											
		06 Flat actuator 16 Curved actuator 08 Curved actuator + chamfer 07 Flat actuator + chamfer 6P Flat actuator + knurled nut 6B Curved actuator + knurled nut		3 NO		0 Short		C Brass, silver plated		9 Screw	

BUSHING/ACTUATOR MATERIALS		SEALING	
00 (std) Nickel plated brass / Nickel plated brass 10 Nickel plated brass / Stainless steel 40 Stainless steel / Stainless steel 70 Black chrome plated brass / Black chrome plated brass		Blank No sealing K Sealed to IP65	



ABOUT THIS SERIES

On the following pages, you will find successively basic part numbers of switches and options in the same order as in above chart

- Notice:** please note that not all combinations of above numbers are available. Refer to the following pages for further information.
- Mounting accessories:** standard hardware supplied : 1 hex nut. Standard and special hardware is presented in the "Hardware" section of website.

AV series

Snap action security pushbutton switches •
 Ø 16 mm • momentary (NO)

FLAT OR CURVED ACTUATOR SCREW TERMINALS



Flat actuator

AV0630C9



Curved actuator

AV1630C9



FLAT OR CURVED ACTUATOR WITH CHAMFER



Flat actuator

AV0830C9



Curved actuator

AV0730C9



WITH KNURLED NUT FOR MATRIX MOUNTING 20 X 20 (.787X.787)



Flat actuator

AV6P30C9




Curved actuator

AV6B30C9






Screw terminals for wires 1,5 mm² max.

Hex nut 19 (.748) across flats



Hex nut 19 (.748) across flats




Wrench available under P/N U1990.

AV series


Snap action security pushbutton switches •
Ø 16 mm • momentary (NO)

BUSHING/ACTUATOR MATERIALS




CODE	BUSHING	ACTUATOR
00 (std)	Nickel plated brass	Nickel plated brass
10	Nickel plated brass	Stainless steel
40	Stainless steel	Stainless steel
70	Black chrome plated brass	Black chrome plated brass

FLAT OR CURVED METAL ACTUATOR




SEALING



Blank No sealing
K Front panel sealing to IP65

OPTION K



- ① - elastomeric membrane
- ② - external gasket