






- ⚠ USE CRIMP TOOL: 354940-1
2. PANEL THICKNESS = 5.08 [.200] MAX
3. USE INSTRUCTION SHEET 408-4048
4. CAPACITANCE = 9400 PF ± 10% TOTAL
VOLTAGE = 500 VDC
- ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



OBSOLETE ⚠	RG-174/U, 188/U, 316/U	4.52 [.178]	1.73 [.068]	58436-3	227194-5	9-413658-0	1-329632-2	1-329631-2	1-413774-5	414757-3	5414758-3
	RG-174/U, 188/U, 316/U	4.52 [.178]	1.73 [.068]	58436-3	227194-5	9-413658-0	1-329632-2	1-329631-2	1-413774-5	414757-2	5414758-2
	RG-58/U, 58A/U, 58B/U, 58C/U	5.41 [.213]	1.73 [.068]	58436-1	-	9-221132-0	1-329631-2	1-329631-2	413774-5	414757-1	5414758-1
FOR USE WITH CABLE		FERRULE	CENTER CONTACT	DIE SET ⚠	⑥ SPACER QTY=1	⑤ FERRULE QTY=1	④ LOCK WASHER QTY=1	③ JAM NUT QTY=1	② CONTACT QTY=1	① JACK ASSEMBLY QTY=1	PART NUMBER
		HEX CRIMP HEIGHTS									