


DRAWING MADE IN AMERICAN PROJECTION

⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


NUMBER C-160718



.020 MAX.
(0.5)

.020 MAX.
(0.5)

FOR .020 TAB-THICKNESS
(0.5)



.010
(0.25)

.550
(14.0)

⚠ FOR AMP-D-TATOR APPLICATION

⚠ REELED WITH PAPER COVER

160718-9	⚠	BRASS	PRETIN	⚠
160718-8	⚠	BRASS	—	⚠
160718-5	⚠	PHOSPHOR BR	—	—
160718-4	⚠	BRASS	PRETIN	⚠
160718-3	⚠	BRASS	SILVER	—
160718-2	⚠	BRASS	PRETIN	—
160718-1	⚠	BRASS	—	—
ORDER NO.		MATERIAL	PLATING	
DR R. J. 13/11/77	DATE	DATE	DATE	DATE
CHK	DATE	DATE	DATE	DATE

CUSTOMER COPY FOR REFERENCE ONLY

©1977 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



AMP-HOLLAND N.V.
HERTOGENBOSCH
HOLLAND

WIRE RANGE 0.5-10 mm	INSUL RANGE 0.80-340 / 2x200 mm	FIRST USED
SCALE 4 ≈ 1	LOC H	SIZE A
NO C-160718	REV E2	

NAME 110 Ser FASTON RECEPTACLE

DIMENSIONS IN (MM) DO NOT SCALE PRINT