

1 2 3 4

A

B

C

D


A

B

C

D

Coupe AA



Racc CAD # 26 a 30


PART NUMBER	Finishing contact area
86290200162255DALF	Gold thickness(0.40µm mini) over Ni (2µm mini)
86290200162265DALF	Gold thickness(0.75µm mini) over Ni (2µm mini)

REV	DESIGNATION
B	UPDATE LOGO
C	ADD P/N


NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in 65-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see 65-14-920.

VUE F



VUE G



European Views

www.fciconnect.com				surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
				TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	TARON		2005/10/12	ANGULAR	LINEAR	0.X	±0.1	size	A3			
Eng	TARON		2005/10/12			0.XX' ±2°	0.XX	±0.1	Scale 3			
Chr	LEGARE		2005/10/12			0.XXX	±0.1	ECN LS06-0211				
Appr	LEGARE		2005/10/12	Product family				DIN HPC		Spec ref -		
				ENSEMBLE MODULES 4 * 5				dwg no C-8629-0106		Rev. C		
title REPRISE ARRIERE HDI												
catalog no				SEE TABLE				CUSTOMER		sheet 1 of 1		

rev	ecn no	dr	date
A	LS05-0086	JTA	2005/10/12
B	LS06-0095	LGO	2006/07/06
C	LS 06-0211	HLE	2006/12/11
-	-	-	-
-	-	-	-
-	-	-	-



REV F - 2006-04-17

1 2 3 4

PDM: Rev:C

STATUS:Released

Printed: Sep 28, 2009