









P.C.B. LAYOUT



CIRCUIT: DIAGRAM



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 260 ± 50 gf
6. TRAVEL: $0.25 \text{ mm} \pm 0.15$
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: $130g > 50,000$ CYCLES
- ▲ 9. SILVER CONTACT
10. PACKAGING: TAPE & REEL; 2300 PIECES PER REEL.
11. ▲ DENOTES CRITICAL PARAMETER

E-SWITCH®

TITLE TL3330AF260QG

A	16309	NEW RELEASE	8/14/06	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 8=1

DATE 6/14/2006

DR RC

DWG P010951

REV A