






Copyright FCI.



SCALE 1.000





rev	ecn no	dr	date
A	DG07-0385	CS	09/04/07
B	DG08-0248	BL	09/10/08
C	DG09-0040	BL	02/19/09
D	DG09-0094	BL	03/26/09
E	N10-0076	R.B	2010-04-30

www.fciconnect.com			surface - ✓		tolerance std		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	MAGGIE WU	07/14/06	ANGULAR	LINEAR	0. XXX		±0.15		size A4	Scale 0.707
Eng	GARY HSIEH	07/14/06			0. XX		±0.30			
Chr	PAUL WANG	07/14/06	0°		±°	0. X		±0.5		
Appr	JOSEPH HSIA	07/14/06	Product family -					ECN N10-0076		
								Spec ref *		
			title SMT TYPE DDR II ASS'Y					dwg no 10070983		Rev. E
			DDR II 240P							
			catalog no -					CUSTOMER		sheet 1 of 4

REV F - 2006-04-17







Copyright FCI.



title	SMT TYPE DDR II ASS'Y	dwg no	10070983	Rev.	E
	DDR II 240P				
catalog no	-	CUSTOMER	sheet 2 of 4		



Copyright FCI.



	title	SMT TYPE DDR II ASS'Y	dwg no	10070983	Rev.	E
		DDR II 240P				
	catalog no	-	CUSTOMER	sheet 3 of 4		



Copyright FCI.

10070983 - □ □ □ □

STYLE : MECHANICAL KEYING

1 : 1.8 VOLT. W/ CENTER KEY

HOLD DOWN TYPE

0 : CENTER HOLD DOWN, FORK LOCK
AT BOTH END

RESERVED

0

PLATING

CODE	CONTACT	SOLDERTAIL	UNDERPLATE
1LF	10u" (0.25um) MIN. GOLD	100u" (2.54um) MIN. 100% MATT TIN	50u" (1.27um) MIN. NICKEL OVERALL
2LF	15u" (0.38um) MIN. GOLD		
3LF	30u" (0.76um) MIN. GOLD		
4LF	GOLD FLASH		

COLOR OF HOUSING AND EJECTOR

0 : BLACK HOUSING + IVORY EJECTOR

NOTES:

1. MATERIAL:
HOUSING: HIGH PERFORMANCE RESINS, GLASS FILLED UL94V-0 RATED.
EJECTOR: HIGH PERFORMANCE RESINS, GLASS FILLED UL94V-0 RATED.
TERMINAL: HIGH PERFORMANCE COPPER ALLOY
METAL CLIP: COPPER ALLOY.
FCI LOGO TO BE APPROXIMATELY LOCATED AS SHOWN ON PRINT.
3. PRODUCT SPECIFICATION: GS-12-481.
4. PACKAGING SPECIFICATION: GS-14-899.
5. RECOMMENDED STENCIL THICKNESS NO LESS THAN 0.15 mm.
6. FOR OPTIMUM PERFORMANCE, THE TIE BAR IS TO BE ON AN INTERNAL LAYER SO THAT THE REMNANT CANNOT CAUSE CONTACT DAMAGE.
7. THE DATE CODE IS SHOWN "MM-DD-YY-W". "W" MEANS PRODUCTION LINE.
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
9. THE HOUSING WILL WITH STAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN AN IR REFLOW SOLDERING APPLICATION.



title SMT TYPE DDR II ASS'Y
DDR II 240P
catalog no -

dwg no 10070983

Rev.
E

CUSTOMER sheet 4 of 4