


NOT RECOMMENDED FOR NEW DESIGN,
USE SB1X0 SERIES

Features

High Current Capability and Low Forward Drop
 High Surge Capacity
 Guard Ring for Transient Protection
 Low Power Loss, High Efficiency



Mechanical Data

Case: DO-41, Molded Plastic
 Plastic Material: UL Flammability
 Classification Rating 94V-0
 Moisture sensitivity: Level 1 per J-STD-020A
 Terminals: Axial lead, Solderable per
 MIL-STD-202, Method 208
 Polarity: Cathode band
 Weight: 0.35 grams (approx.)

DO-41		
Dim	Min	Max
A	25.4	
B	4.1	5.2
C	0.71	0.86
D	2.0	2.7
All Dimensions in mm		

Maximum Ratings and Electrical Characteristics @ T_A = 25 °C unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load.
 For capacitive load, derate current by 20%.

Characteristic	Symbol	SR102	SR103	SR104	SR105	SR106	Unit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	V
Maximum RMS Voltage	V _{RSM}	14	21	28	35	42	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	V
Maximum Average Forward Rectified Current @ Lead Temperature (TL) measured 9.5mm lead length @ T _L = 75 C @ T _L = 100 C	I _(AV)	1.0			1.0		A
Peak Forward Surge Current 8.3ms half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	25					A
Maximum Forward Voltage @ 1.0A	V _F	0.55		0.60	0.70		V
Maximum Average Reverse Current at Peak Reverse Voltage @ T _A = 25 C @ T _A = 100 C	I _R I _R	1.0 10					mA
Typical Thermal Resistance (Note 1)	R _{JL}	15					K/W
Typical Total Capacitance (Note 2)	C _T	110			80		pF
Storage and Operating Temperature Range	T _J , T _{STG}	-65 to +150					C

Notes: 1. Thermal Resistance from Junction to Ambient with Vertical PC Board Mounting, 1.27mm Lead Length.
 2. Measured at 1.0MHz and applied reverse voltage of 4.0V.




Fig. 1, Forward Current Derating Curve




Fig. 2, Typical Forward Characteristics




Fig. 3, Typical Total Capacitance




Fig. 4, Max Non-Repetitive Peak Fwd Surge Current

NOT RECOMMENDED FOR NEW DESIGN,
USE SB1X0 SERIES