




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
170	A	RELEASED	SAS	07/21/99	JC	2/11/00	DJC	4/28/00



WIRE ATTACHMENT
BUTTON

WIRE ACCESS
HOLE



SPECIFICATIONS:

1. DO-IT-YOURSELF, Ø4mm STACKING BANANA PLUG, BUTTON ATTACHMENT (SOLDERLESS).
2. INSULATOR BODY: POLYACETAL
3. PLUG BODY: BRASS, NICKEL PLATED
4. CONTACT SPRING: BECU, NICKEL PLATED
5. VOLTAGE: 500V
6. CURRENT: 36A MAX.
7. TEMPERATURE: -20°C TO +80°C
8. CONDUCTOR: SIZES Ø.090 (12AWG)
9. INSULATION: Ø.156
10. STRIP LENGTH: .25 (6.4)

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

DRAWING TITLE:
STACKING PLUG, BUTTON ATTACHMENT, RED

Tolerances Unless
Otherwise Specified
Fractions $\pm 1/32$
Decimals
.XX $\pm .01$
.XXX $\pm .005$

DRAWN BY:	DATE:
SCOTT SERRITELLA	07/21/99
CHECKED BY:	DATE:
JOHN COLE	2/11/00
APPROVED BY:	DATE:
DANIEL CAREY	4/28/00

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	2296	92N4658.DWG	A
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1