

4

3

2

1

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-11-004587			11MAR11	RK	HMR




MATERIALS:
HOUSING: POLYAMIDE, UL94V-0, BLACK.
TERMINALS: COPPER ALLOY, TIN PLATED.
SCREWS: STEEL, ZINC PLATED, UNLESS OTHERWISE STATED.

ELECTRICAL:
RATING: 20A, UL & CSA.


MECHANICAL:
WIRE RANGE: 12-22 AWG.
MAXIMUM TIGHTENING TORQUE: 7 IN-LBS.

ENVIRONMENTAL:
CONTINUOUS OPERATING TEMP.: -40°C TO +105°C

- 1 PRELIMINARY PART NUMBER.
- 2 SCREWS ARE NICKEL PLATED BRASS.



1546834-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 8/17/04	 TE Connectivity					
		CHK S YODER 8/17/04						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .010 4 PLC ± - ANGLES ± -	APVD S YODER 8/17/04	NAME NC6-P107-XX ASSEMBLY					
		PRODUCT SPEC -						
		APPLICATION SPEC -	SIZE			CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT -	A3		00779	C-1437664-4		-
MATERIAL -	FINISH -	CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1	REV B1

9.059	24	NC6-P107-24	2-1437664-7
8.684	23	NC6-P107-23	1546834-4
8.309	22	NC6-P107-22	2-1437664-6
7.934	21	NC6-P107-21	1546834-3
7.559	20	NC6-P107-20	2-1437664-5
7.184	19	NC6-P107-19	1546834-2
6.809	18	NC6-P107-18	1546834-1
6.434	17	NC6-P107-17	2-1437664-3
6.059	16	NC6-P107-16	2-1437664-2
5.684	15	NC6-P107-15	2-1437664-1
5.309	14	NC6-P107-14	2-1437664-0
4.934	13	NC6-P107-13	1-1437664-8
4.559	12	NC6-P105-12	1-1546834-0
4.559	12	NC6-P107-12	1-1437664-7
4.184	11	NC6-P105-11	1546834-9
4.184	11	NC6-P107-11	1-1437664-6
3.809	10	NC6-P105-10	1546834-8
3.809	10	NC6-P107-10	1-1437664-4
3.434	9	NC6-P107-09	1-1437664-3
3.059	8	NC6-P105-08	1546834-7
3.059	8	NC6-P107-08	1-1437664-1
2.684	7	NC6-P107-07-060	1546834-6
2.684	7	NC6-P107-07	1-1437664-0
2.309	6	NC6-P107-06	1437664-9
1.934	5	NC6-P107-05	1437664-7
1.559	4	NC6-P107-04	1437664-6
1.184	3	NC6-P107-03	1437664-5
.809	2	NC6-P107-02	1437664-4

DIM A	NO OF POS	CATALOG NUMBER	PART NUMBER
-------	-----------	----------------	-------------