

4

DRAWING MADE IN THIRD ANGLE PROJECTION

3

THIS DRAWING IS UNPUBLISHED.

2

RELEASED FOR PUBLICATION

1

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F

ZONE

LTR

DESCRIPTION

DATE

APPD

CH

11

D

ECN96022902 OBSOLETE (PENDING) 192447-3

05/MAR/96

D1

REVISED PER ECO-09-020935

09SEP09

AEG

1

FINISH – SILVER PLATE, 200 MIN μINCHES THICK, PER AMP SPEC 112-32-1.

2

FINISH – NICKEL PLATE, 100 MIN μINCHES THICK, PER AMP SPEC 112-246-1.

3

HARDWARE FURNISHED FOR:

192447-7 2 NUTS, 2 WASHERS

1-192447-1 2 NUTS, NO WASHERS

1-192447-9 1 NUT, NO WASHERS

4

UNLESS OTHERWISE SPECIFIED, Ø”F” EQUALS Ø”C”.

5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	5	-	-	9.4[.37]	Ø6.1[.24]	1/2-20UNF-2A	31.7[1.25]	NO	A	1	-	2-192447-0
		-	-	17.0[.67]	Ø8.2[.32]	9/16-18UNF-2A	34.2[1.35]	YES	A	1	-	1-192477-9
OBSOLETE	5	-	-	17.0[.67]	Ø8.2[.32]	9/16-18UNF-2A	34.2[1.35]	NO	A	1	09112	1-192447-8
		-	-	9.4[.37]	Ø4.1[.16]	5/16-32UNEF-2A	19.6[.77]	NO	A	1	-	1-192447-7
		-	41.8[1.64]	19.9[.78]	Ø35.0[1.38]	M50 X 1.5-6g	62.0[2.44]	NO	B	1	09133	1-192447-6
		-	41.3[1.62]	20.7[.81]	Ø30.0[1.18]	M48 X 1.5-6g	62.0[2.44]	NO	B	1	09079	1-192447-5
		-	43.1[1.69]	21.9[.86]	Ø25.0[.98]	1 5/8-16UN-2A	62.2[2.45]	NO	B	1	09165	1-192447-4
OBSOLETE		-	-	21.1[.83]	Ø20.1[.79]	1 1/4-18UNEF-2A	42.2[1.66]	NO	A	1	09173	1-192447-3
		-	-	17.3[.68]	Ø12.0[.47]	3/4-16UNF-2A	34.0[1.34]	NO	A	1	10260	1-192447-2
		-	-	17.0[.67]	Ø8.2[.32]	9/16-18UNF-2A	34.2[1.35]	YES	A	1	-	1-192447-1
		-	-	8.4[.33]	Ø2.3[.09]	5/16-32UNEF-2A	16.5[.65]	NO	A	1	09183	1-192447-0
		-	-	9.4[.37]	Ø4.1[.16]	M8 X 0.75-6g	19.6[.77]	NO	A	1	09026	192447-9
		-	-	9.4[.37]	Ø4.1[.16]	5/16-32UNEF-2A	19.6[.77]	NO	A	1	09111	192447-8
		-	-	9.4[.37]	Ø4.1[.16]	5/16-32UNEF-2A	19.6[.77]	YES	A	2	10244	192447-7
		-	-	14.5[.57]	Ø4.1[.16]	5/16-32UNEF-2A	28.4[1.12]	NO	A	1	10394	192447-6
		Ø4.3[.17]	-	14.5[.57]	Ø4.1[.16]	5/16-32UNEF-2A	38.1[1.50]	NO	A	1	10611	192447-5
		-	-	9.4[.37]	Ø6.1[.24]	1/2-28UNEF-2A	19.6[.77]	NO	A	1	10934	192447-4
		-	-	9.4[.37]	Ø6.1[.24]	1/2-20UNF-2A	19.6[.77]	NO	A	2	10263	192447-3
		-	-	9.4[.37]	Ø6.1[.24]	1/2-20UNF-2A	19.6[.77]	NO	A	1	09182	192447-2
		-	-	19.2[.76]	Ø16.1[.63]	15/16-20UNEF-2A	38.1[1.50]	NO	A	1	09066	192447-1
		F	E	D	C	B	A	H'WARE INCL	FIGURE	FINISH (NOTE #)	WAS	PART NO.

DO NOT SCALE PRINT. UNLESS SPECIFIED

DIMENSIONS IN mm [INCHES]

TOLERANCES ON :

1 PLC DEC ± 0.5 [.02]

2 PLC DEC ± 0.25 [.010]

ANGLES ± -

MATERIAL

BRASS

FINISH

1 2

DR D. WILSON

04-02-92

CHK R.JAYNE

5-04-92

APPD A.GRIFFIN

5-04-92

APPD P.GLASER

5-06-92

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

AMP

AMP Incorporated

Harrisburg, PA 17105-3608

NAME

THREADED SLEEVE SOCKET ASSY

SIZE

CAGE CODE

DRAWING NO

192447

SCALE

NONE

SHEET

1 OF 2

AMP 1471-6 REV 7-90

Translation 061031.040412 (YYMMDD.HHMMSS) from Computervision, Inc., Medusa Revision 12.2.5T

CUSTOMER DRAWING

