




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			W	REV PER ECO 15-016064	11-9-15	CT	CD

1. THIS RECEPTACLE WILL MATE WITH ANY PLUG CONNECTOR WITH THE SAME INSERT ARRANGEMENT AS DEFINED BY MS18275-2.
2. MAXIMUM WIRE INSULATION USED WITH THIS RCPT. IS .054 [1.37] DIA.
3. Be-Cu RETENTION CLIPS ARE INCLUDED IN INSERTS.

- ④ INSPECTION REQUIREMENTS PER R4383.
- ⑤ CONNECTOR SUPPLIED WITH 49 CONTACTS, MFG'S PART NUMBER 206071-1. INSPECTION REQUIREMENTS PER R4383 WITHOUT TESTS FOR HIGH ALTITUDE DIELECTRIC WITHSTANDING VOLTAGE AS CALLED FOR IN TABLE II SCREENING AND TESTING.
- ⑥ UL/CSA DESIGNATION MARKED IN THIS AREA,OPTIONAL
- ⑦ SPECIAL TESTING PER GE DOCUMENT 20025720. CONNECTOR SUPPLIED WITH 54 CONTACTS, MFG'S P/N 206071-1.
- ⑧ RESTRICTED TO CAE ELECTRONICS ONLY.
- ⑨ THESE CONNECTORS ARE QUALIFIED TO GODDARD SPACE FLIGHT CENTER SPECIFICATION S-311-P-4.



MFG'S P/N 206071-1
GSFC P/N G-08-S1
(SUPPLIED WITH 206064-7 AND
206064-8 ONLY)



	.120 [3.05]	570566-3	1-206064-0	1-206064-0
	.120 [3.05]	311P407-3S-B-12	206064-4	206064-9
	.120 [3.05]	20025720P1044S	206064-8	206064-8
	.120 [3.05]	R4383P44S	206064-7	206064-7
	.120 [3.05]	---	206064-6	206064-6
	.120 [3.05]	R4383P44S-2	206064-5	206064-5
	.120 [3.05]	311P407-3S-B-12	206064-4	206064-4
	.154 [3.91]	---	206064-3	206064-3
	.154 [3.91]	311P407-3S-B-15	206064-2	206064-2
	.120 [3.05]	R9259P44S	206064-1	206064-1
REMARKS	DIA A	CUSTOMER P/N ON CONNECTOR	AMP P/N ON CONNECTOR	MFG'S P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN P. YEAGER		050C106		 TE Connectivity			
DIMENSIONS: INCHES				TOLERANCES UNLESS OTHERWISE SPECIFIED:						CHK D. MILLER		050C106		NAME			
										APPRO D. MILLER							