


Panasonic
ideas for life

HIGH ELECTRICAL & MECHANICAL NOISE IMMUNITY RELAY

JQ RELAYS



mm inch

FEATURES

- High electrical noise immunity
- High switching capacity in a compact package
- High sensitivity: 200 mW (1a), 400 mW (1c)
- High surge voltage: 8,000 V between contacts and coil
- UL, CSA, VDE, TÜV, SEMKO approved
- Class B coil insulation type available

SPECIFICATIONS

Contact

				Standard type		High capacity type	
Arrangement				1 Form A, 1 Form C			
Initial contact resistance, max. (By voltage drop 6 V DC 1 A)				100 mΩ			
Contact material				Silver alloy			
Rating (resistive)	Nominal switching capacity	1a		5 A 125 V AC 2 A 250 V AC 5 A 30 V DC		10 A 125 V AC 5 A 250 V AC 5 A 30 V DC	
				5 A 125 V AC 2 A 250 V AC 3 A 30 V AC		10 A 125 V AC 5 A 250 V AC 5 A 30 V DC	
				2 A 125 V AC 1 A 250 V AC 1 A 30 V DC		3 A 125 V AC 2 A 250 V AC 1 A 30 V DC	
		1c		2 A 125 V AC 1 A 250 V AC 1 A 30 V DC		3 A 125 V AC 2 A 250 V AC 1 A 30 V DC	
				625 VA, 150 W		1,250 VA, 150 W	
				625 VA, 90 W		1,250 V AC, 150 W	
	Max. switching power	1c		250 VA, 30 W		500 V AC, 30 W	
				Max. switching voltage 250 V AC, 110 V DC (0.3A)			
	Max. switching current				N.O.: 5 A N.C.: 2 A		N.O.: 10 A N.C.: 3 A
Min. switching capacity ^{#1}				100 mA, 5 V DC			
Expected mechanical life (at 180 cpm)(min. operations)				10 ⁷			

Expected electrical life (min. operations)

Type	Switching capacity	No. of operations
Standard type	1a	5 A 125 V AC 3 A 125 V AC 2 A 250 V AC 5 A 30 V DC 10 ⁵
		5×10 ⁴ 2×10 ⁵ 2×10 ⁵ 10 ⁵
	1c	5 A 125 V AC 2 A 250 V AC 3 A 30 V DC 10 ⁵
		5×10 ⁴ 2×10 ⁵ 10 ⁵
	1c	2 A 125 V AC 1 A 250 V AC 1 A 30 V DC 10 ⁵
		2×10 ⁵ 2×10 ⁵ 10 ⁵
High capacity type	1a	10 A 125 V AC 5 A 250 V AC 5 A 30 V DC 10 ⁵
		5×10 ⁴ 5×10 ⁴ 10 ⁵
	1c	10 A 125 V AC 5 A 250 V AC 5 A 30 V DC 10 ⁵
		5×10 ⁴ 5×10 ⁴ 10 ⁵
	1c	3 A 125 V AC 2 A 250 V AC 1 A 30 V DC 10 ⁵
		2×10 ⁵ 2×10 ⁵ 10 ⁵

Coil (at 20°C 68°F)

Nominal operating power	1a: 200 mW	1c: 400 mW
-------------------------	------------	------------

Characteristics

Max. operating speed		20 cpm
Initial insulation resistance ^{*1}		Min. 1,000 MΩ at 500 V DC
Initial breakdown voltage ^{*2}	Between open contacts	1a: 1,000 Vrms for 1 min. 1c: 750 Vrms for 1 min.
	Between contacts and coil	4,000 Vrms for 1 min.
Surge voltage between contact and coil ^{*3}		8,000 V
Operate time ^{*4} (at nominal voltage)		Approx. 5 ms
Release time ^{*4} (at nominal voltage)(without diode)		Approx. 2 ms
Temperature rise ^{*5}		Max. 45°C
Shock resistance	Functional ^{*6}	Min. 294 m/s ² {30 G}
	Destructive ^{*7}	Min. 980 m/s ² {100 G}
Vibration resistance	Functional ^{*8}	98 m/s ² {10 G}, 10 to 55 Hz at double amplitude of 1.6 mm
	Destructive	117.6 m/s ² {12 G}, 10 to 55 Hz at double amplitude of 2.0 mm
Conditions for operation, transport and storage ^{*9} (Not freezing and condensing at low temperature)		Ambient temp. ^{*10}
		Humidity
		–40°C to +85°C –40°F to +185°F
		5 to 85% R.H.
Unit weight		Approx. 7 g .25 oz

^{#1} This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

Remarks

* Specifications will vary with foreign standards certification ratings.

^{*1} Measurement at same location as "Initial breakdown voltage" section

^{*2} Detection current: 10 mA

^{*3} Wave is standard shock voltage of ±1.2 × 50μs according to JEC-212-1981

^{*4} Excluding contact bounce time

^{*5} Measured conditions

Standard type	Resistive, nominal voltage applied to the coil. Contact carrying current: 5 A, at 70°C 158°F
High capacity type	Resistive, nominal voltage applied to the coil. Contact carrying current: 10 A, at 70°C 158°F

^{*6} Half-wave pulse of sine wave: 11ms; detection time: 10μs

^{*7} Half-wave pulse of sine wave: 6ms

^{*8} Detection time: 10μs

^{*9} Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT

^{*10} When using relays in a high ambient temperature, consider the pick-up voltage rise due to the high temperature (a rise of approx. 0.4% V for each 1°C 33.8°F with 20°C 68°F as a reference) and use a coil impressed voltage that is within the maximum allowable voltage range.

TYPICAL APPLICATIONS

- Air conditioners
- Refrigerators
- Microwave ovens
- Heaters

ORDERING INFORMATION

Ex. JQ 1a P — B — 12 V — F


Contact arrangement	Contact capacity	Coil insulation class	Coil voltage (DC)	Environmental support
1a: 1 Form A 1: 1 Form C	Nil: Standard P: High capacity	Nil: Class E coil insulation B: Class B coil insulation	5, 6, 9, 12, 18, 24, 48* V	F: RoHS Directive conforming type (AgSnO ₂ type) Nil: RoHS Directive non-conforming type (AgCdO type)

UL/CSA, VDE, SEMKO approved type is standard.

* Available only for 1 Form C type

TYPES AND COIL DATA at 20°C 68°F



	Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (min.)	Drop-out voltage, V DC (min.)	Nominal operating current, mA	Nominal operating power, mW	Coil resistance, Ω (±10%)	Max. allowable voltage, V DC
1 Form A	Standard type	JQ1a-5V (-F)	5	3.75	40	200	125	180% of nominal voltage (at 20°C 68°F)
		JQ1a-6V (-F)	6	4.5	33.3		180	
		JQ1a-9V (-F)	9	6.75	22.2		405	
		JQ1a-12V (-F)	12	9	16.7		720	
		JQ1a-18V (-F)	18	13.5	11.1		1,620	
		JQ1a-24V (-F)	24	18	8.3		2,880	
	High capacity type	JQ1aP-5V (-F)	5	4	40	200	125	130% of nominal voltage (at 85°C 185°F)
		JQ1aP-6V (-F)	6	4.8	33.3		180	
		JQ1aP-9V (-F)	9	7.2	22.2		405	
		JQ1aP-12V (-F)	12	9.6	16.7		720	
		JQ1aP-18V (-F)	18	14.4	11.1		1,620	
		JQ1aP-24V (-F)	24	19.2	8.3		2,880	
1 Form C	Standard type	JQ1-5V (-F)	5	3.75	80	400	62.5	150% of nominal voltage (at 20°C 68°F)
		JQ1-6V (-F)	6	4.5	66.7		90	
		JQ1-9V (-F)	9	6.75	44.4		202.5	
		JQ1-12V (-F)	12	9	33.3		360	
		JQ1-18V (-F)	18	13.5	22.2		810	
		JQ1-24V (-F)	24	18	16.7		1,440	
	High capacity type	JQ1P-5V (-F)	5	4	80	400	62.5	110% of nominal voltage (at 85°C 185°F)
		JQ1P-6V (-F)	6	4.8	66.7		90	
		JQ1P-9V (-F)	9	7.2	44.4		202.5	
		JQ1P-12V (-F)	12	9.6	33.3		360	
		JQ1P-18V (-F)	18	14.4	22.2		810	
		JQ1P-24V (-F)	24	19.2	16.7		1,440	
		JQ1P-48V (-F)	48	38.4	8.3		5,760	



REFERENCE DATA

Max. switching capacity (1 Form A type)

Max. switching capacity (1 Form C type)



Standard type

1-(1). Operate & release time (1 Form A type)
Tested sample: JQ1a-12V, 25 pcs.

1-(2). Operate & release time (1 Form C type)
Tested sample: JQ1-24V, 25 pcs.

2. Life curve
Ambient temperature: room temperature

