





REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	A	RELEASED	EO	07/25/06	SA	07/25/06	HO	07/25/06


 RoHS
Compliant

PANEL CUTOUT

SPECIFICATIONS:


Shell: Steel, Zinc Yellow Chromated
 Insulator: UL 94V-0 Rated, Black
 1. PBT+30% Fiber Glass
 2. Nylon-66
 Current Rating: 5 Amps
 Contact Resistance: 15 miliohms Max
 Insulator Resistance: 1000 Megohms Min
 Voltage: 500 VAC for 1 Minute
 Temperature: -50°C to +100°C

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
 HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
 BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
 CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
 USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
 FOR THE INTENDED USE AND ASSUME ALL RISK AND
 LIABILITY WHATSOEVER IN CONNECTION THEREWITHE.

TOLERANCES:
 Unless Otherwise
 Specified
 $.X \pm 0.35$ [0.014]
 $.XX \pm 0.15$ [0.006]

DRAWN BY: EKLAS ODISH
DATE: 07/25/06
CHECKED BY: SAMI ALNADI
DATE: 07/25/06
APPROVED BY: HISHAM ODISH
DATE: 07/25/06

DRAWING TITLE: 25 Pin Crimp Type D-Sub Plug
SIZE A **DWG. NO.** SPC15272 **ELECTRONIC FILE** 79K4869.DWG **REV** A
SCALE: NTS **U.O.M.:** mm [INCHES] **SHEET:** 1 OF 2



SPECIFICATIONS

Contact: Brass, Stamped Gold-Plated
on Contact Area Nickel-Plated
on Crimp-Area