


### SUBMINIATURE T-3/4 (1.9 mm) SOLID STATE LAMPS

|               |                  |                 |               |                  |       |
|---------------|------------------|-----------------|---------------|------------------|-------|
| High Eff. Red | <b>QTLP913-2</b> | RED DIFFUSED    | High Eff. Red | <b>QTLP912-2</b> | CLEAR |
| Yellow        | <b>QTLP913-3</b> | YELLOW DIFFUSED | Yellow        | <b>QTLP912-3</b> | CLEAR |
| Green         | <b>QTLP913-4</b> | GREEN DIFFUSED  | Green         | <b>QTLP912-4</b> | CLEAR |
| AlGaAs Red    | <b>QTLP913-7</b> | RED DIFFUSED    | AlGaAs Red    | <b>QTLP912-7</b> | CLEAR |
| AlGaAs Red    | <b>QTLP913-9</b> | RED DIFFUSED    | AlGaAs Red    | <b>QTLP912-9</b> | CLEAR |

#### PACKAGE DIMENSIONS



Note: All dimensions are in inches (mm).

#### DESCRIPTION

These subminiature LED lamps are intended for low cost status indication on PCBs, backlighting keyboards and switches. They are compatible with vapor phase reflow or wave solder surface mount equipment. Both clear and tinted diffused lenses, as well as a choice of "yoke", "Z-bend", or "gull-wing" lead bends are available.

#### FEATURES

- Subminiature package
- Low package profile
- Choice of clear or tinted diffused lens
- Three lead bend options
- Tape and reel option

#### ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub>=25°C unless otherwise specified)






|                                                                             | High Eff. Red<br><b>QTLP913-2</b><br><b>QTLP912-2</b>         | Yellow<br><b>QTLP913C-3</b><br><b>QTLP912C-3</b> | Green<br><b>QTLP913-4</b><br><b>QTLP912-4</b> | AlGaAs Red<br><b>QTLP913C-7,9</b><br><b>QTLP912C-7,9</b> | Unit |
|-----------------------------------------------------------------------------|---------------------------------------------------------------|--------------------------------------------------|-----------------------------------------------|----------------------------------------------------------|------|
| DC Forward Current (I <sub>F</sub> )                                        | 30                                                            | 20                                               | 30                                            | 40                                                       | mA   |
| Peak Forward Current (I <sub>F</sub> )<br>@ f = 1.0 KHz, Duty factor = 1/10 | 160                                                           | 160                                              | 160                                           | 200                                                      | mA   |
| Power Dissipation (P <sub>d</sub> )                                         | 100                                                           | 85                                               | 100                                           | 100                                                      | mW   |
| Reversed Voltage (V <sub>R</sub> ) I <sub>R</sub> = 10μA                    | 5                                                             | 5                                                | 5                                             | 5                                                        | V    |
| Operating Temperature Range                                                 | -40°C to +85°C                                                |                                                  |                                               |                                                          |      |
| Storage Temperature Range                                                   | -40°C to +100°C                                               |                                                  |                                               |                                                          |      |
| Lead Soldering Time                                                         | 5 secs @ 260°C for wave solder; 10 secs @ 260°C for IR reflow |                                                  |                                               |                                                          |      |

#### ELECTRO-OPTICAL CHARACTERISTICS (T<sub>A</sub>=25°C unless otherwise specified)

| Part Number: QTLP                      | High Eff.<br>Red<br>912-2 | Yellow<br>912-3 | Green<br>912-4 | AlGaAs<br>Red<br>912-7,9 | Test Condition         |
|----------------------------------------|---------------------------|-----------------|----------------|--------------------------|------------------------|
| <b>Luminous Intensity (mcd)</b>        |                           |                 |                |                          | I <sub>F</sub> = 20 mA |
| <b>Minimum</b>                         | 40                        | 15              | 30             | 110                      |                        |
| <b>Typical</b>                         | 80                        | 30              | 50             | 170                      |                        |
| <b>Forward Voltage (V<sub>F</sub>)</b> |                           |                 |                |                          | I <sub>F</sub> = 20 mA |
| <b>Minimum</b>                         | 1.7                       | 1.7             | 1.7            | 1.7                      |                        |
| <b>Typical</b>                         | 2.0                       | 2.0             | 2.1            | 2.0                      |                        |
| <b>Maximum</b>                         | 2.8                       | 2.8             | 2.8            | 2.8                      |                        |
| <b>Peak Wavelength (nm)</b>            | 635                       | 585             | 565            | 660                      | I <sub>F</sub> = 20 mA |
| <b>Spectral Line Half Width (nm)</b>   | 45                        | 35              | 30             | 20                       | I <sub>F</sub> = 20 mA |
| <b>Viewing Angle (degrees)</b>         | 25                        | 25              | 25             | 25                       | I <sub>F</sub> = 20 mA |

| Part Number: QTLP                      | High Eff.<br>Red<br>913-2 | Yellow<br>913-3 | Green<br>913-4 | AlGaAs<br>Red<br>913-7,9 | Test Condition         |
|----------------------------------------|---------------------------|-----------------|----------------|--------------------------|------------------------|
| <b>Luminous Intensity (mcd)</b>        |                           |                 |                |                          | I <sub>F</sub> = 20 mA |
| <b>Minimum</b>                         | 10                        | 10              | 2              | 70                       |                        |
| <b>Typical</b>                         | 15                        | 15              | 5              | 110                      |                        |
| <b>Forward Voltage (V<sub>F</sub>)</b> |                           |                 |                |                          | I <sub>F</sub> = 20 mA |
| <b>Minimum</b>                         | 1.7                       | 1.7             | 1.7            | 1.7                      |                        |
| <b>Typical</b>                         | 2.0                       | 2.0             | 2.1            | 2.0                      |                        |
| <b>Maximum</b>                         | 2.8                       | 2.8             | 2.8            | 2.8                      |                        |
| <b>Peak Wavelength (nm)</b>            | 635                       | 585             | 565            | 660                      | I <sub>F</sub> = 20 mA |
| <b>Spectral Line Half Width (nm)</b>   | 45                        | 35              | 30             | 20                       | I <sub>F</sub> = 20 mA |
| <b>Viewing Angle (degrees)</b>         | 50                        | 50              | 50             | 50                       | I <sub>F</sub> = 20 mA |

## TYPICAL ELECTRO-OPTICAL CHARACTERISTIC CURVES (T<sub>A</sub> = 25°C)



**DISCLAIMER**

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

**LIFE SUPPORT POLICY**

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Everlight:

[QTLP9132YR](#) [QTLP9133GR](#) [QTLP9137GR](#) [QTLP9134YR](#) [QTLP912EGR](#) [QTLP912RYR](#) [QTLP9133YR](#)  
[QTLP912RZR](#) [QTLP912YYR](#) [QTLP9133ZR](#) [QTLP912EZR](#) [QTLP9123GR](#) [QTLP9122YR](#) [QTLP912RGR](#)  
[QTLP9134ZR](#) [QTLP912YGR](#) [QTLP9132ZR](#) [QTLP912EYR](#) [QTLP9124YR](#) [QTLP9122ZR](#) [QTLP9124ZR](#)  
[QTLP9132GR](#) [QTLP9127YR](#) [QTLP9123YR](#) [QTLP9137YR](#) [QTLP9134GR](#) [QTLP9123ZR](#) [QTLP9127ZR](#)  
[QTLP912YZR](#) [QTLP9127GR](#) [QTLP9137ZR](#) [QTLP9122GR](#)