

SEARCH OUR
PRODUCTS

aluminum
electrolytic &
organic
semiconductor

film

power film

tantalum
ceramic

TECH TOOLS



Aluminum Electrolytic Capacitors

+105°C General Purpose Surface Mount Chip Aluminum Electrolytic Capacitors

Part Number: 336SMH035M

[General Specifications \(PDF\)](#)

[Special Order Options](#)

[SMH document \(PDF\)](#)



Electrical Specifications

Capacitance: 33.0 μ F

Tolerance: -20 %, +20 %

Dissipation Factor: 0.14 at 120 Hz

ESR: 7.033 Ohms at 20° C and 120 Hz

Impedance:

--

--

Impedance Ratios:

2.0 at at -25°C/20°C

3.0 at at -40°C/20°C

Load Life:

1000 Hours at 105°C with 100% of rated voltage and with 0% of rated ripple current

Temperature Range: -55°C to +105°C

WVDC: 35 volts DC

SVDC: 44.0 volts DC

Leakage Current:

11.55 μ A after 2 Minutes

Ripple Current:

42.0 mA at 120 Hz and 105°C

Physical Specifications

Diameter (D): 6.3 mm + 0.5 mm

Length (L): 5.8 mm + 0.2 mm

Lead Spacing: 2.2 mm +/- 0.2 mm

Lead Wire(R): 0.5 mm to 0.8 mm

Base Length(H): 6.6 mm +/- 0.2 mm

Lead to Lead(C): 7.3 mm +/- 0.2 mm

Base Width(W): 6.6 mm +/- 0.2 mm

