






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		0	RELEASED PER 063B-0330-01	17-AUG-01	KW	CJ



- 1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.
- 2 PLATING: CONTACTS - 0.38µm MINIMUM GOLD ON MATING END,
2.54µm MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27µm MINIMUM NICKEL.
HOLDDOWNS: 2.54µm MINIMUM TIN-LEAD OVER 1.27µm MINIMUM
NICKEL.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.



PCB LAYOUT COMPONENT SIDE 4

METRIC

33.00	37.43	33.00	40.14	12	1-1445088-2
30.00	34.43	30.00	37.14	11	1-1445088-1
27.00	31.43	27.00	34.14	10	1-1445088-0
24.00	28.43	24.00	31.14	9	1445088-9
21.00	25.43	21.00	28.14	8	1445088-8
18.00	22.43	18.00	25.14	7	1445088-7
15.00	19.43	15.00	22.14	6	1445088-6
12.00	16.43	12.00	19.14	5	1445088-5
9.00	13.43	9.00	16.14	4	1445088-4
6.00	10.43	6.00	13.14	3	1445088-3
3.00	7.43	3.00	10.14	2	1445088-2
DIM Z	DIM V	DIM T	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J.ROOT 09OCT2000	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK K. WHITAKER 17-APR-2001	NAME RT ANG THRU HOLE HEADER ASSY, 0.38 MIC GOLD CONTACTS W/THRU HOLE HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH -		APVD C. JONES 17-APR-2001	SIZE A2	
MATERIAL -		PRODUCT SPEC -	CAGE CODE 00779	
		APPLICATION SPEC -	DRAWING NO 1445088	
		WEIGHT -	SCALE 5:1	
		CUSTOMER DRAWING	SHEET 1 OF 1	
			REV 0	