






Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4600-050.
TUSONIX RoHS COMPLIANT PART NUMBER: 4600-050 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. MATERIALS:
BUSHING - TIN PLATED STEEL.
LEAD STANDARD PART; SOLDER PLATED COPPER.
RoHS PART; SILVER PLATED COPPER.
NUT - TIN PLATED BRASS.
L"WASHER - TIN PLATED PHOSPHOR BRONZE.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. MOUNTING TORQUE: 8 lb - ins. max.
5. DCR - .01 max.
6. MAX. SOLDER TEMPERATURE 500°F.



MIN. CAP (UF)		DWV (VDC)	I.R. MIN. @ 100 (VDC.)	WORKING VOLTAGE D.C.		CURRENT DC (AMPS).	MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220						TEMP. CHARAC.																											
				85°C	125°C		30 KHz	100 KHz	300 KHz	1 MHz	10 MHz	1 GHz																												
1.4		300	10 G	100	70	15	15	25	34	44	60	70	X7W																											
<table><tr><td colspan="2" rowspan="4"> REVISION RECORD Original Release C.O. 6769 METRIC DIMS & NOTES ADDED. E.C. 7-17-92 6789 WVDC REVISED 100 & 70 WERE 80 & 50. L.E. 10-26-92 6992 RDN TO COMP FMT. S.M. 02-14-02 20020213-4-03 WORKING VOLTAGE REV'D 100, 70 WERE 80, 50 & TEMP. CHARAC. ADDED 20020903-1-02 ADDED NOTE S 1 & 3. REVISED NOTE 2. S.M. 06-24-05 20050608-2-02 </td><td colspan="2">--TOLERANCES-- Unless Otherwise Specified</td><td colspan="4" rowspan="2">Title COAXIAL BROADBAND - "C" </td></tr><tr><td colspan="2">DECIMAL ± </td></tr><tr><td colspan="2">ANGLES ± </td><td colspan="2">Drawn S.M. 02-14-02</td><td colspan="2">Scale 2 X</td></tr><tr><td colspan="2" rowspan="2"> TUSONIX TUCSON, ARIZONA </td><td colspan="4">Approved T.C. 02-14-02</td></tr><tr><td>A</td><td colspan="4">4600-050</td></tr></table>														REVISION RECORD Original Release C.O. 6769 METRIC DIMS & NOTES ADDED. E.C. 7-17-92 6789 WVDC REVISED 100 & 70 WERE 80 & 50. L.E. 10-26-92 6992 RDN TO COMP FMT. S.M. 02-14-02 20020213-4-03 WORKING VOLTAGE REV'D 100, 70 WERE 80, 50 & TEMP. CHARAC. ADDED 20020903-1-02 ADDED NOTE S 1 & 3. REVISED NOTE 2. S.M. 06-24-05 20050608-2-02		--TOLERANCES-- Unless Otherwise Specified		Title COAXIAL BROADBAND - "C"				DECIMAL ±		ANGLES ±		Drawn S.M. 02-14-02		Scale 2 X		TUSONIX TUCSON, ARIZONA		Approved T.C. 02-14-02				A	4600-050			
																REVISION RECORD Original Release C.O. 6769 METRIC DIMS & NOTES ADDED. E.C. 7-17-92 6789 WVDC REVISED 100 & 70 WERE 80 & 50. L.E. 10-26-92 6992 RDN TO COMP FMT. S.M. 02-14-02 20020213-4-03 WORKING VOLTAGE REV'D 100, 70 WERE 80, 50 & TEMP. CHARAC. ADDED 20020903-1-02 ADDED NOTE S 1 & 3. REVISED NOTE 2. S.M. 06-24-05 20050608-2-02						--TOLERANCES-- Unless Otherwise Specified		Title COAXIAL BROADBAND - "C"																
																		DECIMAL ±																						
																		ANGLES ±		Drawn S.M. 02-14-02		Scale 2 X																		
														TUSONIX TUCSON, ARIZONA				Approved T.C. 02-14-02																						
A	4600-050																																							