

1 : STANDARD PRODUCT
W/ BOX PACKING

```
02: 2 POLES
03: 3 POLES
04: 4 POLES
|
|
24: 24 POLES
```

CODE	SCREW TYPE		AVAILABILITY
A	-/+		ON REQUEST ONLY
B	-		STANDARD

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

NOTES:

MATERIALS

1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.

1-2 SCREW: STEEL, ZINC PLATED.

1-3 CLAMP: COPPER ALLOY, NICKEL PLATED.

1-4 TERMINAL: COPPER ALLOY, TIN PLATED.

2. PRODUCTION SPECIFICATION REFER TO FCI GS-12-625.

3. BOXED PACKAGING.



DETAILED PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.

4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.

5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



[illegible]

PRODUCT NUMBER	SERIES NAME	PITCH
20020006-GXXXXXL	01-500	5.00 mm




N= NUMBER OF POLES
DIMENSION

Dim L	$N \times 5.0 [.197]$
Bim B	$(N-1) \times 5.0 [.197]$
Dim C	$N \times 5.0 [.197] + 0.10 [.004]$







SECTION P-P

Poles	Tolerance
2P-5P	$\pm 0.15 [.006]$
6P-10P	$\pm 0.20 [.008]$
11P-15P	$\pm 0.25 [.010]$
16P-20P	$\pm 0.30 [.012]$
21P-24P	$\pm 0.40 [.016]$




mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
H				angles	$X \pm 0.5 [.020]$ $X.X \pm 0.3 [.012]$ $X \pm 1$	scale	TERMINAL BLOCK PLUGGABLE PLUG, CONTACT UP SIDE
				dr	BEER FU 062509		dwg no
				enr	BEER FU 062509		sheet 2 of 3 size
				chr	GARY HSIEH 062509		20020006 A4
				appd	JOSEPH HSIA 062509		type
sheet index	revision sheet						CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020006-HXXXXXXLF	01-508	5.08 mm



SECTION P-P



N= NUMBER OF POLES
DIMENSION

Dim L	$N \times 5.08 [.200]$
Bim B	$(N-1) \times 5.08 [.200]$
Dim C	$N \times 5.08 [.200] + 0.10 [.004]$

Poles	Tolerance
2P–5P	$\pm 0.15[.006]$
6P–10P	$\pm 0.20[.008]$
11P–15P	$\pm 0.25[.010]$
16P–20P	$\pm 0.30[.012]$
21P–24P	$\pm 0.40[.016]$

mat'l. code				surface ASME Y14.5				tolerance ASME Y14.5				projection 				product family TERMINAL BLOCK															
ltr ecn no dr date				tolerances unless otherwise specified																				title							
H																MM  [INCH]				TERMINAL BLOCK											
								angles				lineal								PLUGGABLE PLUG, CONTACT UP SIDE											
								X.±0.5[.020]																							
								X.X±0.3[.012]																							
								X*±1*				X.XX±0.1[.004]				scale															
								dr BEER FU 062509												dwg no sheet 3 of 3 size											
								enr BEER FU 062509												20020006 A4											
								chr GARY HSIEH 062509																							
								appd JOSEPH HSIA 062509												type CUSTOMER Drawing											
sheet index				revision sheet																											