


MATERIALS AND FINISHES

BODY, JAM NUT, FLAT WASHER: BRASS
PLATED: GOLD




CENTER CONTACT: BeCu
PLATED: GOLD

INSULATOR: TEFLON


LOCKWASHER: PHOSPHOR BRONZE
PLATED: GOLD





RECOMMENDED PANEL CUTOUT




JAM NUT FOR
73251-2121 & -2122



LOCK WASHER FOR
73251-2121 ONLY





FLAT WASHER FOR
73251-2122 ONLY



RECOMMENDED PAD LAYOUT

BASE WIDTH: 6.35(.250) NOM.
BOARD THICKNESS: 1.57(.062) NOM.
BOARD MATERIAL: FR4 W/1.0 OZ COPPER
BOTH SIDES



73251-2123	ONE PIECE -2120 WITHOUT HARDWARE PER BAG	
73251-2122	-2120 W/JAM NUT & FLAT WASHER / TRAY PACKING	
73251-2121	-2120 W/JAM NUT & LOCK WASHER / TRAY PACKING	
73251-2120	-2120 WITHOUT HARDWARE / TRAY PACKING	
PART NO.	DESCRIPTION	
PS-89675-3460	PRODUCT SPECIFICATION	
MIL-STD-348A, FIG. 310.2	INTERFACE	
SPECIFICATION	DESCRIPTION	

CHG: REGENERATED DWG & ADDED TOLERANCE PER RF13-E072
EC NO: URF2013-0355
2012/12/12
CHKD: DRWINRYEH
APPR: MHIANG
REV A5

REV	DESCRIPTION
1	QUALITY SYMBOLS
2	QUALITY SYMBOLS
3	QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005
0 PLACE	± .005	± .0005
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM/IN	DATE
DRAWN BY SSS	2003/07/09
CHECKED BY TEF	2003/07/09
APPROVED BY JWIENER	2010/10/27
MATERIAL NO.	
SEE TABLE	
SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
7:1	METRIC	
SMA JACK, EDGE MOUNT .062 BOARD, 50 OHMS, EWR-2074 SMA-J/PCB		
molex		
DOCUMENT NO. SD-73251-212		SHEET NO. 1 OF 1

MATERIALS AND FINISHES





BODY: BRASS
PLATED: NICKEL

CENTER CONTACT: BERYLLIUM COPPER
PLATED: GOLD



INSULATOR: PTFE



SMA JACK
INTERFACE



RECOMMENDED PANEL CUTOUT



PART # 73251-9340

PS-89675-3460	PRODUCT SPECIFICATION
MIL-STD-348A, FIG. 310.2	INTERFACE
SPECIFICATION	DESCRIPTION

RECOMMENDED PAD LAYOUT:
BASE WIDTH: 6.35(.250) NOM.
BOARD THICKNESS: 1.57(.062) NOM.
BOARD MATERIAL: FR4 W/1.0 OZ COPPER
BOTH SIDES

CHG: NEW RELEASE	EC NO: URF2014-0585 DRWN: JLEE02 CHKD: SSS APPR: WSPINK	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
						MM/IN		INCH				
				▽=0	4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE		
				▽=0	3 PLACES	± ---	± ---	AROBERTSON	2014/04/08			
				▽=0	2 PLACES	± ---	± ---	CHECKED BY	DATE			
					1 PLACE	± ---	± ---	2014/04/08	SSS	SMA JACK BK RM EDGE LAUNCH .062" PCB SMA-J/BK/PCB, EWR-5375		
					0 PLACE	± ---	± ---	APPROVED BY	DATE			
								WSPINK	2014/04/14			
					ANGULAR ± 2 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
					DRAFT WHERE APPLICABLE		SEE TABLE		SD-73251-934		1 OF 1	
	MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73251-2120](#)