




REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
A	PRODUCT DRAWING (EAR 12956)	OCT03/06	K.L.

ORDERING CODE:

PART
NUMBER: 1 7 E H D - 0 2 6 P A M - 1 0 0

SERIES

NUMBER OF CONTACTS
026

STYLE

P=PIN
S=SOCKET

TERMINATION-MOUNTING OPTIONS

000= SOLDER CUP, .120 [3.05] DIA.
THROUGH HOLE
100= SOLDER CUP, #4-40 UNC
THREADED HOLES
200= SOLDER CUP, #4-40 UNC HEX
JACK SOCKETS INSTALLED

CONTACT PLATING OPTIONS
FOR ENGAGEMENT AREA

AA= 3μ" [0.08 MICRONS] GOLD FLASH
CH= 15μ" [0.38 MICRONS] GOLD
AM= 30μ" [0.76 MICRONS] GOLD

SPECIFICATIONS:

MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT

SHELL: STEEL, TIN PLATED

INSERTS: HIGH TEMPERATURE RESISTANT NYLON, GLASS
REINFORCED, UL FLAMMABILITY RATING
94V-0, COLOUR: BLACK

CONTACTS: COPPER ALLOY, GOLD PLATING (SEE ORDERING CODE) OVER
50μ" [1.27 MICRONS] NICKEL ON ENGAGEMENT AREA WITH
100μ" [2.54 MICRONS] MIN. MATTE TIN ON CONTACT
TERMINALS.

ELECTRICAL DATA:

CURRENT RATING: 3 AMP
CONTACT RESISTANCE: 15 MILLIOHMS MAX.
INSULATION RESISTANCE: 3000 MEGOHMS MIN.
DIELECTRIC
WITHSTANDING VOLTAGE: 1000 VAC rms
OPERATING TEMPERATURE: -55°C TO +105°C

DRAWN	J.LEE	DATE	OCT03/06	Amphenol Canada Corp.			
DESIGNED							
CHECKED	K.LAMBIE	OCT03/06					
I. E. APPRD.							
Q. A. APPRD.							
DWG. APPRD.							
ENG. REL. NO.							
REF.	EAR 12956						
DIMENSIONS ARE IN	INCHES	CODE ID. NO.	03554	DWG	DRAWING NO.	REV.	
				C	P-17EHD-026XXX-X00	A	
				SCALE	2/1	WT.	
						SURF.	
							SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[17EHD026PAA100](#) [17EHD026PAA200](#) [17EHD026PAM000](#) [17EHD026PAM100](#) [17EHD026PAM200](#)
[17EHD026SAA100](#) [17EHD026SAA200](#) [17EHD026SAM000](#) [17EHD026SAM100](#) [17EHD026SAM200](#) [17EHD-026P-AA000](#) [17EHD-026S-AA000](#)