



## Frequency Generator with 200MHz Differential CPU Clocks

### Recommended Application:

CK-408 clock for BANIAS processor/ ODEM and MONTARA-G chipsets.

### Output Features:

- 3 0.7V Differential CPU Clock Pairs
- 7 PCI (3.3V) @ 33.3MHz
- 3 PCI\_F (3.3V) @ 33.3MHz
- 1 USB (3.3V) @ 48MHz
- 1 DOT (3.3V) @ 48MHz
- 1 REF (3.3V) @ 14.318MHz
- 5 3V66 (3.3V) @ 66.6MHz
- 1 VCH/3V66 (3.3V) @ 48MHz or 66.6MHz

### Features:

- Supports spread spectrum modulation, down spread 0 to -0.5%. (CPU, 3V66, PCI)
- Efficient power management scheme through PD#, CPU\_STOP# and PCI\_STOP#.

### Key Specifications:

- CPU Output Jitter <150ps
- 3V66 Output Jitter <250ps
- CPU Output Skew <100ps

### Pin Configuration


|            |    |    |                |
|------------|----|----|----------------|
| VDDREF     | 1  | 56 | REF            |
| X1         | 2  | 55 | FS1            |
| X2         | 3  | 54 | FS0            |
| GND        | 4  | 53 | CPU_STOP#*     |
| PCICLK_F0  | 5  | 52 | CPUCLKT0       |
| PCICLK_F1  | 6  | 51 | CPUCLKC0       |
| PCICLK_F2  | 7  | 50 | VDDCPU         |
| VDDPCI     | 8  | 49 | CPUCLKT1       |
| GND        | 9  | 48 | CPUCLKC1       |
| PCICLK0    | 10 | 47 | GND            |
| PCICLK1    | 11 | 46 | VDDCPU         |
| PCICLK2    | 12 | 45 | CPUCLKT2       |
| PCICLK3    | 13 | 44 | CPUCLKC2       |
| VDDPCI     | 14 | 43 | MULTSELO*      |
| GND        | 15 | 42 | IREF           |
| PCICLK4    | 16 | 41 | GND            |
| PCICLK5    | 17 | 40 | FS2            |
| PCICLK6    | 18 | 39 | 48MHz_USB      |
| VDD3V66    | 19 | 38 | 48MHz_DOT      |
| GND        | 20 | 37 | VDD48          |
| 3V66_2     | 21 | 36 | GND            |
| 3V66_3     | 22 | 35 | 3V66_1/VCH_CLK |
| 3V66_4     | 23 | 34 | PCI_STOP#*     |
| 3V66_5     | 24 | 33 | 3V66_0         |
| *PD#       | 25 | 32 | VDD3V66        |
| VDDA       | 26 | 31 | GND            |
| GND        | 27 | 30 | SCLK           |
| Vtt_PWRGD# | 28 | 29 | SDATA          |

56-Pin 300mil SSOP

6.10 mm. Body, 0.50 mm. pitch TSSOP

\* These inputs have 150K internal pull-up resistor to VDD.

### Block Diagram



### Functionality

| FS2 | FS1 | FS0 | CPU (MHz) | 3V66(5:0) (MHz) | PCI_F PCI (MHz) |
|-----|-----|-----|-----------|-----------------|-----------------|
| X   | 0   | 0   | 166.66    | 66.66           | 33.33           |
| X   | 0   | 1   | 100.00    | 66.66           | 33.33           |
| X   | 1   | 0   | 200.00    | 66.66           | 33.33           |
| X   | 1   | 1   | 133.33    | 66.66           | 33.33           |
| Mid | 0   | 0   | Tristate  | Tristate        | Tristate        |
| Mid | 0   | 1   | TCLK/2    | TCLK/4          | TCLK/8          |
| Mid | 1   | 0   | Reserved  | Reserved        | Reserved        |
| Mid | 1   | 1   | Reserved  | Reserved        | Reserved        |



## Pin Configuration

| PIN NUMBER | PIN NAME  | TYPE | DESCRIPTION                                                                                                                                                                                                                   |
|------------|-----------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1          | VDDREF    | PWR  | Ref, XTAL power supply, nominal 3.3V                                                                                                                                                                                          |
| 2          | X1        | IN   | Crystal input, nominally 14.318MHz.                                                                                                                                                                                           |
| 3          | X2        | OUT  | Crystal output, nominally 14.318MHz.                                                                                                                                                                                          |
| 4          | GND       | PWR  | Ground pin for 3V outputs.                                                                                                                                                                                                    |
| 5          | PCICLK_F0 | OUT  | Free running PCI clock not affected by PCI_STOP# .                                                                                                                                                                            |
| 6          | PCICLK_F1 | OUT  | Free running PCI clock not affected by PCI_STOP# .                                                                                                                                                                            |
| 7          | PCICLK_F2 | OUT  | Free running PCI clock not affected by PCI_STOP# .                                                                                                                                                                            |
| 8          | VDDPCI    | PWR  | Power supply for PCICLK_F and PCICLK, nominal 3.3V                                                                                                                                                                            |
| 9          | GND       | PWR  | Ground pin for 3V outputs.                                                                                                                                                                                                    |
| 10         | PCICLK0   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 11         | PCICLK1   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 12         | PCICLK2   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 13         | PCICLK3   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 14         | VDDPCI    | PWR  | Power supply for PCICLK_F and PCICLK, nominal 3.3V                                                                                                                                                                            |
| 15         | GND       | PWR  | Ground pin for 3V outputs.                                                                                                                                                                                                    |
| 16         | PCICLK4   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 17         | PCICLK5   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 18         | PCICLK6   | OUT  | PCI clock outputs.                                                                                                                                                                                                            |
| 19         | VDD3V66   | PWR  | Power pin for the 3V66 clocks.                                                                                                                                                                                                |
| 20         | GND       | PWR  | Ground pin for 3V outputs.                                                                                                                                                                                                    |
| 21         | 3V66_2    | OUT  | 66MHz outputs at 3.3V.                                                                                                                                                                                                        |
| 22         | 3V66_3    | OUT  | 66MHz outputs at 3.3V.                                                                                                                                                                                                        |
| 23         | 3V66_4    | OUT  | 66MHz outputs at 3.3V.                                                                                                                                                                                                        |
| 24         | 3V66_5    | OUT  | 66MHz input/output at 3.3V.                                                                                                                                                                                                   |
| 25         | PD#       | IN   | Asynchronous active low input pin used to power down the device into a low power state. The internal clocks are disabled and the VCO and the crystal are stopped. The latency of the power down will not be greater than 3ms. |
| 26         | VDDA      | PWR  | 3.3V power for the PLL core.                                                                                                                                                                                                  |
| 27         | GND       | PWR  | Ground pin for 3V outputs.                                                                                                                                                                                                    |

**Pin Configuration (Continued)**

| PIN NUMBER | PIN NAME       | TYPE | DESCRIPTION                                                                                                                                                                 |
|------------|----------------|------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 28         | Vtt_PWRGD#     | IN   | This 3.3V LVTTTL input is a level sensitive strobe used to determine when FS[2:0] and MULTISEL0 inputs are valid and are ready to be sampled. (active low)                  |
| 29         | SDATA          | I/O  | Data pin for I2C circuitry 5V tolerant                                                                                                                                      |
| 30         | SCLK           | IN   | Clock pin of I2C circuitry 5V tolerant                                                                                                                                      |
| 31         | GND            | PWR  | Ground pin for 3V outputs.                                                                                                                                                  |
| 32         | VDD3V66        | PWR  | Power pin for the 3V66 clocks.                                                                                                                                              |
| 33         | 3V66_0         | OUT  | 66MHz outputs at 3.3V.                                                                                                                                                      |
| 34         | PCI_STOP#      | IN   | Stops all PCICLKs besides the PCICLK_F clocks at logic 0 level, when input low                                                                                              |
| 35         | 3V66_1/VCH_CLK | OUT  | Selectable 48MHz non-SSC or 66MHz SSC clock output                                                                                                                          |
| 36         | GND            | PWR  | Ground pin for 3V outputs.                                                                                                                                                  |
| 37         | VDD48          | PWR  | Power for 48MHz output buffers and fixed PLL core.                                                                                                                          |
| 38         | 48MHz_DOT      | OUT  | 48MHz output clock                                                                                                                                                          |
| 39         | 48MHz_USB      | OUT  | 48MHz output clock                                                                                                                                                          |
| 40         | FS2            | IN   | Frequency select pin.                                                                                                                                                       |
| 41         | GND            | PWR  | Ground pin for 3V outputs.                                                                                                                                                  |
| 42         | IREF           | OUT  | This pin establishes the reference current for the CPUCLK pairs. This pin requires a fixed precision resistor tied to ground in order to establish the appropriate current. |
| 43         | MULTSEL0       | IN   | 3.3V LVTTTL input for selection the current multiplier for CPU outputs                                                                                                      |
| 44         | CPUCLKC2       | OUT  | "Complementary" clocks of differential pair CPU outputs. These are current mode outputs. External resistors are required for voltage bias.                                  |
| 45         | CPUCLKT2       | OUT  | "True" clocks of differential pair CPU outputs. These are current mode outputs. External resistors are required for voltage bias.                                           |
| 46         | VDDCPU         | PWR  | Supply for CPU clocks, 3.3V nominal                                                                                                                                         |
| 47         | GND            | PWR  | Ground pin for 3V outputs.                                                                                                                                                  |
| 48         | CPUCLKC1       | OUT  | "Complementary" clocks of differential pair CPU outputs. These are current mode outputs. External resistors are required for voltage bias.                                  |
| 49         | CPUCLKT1       | OUT  | "True" clocks of differential pair CPU outputs. These are current mode outputs. External resistors are required for voltage bias.                                           |
| 50         | VDDCPU         | PWR  | Supply for CPU clocks, 3.3V nominal                                                                                                                                         |
| 51         | CPUCLKC0       | OUT  | "Complementary" clocks of differential pair CPU outputs. These are current mode outputs. External resistors are required for voltage bias.                                  |
| 52         | CPUCLKT0       | OUT  | "True" clocks of differential pair CPU outputs. These are current mode outputs. External resistors are required for voltage bias.                                           |
| 53         | CPU_STOP#      | IN   | This asynchronous input halts to active low level when driven low.                                                                                                          |
| 54         | FS0            | IN   | Frequency select pin.                                                                                                                                                       |
| 55         | FS1            | IN   | Frequency select pin.                                                                                                                                                       |
| 56         | REF            | OUT  | 14.318 MHz reference clock.                                                                                                                                                 |



## Power Groups

### (Analog)

VDDA = PLL1

VDD48 = 48MHz, PLL

VDDREF = VDD for Xtal, POR

### (Digital)

VDDPCI

VDD3V66

VDDCPU

## Truth Table

| FS2 | FS1 | FS0 | CPU<br>(MHz) | 3V66<br>(5:0)<br>(MHz) | PCI_F<br>PCI<br>(MHz) | REF0<br>(MHz) | USB/DOT<br>(MHz) |
|-----|-----|-----|--------------|------------------------|-----------------------|---------------|------------------|
| X   | 0   | 0   | 166.66       | 66.66                  | 33.33                 | 14.318        | 48.00            |
| X   | 0   | 1   | 100.00       | 66.66                  | 33.33                 | 14.318        | 48.00            |
| X   | 1   | 0   | 200.00       | 66.66                  | 33.33                 | 14.318        | 48.00            |
| X   | 1   | 1   | 133.33       | 66.66                  | 33.33                 | 14.318        | 48.00            |
| Mid | 0   | 0   | Tristate     | Tristate               | Tristate              | Tristate      | Tristate         |
| Mid | 0   | 1   | TCLK/2       | TCLK/4                 | TCLK/8                | TCLK          | TCLK/2           |
| Mid | 1   | 0   | Reserved     | Reserved               | Reserved              | Reserved      | Reserved         |
| Mid | 1   | 1   | Reserved     | Reserved               | Reserved              | Reserved      | Reserved         |

## Maximum Allowed Current

|                                        |                                                                                                          |
|----------------------------------------|----------------------------------------------------------------------------------------------------------|
| <b>Condition</b>                       | Max 3.3V supply consumption<br>Max discrete cap loads,<br>Vdd = 3.465V<br>All static inputs = Vdd or GND |
| <b>Powerdown Mode</b><br>(PWRDWN# = 0) | 25mA                                                                                                     |
| <b>Full Active</b>                     | 360mA                                                                                                    |

## Host Swing Select Functions

| MULTISEL0 | Board Target<br>Trace/Term Z | Reference R,<br>Iref =<br>$V_{DD}/(3 \cdot R_r)$ | Output<br>Current | Voh @ Z   |
|-----------|------------------------------|--------------------------------------------------|-------------------|-----------|
| 0         | -                            | -                                                | -                 | -         |
| 1         | 50 ohms                      | Rr = 475 1%,<br>Iref = 2.32mA                    | Ioh = 6 * I REF   | 0.7V @ 50 |

NOTE: MULTSEL0 = 0 not supported in ICS950810. Refer to ICS950805 for Buffered Mode support.



## Power Management

| PD# | CPU_STOP# | PCI_STOP# | VCO  | CPU    | CPU#  | PCICLK | 3v66 | 48MHz | REF |
|-----|-----------|-----------|------|--------|-------|--------|------|-------|-----|
| 0   | X         | X         | STOP | Iref*2 | FLOAT | LOW    | LOW  | LOW   | LOW |
| 1   | 1         | 1         | RUN  | RUN    | RUN   | RUN    | RUN  | RUN   | RUN |
| 1   | 0         | 1         | RUN  | Iref*2 | FLOAT | RUN    | RUN  | RUN   | RUN |
| 1   | 1         | 0         | RUN  | RUN    | RUN   | LOW    | RUN  | RUN   | RUN |
| 1   | 1         | 1         | RUN  | RUN    | RUN   | RUN    | RUN  | RUN   | RUN |

Note: PCI\_F is not affected by PCI\_STOP# and CPU\_STOP#

## Tri-State Control of CPU Outputs

| State | Byte0 bit6<br>PD# | Byte1 bit6<br>Cpu_stop# | Pin<br>PD# | Pin<br>Cpu_Stop# | Stoppable<br>CPU outputs | Free-Running<br>CPU outputs |
|-------|-------------------|-------------------------|------------|------------------|--------------------------|-----------------------------|
| 0     | 0                 | 0                       | 1          | 1                | Running                  | Running                     |
| 1     | 0                 | 0                       | 1          | 0                | Irefx6                   | Running                     |
| 2     | 0                 | 0                       | 0          | 1                | Irefx2                   | Irefx2                      |
| 3     | 0                 | 0                       | 0          | 0                | Irefx2                   | Irefx2                      |
| 4     | 0                 | 1                       | 1          | 1                | Running                  | Running                     |
| 5     | 0                 | 1                       | 1          | 0                | Hi-Z                     | Running                     |
| 6     | 0                 | 1                       | 0          | 1                | Hi-Z                     | Irefx2                      |
| 7     | 0                 | 1                       | 0          | 0                | Hi-Z                     | Irefx2                      |
| 8     | 1                 | 0                       | 1          | 1                | Running                  | Running                     |
| 9     | 1                 | 0                       | 1          | 0                | Irefx6                   | Running                     |
| 10    | 1                 | 0                       | 0          | 1                | Hi-Z                     | Hi-Z                        |
| 11    | 1                 | 0                       | 0          | 0                | Hi-Z                     | Hi-Z                        |
| 12    | 1                 | 1                       | 1          | 1                | Running                  | Running                     |
| 13    | 1                 | 1                       | 1          | 0                | Hi-Z                     | Running                     |
| 14    | 1                 | 1                       | 0          | 1                | Hi-Z                     | Hi-Z                        |
| 15    | 1                 | 1                       | 0          | 0                | Hi-Z                     | Hi-Z                        |



## Absolute Maximum Ratings

|                               |                                |
|-------------------------------|--------------------------------|
| Supply Voltage                | 5.5 V                          |
| Logic Inputs                  | GND –0.5 V to $V_{DD} + 0.5$ V |
| Ambient Operating Temperature | 0°C to +85°C                   |
| Case Temperature              | 115°C                          |
| Storage Temperature           | –65°C to +150°C                |

Stresses above those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These ratings are stress specifications only and functional operation of the device at these or any other conditions above those listed in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect product reliability.

## Electrical Characteristics - Input/Supply/Common Output Parameters

$T_A = 0 - 70^\circ\text{C}$ ; Supply Voltage  $V_{DD} = 3.3$  V  $\pm 5\%$

| PARAMETER                        | SYMBOL             | CONDITIONS                                             | MIN            | TYP    | MAX            | UNITS         |
|----------------------------------|--------------------|--------------------------------------------------------|----------------|--------|----------------|---------------|
| Input High Voltage               | $V_{IH}$           |                                                        | 2              |        | $V_{DD} + 0.3$ | V             |
| Input Low Voltage                | $V_{IL}$           |                                                        | $V_{SS} - 0.3$ |        | 0.8            | V             |
| Input High Current               | $I_{IH}$           | $V_{IN} = V_{DD}$                                      | -5             |        | 5              | $\mu\text{A}$ |
| Input Low Current                | $I_{IL1}$          | $V_{IN} = 0$ V; Inputs with no pull-up resistors       | -5             |        |                |               |
|                                  | $I_{IL2}$          | $V_{IN} = 0$ V; Inputs with pull-up resistors          | -200           |        |                |               |
| Operating Supply Current         | $I_{DD3.3OP}$      | $C_L = \text{Full load}$ ; Select @ 100 MHz            | 229            | 230    | 360            | mA            |
|                                  | $I_{DD3.3OP}$      | $C_L = \text{Full load}$ ; Select @ 133 MHz            | 220            | 233    | 360            | mA            |
| Powerdown Current                | $I_{DD3.3PD}$      | $I_{REF} = 2.32$ mA                                    |                | 22     | 25             | mA            |
| Input Frequency                  | $F_I$              | $V_{DD} = 3.3$ V                                       |                | 14.318 |                | MHz           |
| Pin Inductance                   | $L_{pin}$          |                                                        |                |        | 7              | nH            |
| Input Capacitance <sup>1</sup>   | $C_{IN}$           | Logic Inputs                                           |                |        | 5              | pF            |
|                                  | $C_{OUT}$          | Output pin capacitance                                 |                |        | 6              | pF            |
|                                  | $C_{INX}$          | X1 & X2 pins                                           | 27             | 30     | 45             | pF            |
| Clk Stabilization <sup>1,2</sup> | $T_{STAB}$         | From PowerUp or deassertion of PowerDown to 1st clock. |                | 1      | 1.8            | ms            |
| Delay <sup>1</sup>               | $t_{PZH}, t_{PZL}$ | Output enable delay (all outputs)                      | 1              |        | 10             | ns            |
|                                  | $t_{PHZ}, t_{PLZ}$ | Output disable delay (all outputs)                     | 1              |        | 10             | ns            |

<sup>1</sup>Guaranteed by design, not 100% tested in production.

<sup>2</sup>See timing diagrams for buffered and un-buffered timing requirements.

**Electrical Characteristics - CPU (0.7V Select)**

$T_A = 0 - 70^\circ\text{C}$ ;  $V_{DD}=3.3\text{V} \pm 5\%$ ;  $C_L = 10\text{-}20\text{ pF}$  (unless otherwise specified)

| PARAMETER                       | SYMBOL                  | CONDITIONS                                               | MIN  | TYP | MAX  | UNITS    |
|---------------------------------|-------------------------|----------------------------------------------------------|------|-----|------|----------|
| Current Source Output Impedance | $Z_{O1}$                | $V_O = V_x$                                              | 3000 |     |      | $\Omega$ |
| Voltage High                    | VHigh                   | Statistical measurement on single ended signal using     | 660  | 810 | 850  | mV       |
| Voltage Low                     | VLow                    |                                                          | -150 | 20  | 150  |          |
| Max Voltage                     | Vovs                    | Measurement on single ended signal using absolute value. |      | 850 | 1150 | mV       |
| Min Voltage                     | Vuds                    |                                                          | -450 | -15 |      |          |
| Crossing Voltage (abs)          | Vcross(abs)             |                                                          | 250  | 380 | 550  | mV       |
| Crossing Voltage (var)          | d-Vcross                | Variation of crossing over all edges                     |      | 22  | 140  | mV       |
| Rise Time                       | $t_r$                   | $V_{OL} = 0.175\text{V}$ , $V_{OH} = 0.525\text{V}$      | 175  | 290 | 700  | ps       |
| Fall Time                       | $t_f$                   | $V_{OH} = 0.525\text{V}$ $V_{OL} = 0.175\text{V}$        | 175  | 310 | 700  | ps       |
| Rise Time Variation             | d- $t_r$                |                                                          |      | 10  | 125  | ps       |
| Fall Time Variation             | d- $t_f$                |                                                          |      | 10  | 125  | ps       |
| Duty Cycle                      | $d_{t3}$                | Measurement from differential waveform                   | 45   | 51  | 55   | %        |
| Skew                            | $t_{sk3}$               | $V_T = 50\%$                                             |      | 16  | 100  | ps       |
| Jitter, Cycle to cycle          | $t_{j\text{cyc-cyc}}^1$ | $V_T = 50\%$                                             |      | 48  | 150  | ps       |

<sup>1</sup>Guaranteed by design, not 100% tested in production.

<sup>2</sup>  $I_{OVT}$  can be varied and is selectable thru the MULTSEL pin.

**Electrical Characteristics - PCICLK**

$T_A = 0 - 70^\circ\text{C}$ ;  $V_{DD}=3.3\text{V} \pm 5\%$ ;  $C_L = 10\text{-}30\text{ pF}$  (unless otherwise specified)

| PARAMETER            | SYMBOL                  | CONDITIONS                                        | MIN | TYP  | MAX  | UNITS |
|----------------------|-------------------------|---------------------------------------------------|-----|------|------|-------|
| Output Impedance     | $R_{DSP1}^1$            | $V_O = V_{DD}*(0.5)$                              | 12  | 33   | 55   | W     |
| Output High Voltage  | $V_{OH}^1$              | $I_{OH} = -1\text{ mA}$                           | 2.4 | 3.28 |      | V     |
| Output Low Voltage   | $V_{OL}^1$              | $I_{OL} = 1\text{ mA}$                            |     | 0.08 | 0.55 | V     |
| Output High Current  | $I_{OH}^1$              | $V_{OH@MIN} = 1.0\text{ V}$                       | -33 | -110 |      |       |
|                      |                         | $V_{OH@MAX} = 3.135\text{ V}$                     |     | -20  | -33  | mA    |
| Output Low Current   | $I_{OL}^1$              | $V_{OL@MIN} = 1.95\text{ V}$                      | 30  | 110  |      |       |
|                      |                         | $V_{OL@MAX} = 0.4\text{ V}$                       |     | 37   | 38   | mA    |
| Rise Time            | $t_{r1}^1$              | $V_{OL} = 0.4\text{ V}$ , $V_{OH} = 2.4\text{ V}$ | 0.5 | 1.28 | 2    | ns    |
| Fall Time            | $t_{f1}^1$              | $V_{OH} = 2.4\text{ V}$ , $V_{OL} = 0.4\text{ V}$ | 0.5 | 1.37 | 2    | ns    |
| Duty Cycle           | $d_{t1}^1$              | $V_T = 1.5\text{ V}$                              | 45  | 51.1 | 55   | %     |
| Skew                 | $t_{sk1}^1$             | $V_T = 1.5\text{ V}$                              |     | 127  | 500  | ps    |
| Jitter, cycle to cyc | $t_{j\text{cyc-cyc}}^1$ | $V_T = 1.5\text{ V}$                              |     | 164  | 250  | ps    |

<sup>1</sup>Guaranteed by design, not 100% tested in production.



### Electrical Characteristics - 3V66 Mode: 3V66 [5:0]

$T_A = 0 - 70^\circ\text{C}$ ;  $V_{DD} = 3.3\text{V} \pm 5\%$ ;  $C_L = 10\text{-}30\text{ pF}$  (unless otherwise specified)

| PARAMETER           | SYMBOL          | CONDITIONS                                     | MIN | TYP  | MAX  | UNITS    |
|---------------------|-----------------|------------------------------------------------|-----|------|------|----------|
| Output Impedance    | $R_{DSP1}^1$    | $V_O = V_{DD} \cdot (0.5)$                     | 12  | 33   | 55   | $\Omega$ |
| Output High Voltage | $V_{OH}^1$      | $I_{OH} = -1\text{ mA}$                        | 2.4 | 3.28 |      | V        |
| Output Low Voltage  | $V_{OL}^1$      | $I_{OL} = 1\text{ mA}$                         |     | 0.08 | 0.55 | V        |
| Output High Current | $I_{OH}^1$      | $V_{OH@MIN} = 1.0\text{ V}$                    | -33 | -110 |      |          |
|                     |                 | $V_{OH@MAX} = 3.135\text{ V}$                  |     | -20  | -33  | mA       |
| Output Low Current  | $I_{OL}^1$      | $V_{OL@MIN} = 1.95\text{ V}$                   | 30  | 110  |      |          |
|                     |                 | $V_{OL@MAX} = 0.4\text{ V}$                    |     | 37   | 38   | mA       |
| Rise Time           | $t_{r1}^1$      | $V_{OL} = 0.4\text{ V}, V_{OH} = 2.4\text{ V}$ | 0.5 | 1.15 | 2    | ns       |
| Fall Time           | $t_{f1}^1$      | $V_{OH} = 2.4\text{ V}, V_{OL} = 0.4\text{ V}$ | 0.5 | 1.53 | 2    | ns       |
| Duty Cycle          | $d_{t1}^1$      | $V_T = 1.5\text{ V}$                           | 45  | 51.3 | 55   | %        |
| Skew                | $t_{sk1}^1$     | $V_T = 1.5\text{ V}$                           |     | 67   | 250  | ps       |
| Jitter              | $t_{jvc-cyc}^1$ | $V_T = 1.5\text{ V}$ 3V66                      |     | 175  | 250  | ps       |

<sup>1</sup>Guaranteed by design, not 100% tested in production.

### Electrical Characteristics - VCH, 48MHz DOT, 48MHz, USB

$T_A = 0 - 70^\circ\text{C}$ ;  $V_{DD} = 3.3\text{V} \pm 5\%$ ;  $C_L = 10\text{-}20\text{ pF}$  (unless otherwise specified)

| PARAMETER             | SYMBOL          | CONDITIONS                                     | MIN | TYP  | MAX | UNITS    |
|-----------------------|-----------------|------------------------------------------------|-----|------|-----|----------|
| Output Impedance      | $R_{DSP1}^1$    | $V_O = V_{DD} \cdot (0.5)$                     | 20  | 48   | 60  | $\Omega$ |
| Output High Voltage   | $V_{OH}^1$      | $I_{OH} = -1\text{ mA}$                        | 2.4 | 3.27 |     | V        |
| Output Low Voltage    | $V_{OL}^1$      | $I_{OL} = 1\text{ mA}$                         |     | 0.08 | 0.4 | V        |
| Output High Current   | $I_{OH}^1$      | $V_{OH@MIN} = 1.0\text{ V}$                    | -29 | -61  |     |          |
|                       |                 | $V_{OH@MAX} = 3.135\text{ V}$                  |     | -12  | -23 | mA       |
| Output Low Current    | $I_{OL}^1$      | $V_{OL@MIN} = 1.95\text{ V}$                   | 29  |      |     |          |
|                       |                 | $V_{OL@MAX} = 0.4\text{ V}$                    |     |      | 27  | mA       |
| 48DOT Rise Time       | $t_{r1}^1$      | $V_{OL} = 0.4\text{ V}, V_{OH} = 2.4\text{ V}$ | 0.5 | 0.69 | 1   | ns       |
| 48DOT Fall Time       | $t_{f1}^1$      | $V_{OH} = 2.4\text{ V}, V_{OL} = 0.4\text{ V}$ | 0.5 | 0.81 | 1   | ns       |
| VCH 48 USB Rise Time  | $t_{r1}^1$      | $V_{OL} = 0.4\text{ V}, V_{OH} = 2.4\text{ V}$ | 1   | 1.37 | 2   | ns       |
| VCH 48 USB Fall Time  | $t_{f1}^1$      | $V_{OH} = 2.4\text{ V}, V_{OL} = 0.4\text{ V}$ | 1   | 1.47 | 2   | ns       |
| 48 DOT Duty Cycle     | $d_{t1}^1$      | $V_T = 1.5\text{ V}$                           | 45  | 51.2 | 55  | %        |
| VCH 48 USB Duty Cycle | $d_{t1}^1$      | $V_T = 1.5\text{ V}$                           | 45  | 53.5 | 55  | %        |
| 48 DOT Jitter         | $t_{jvc-cyc}^1$ | $V_T = 1.5\text{ V}$                           |     | 111  | 350 | ps       |
| 48 USB Jitter         | $t_{jvc-cyc}^1$ | $V_T = 1.5\text{ V}$                           |     | 99   | 350 | ps       |
| USB to DOT Skew       | $t_{sk1}^1$     | $V_T = 1.5\text{ V}$ (0 OR 180 degrees)        |     |      | 1   | ns       |
| VCH Jitter            | $t_{jvc-cyc}^1$ | $V_T = 1.5\text{ V}$                           |     | 147  | 350 | ps       |

<sup>1</sup>Guaranteed by design, not 100% tested in production.

**Electrical Characteristics - REF** $T_A = 0 - 70^\circ\text{C}$ ;  $V_{DD} = 3.3\text{V} \pm 5\%$ ;  $C_L = 10\text{-}20\text{ pF}$  (unless otherwise specified)

| PARAMETER           | SYMBOL          | CONDITIONS                                        | MIN | TYP  | MAX  | UNITS    |
|---------------------|-----------------|---------------------------------------------------|-----|------|------|----------|
| Output Impedance    | $R_{DSP1}^1$    | $V_O = V_{DD} \cdot (0.5)$                        | 20  | 48   | 60   | $\Omega$ |
| Output High Voltage | $V_{OH}^1$      | $I_{OH} = -1\text{ mA}$                           | 2.4 | 3.28 |      | V        |
| Output Low Voltage  | $V_{OL}^1$      | $I_{OL} = 1\text{ mA}$                            |     | 0.08 | 0.4  | V        |
| Output High Current | $I_{OH}^1$      | $V_{OH@MIN} = 1.0\text{ V}$                       | -33 | -110 |      |          |
|                     |                 | $V_{OH@MAX} = 3.135\text{ V}$                     |     | -20  | -33  | mA       |
| Output Low Current  | $I_{OL}^1$      | $V_{OL@MIN} = 1.95\text{ V}$                      | 30  | 110  |      |          |
|                     |                 | $V_{OL@MAX} = 0.4\text{ V}$                       |     | 37   | 38   | mA       |
| Rise Time           | $t_{r1}^1$      | $V_{OL} = 0.4\text{ V}$ , $V_{OH} = 2.4\text{ V}$ | 1   | 1.69 | 2    | ns       |
| Fall Time           | $t_{f1}^1$      | $V_{OH} = 2.4\text{ V}$ , $V_{OL} = 0.4\text{ V}$ | 1   | 1.56 | 2    | ns       |
| Duty Cycle          | $d_{t1}^1$      | $V_T = 1.5\text{ V}$                              | 45  | 53   | 55   | %        |
| Jitter              | $t_{jyc-cyc}^1$ | $V_T = 1.5\text{ V}$                              |     | 152  | 1000 | ps       |

<sup>1</sup>Guaranteed by design, not 100% tested in production.



## General I<sup>2</sup>C serial interface information

The information in this section assumes familiarity with I<sup>2</sup>C programming.  
For more information, contact ICS for an I<sup>2</sup>C programming application note.

### How to Write:

- Controller (host) sends a start bit.
- Controller (host) sends the write address D2<sub>(H)</sub>
- ICS clock will **acknowledge**
- Controller (host) sends a dummy command code
- ICS clock will **acknowledge**
- Controller (host) sends a dummy byte count
- ICS clock will **acknowledge**
- Controller (host) starts sending first byte (Byte 0) through byte 5
- ICS clock will **acknowledge** each byte **one at a time**.
- Controller (host) sends a Stop bit

| How to Write:             |                      |
|---------------------------|----------------------|
| Controller (Host)         | ICS (Slave/Receiver) |
| Start Bit                 |                      |
| Address D2 <sub>(H)</sub> |                      |
|                           | <b>ACK</b>           |
| Dummy Command Code        |                      |
|                           | <b>ACK</b>           |
| Dummy Byte Count          |                      |
|                           | <b>ACK</b>           |
| Byte 0                    |                      |
|                           | <b>ACK</b>           |
| Byte 1                    |                      |
|                           | <b>ACK</b>           |
| Byte 2                    |                      |
|                           | <b>ACK</b>           |
| Byte 3                    |                      |
|                           | <b>ACK</b>           |
| Byte 4                    |                      |
|                           | <b>ACK</b>           |
| Byte 5                    |                      |
|                           | <b>ACK</b>           |
| Byte 6                    |                      |
|                           | <b>ACK</b>           |
| Stop Bit                  |                      |

### How to Read:

- Controller (host) will send start bit.
- Controller (host) sends the read address D3<sub>(H)</sub>
- ICS clock will **acknowledge**
- ICS clock will send the **byte count**
- Controller (host) acknowledges
- ICS clock sends first byte (**Byte 0**) through **byte 6**
- Controller (host) will need to acknowledge each byte
- Controller (host) will send a stop bit

| How to Read:              |                      |
|---------------------------|----------------------|
| Controller (Host)         | ICS (Slave/Receiver) |
| Start Bit                 |                      |
| Address D3 <sub>(H)</sub> |                      |
|                           | <b>ACK</b>           |
|                           | <b>Byte Count</b>    |
| ACK                       |                      |
|                           | <b>Byte 0</b>        |
| ACK                       |                      |
|                           | <b>Byte 1</b>        |
| ACK                       |                      |
|                           | <b>Byte 2</b>        |
| ACK                       |                      |
|                           | <b>Byte 3</b>        |
| ACK                       |                      |
|                           | <b>Byte 4</b>        |
| ACK                       |                      |
|                           | <b>Byte 5</b>        |
| ACK                       |                      |
|                           | <b>Byte 6</b>        |
| ACK                       |                      |
| Stop Bit                  |                      |

### Notes:

1. The ICS clock generator is a slave/receiver, I<sup>2</sup>C component. It can read back the data stored in the latches for verification. **Read-Back will support Intel PIIX4 "Block-Read" protocol.**
2. The data transfer rate supported by this clock generator is 100K bits/sec or less (standard mode)
3. The input is operating at 3.3V logic levels.
4. The data byte format is 8 bit bytes.
5. To simplify the clock generator I<sup>2</sup>C interface, the protocol is set to use only **"Block-Writes"** from the controller. The bytes must be accessed in sequential order from lowest to highest byte with the ability to stop after any complete byte has been transferred. The Command code and Byte count shown above must be sent, but the data is ignored for those two bytes. The data is loaded until a Stop sequence is issued.
6. At power-on, all registers are set to a default condition, as shown.



## I2C Tables

| BYTE<br>0 | Affected Pin |                | Control Function                                                           | Type | Bit Control |        | PWD |
|-----------|--------------|----------------|----------------------------------------------------------------------------|------|-------------|--------|-----|
|           | Pin #        | Name           |                                                                            |      | 0           | 1      |     |
| Bit 7     | -            | Spread Enabled | Spread Spectrum Control                                                    | RW   | OFF         | ON     | 0   |
| Bit 6     | -            | CPU_T(2:0)     | Power down mode output level<br>0= CPU driven in power down<br>1= undriven | RW   | HIGH        | LOW    | 0   |
| Bit 5     | 35           | 3V66_1/VCH_CLK | VCH/66.66 Select                                                           | RW   | 66.66       | 48.00  | 0   |
| Bit 4     | 53           | CPU_STOP#*     | Reflects value of pin                                                      | R    | Stop        | Active | X   |
| Bit 3     | 34           | PCI_STOP#*     | Reflects value of pin at power up. Also can be set.                        | R/RW | Stop        | Active | 1   |
| Bit 2     | 40           | FS2            | Frequency Selection                                                        | RW   | -           | -      | X   |
| Bit 1     | 55           | FS1            | Frequency Selection                                                        | RW   | -           | -      | X   |
| Bit 0     | 54           | FS0            | Frequency Selection                                                        | RW   | -           | -      | X   |

| BYTE<br>1 | Affected Pin |                      | Control Function                                                         | Type | Bit Control |         | PWD |
|-----------|--------------|----------------------|--------------------------------------------------------------------------|------|-------------|---------|-----|
|           | Pin #        | Name                 |                                                                          |      | 0           | 1       |     |
| Bit 7     | 43           | MULTSEL0*            | Reflects value of pin                                                    | R    | -           | -       | x   |
| Bit 6     | -            | CPU_T(2:0)           | CPU_Stop mode output level<br>0= CPU driven when stopped<br>1 = undriven | RW   | HIGH        | LOW     | 0   |
| Bit 5     | 45, 44       | CPUCLKT2<br>CPUCLKC2 | Allow control of output with assertion of CPU_STOP#.                     | RW   | Not Freerun | Freerun | 0   |
| Bit 4     | 49, 48       | CPUCLKT1<br>CPUCLKC1 | Allow control of output with assertion of CPU_STOP#.                     | RW   | Not Freerun | Freerun | 0   |
| Bit 3     | 52, 51       | CPUCLKT0<br>CPUCLKC0 | Allow control of output with assertion of CPU_STOP#.                     | RW   | Not Freerun | Freerun | 0   |
| Bit 2     | 45, 44       | CPUCLKT2<br>CPUCLKC2 | Output control                                                           | RW   | Disable     | Enable  | 1   |
| Bit 1     | 49, 48       | CPUCLKT1<br>CPUCLKC1 | Output control                                                           | RW   | Disable     | Enable  | 1   |
| Bit 0     | 52, 51       | CPUCLKT2<br>CPUCLKC2 | Output control                                                           | RW   | Disable     | Enable  | 1   |



| BYTE<br>2 | Affected Pin |         | Control Function | Type | Bit Control |        | PWD |
|-----------|--------------|---------|------------------|------|-------------|--------|-----|
|           | Pin #        | Name    |                  |      | 0           | 1      |     |
| Bit 7     | -            | -       | (Reserved)       | -    | -           | -      | 0   |
| Bit 6     | 18           | PCICLK6 | Output control   | RW   | Disable     | Enable | 1   |
| Bit 5     | 17           | PCICLK5 | Output control   | RW   | Disable     | Enable | 1   |
| Bit 4     | 16           | PCICLK4 | Output control   | RW   | Disable     | Enable | 1   |
| Bit 3     | 13           | PCICLK3 | Output control   | RW   | Disable     | Enable | 1   |
| Bit 2     | 12           | PCICLK2 | Output control   | RW   | Disable     | Enable | 1   |
| Bit 1     | 11           | PCICLK1 | Output control   | RW   | Disable     | Enable | 1   |
| Bit 0     | 10           | PCICLK0 | Output control   | RW   | Disable     | Enable | 1   |

| BYTE<br>3 | Affected Pin |           | Control Function                                     | Type | Bit Control |             | PWD |
|-----------|--------------|-----------|------------------------------------------------------|------|-------------|-------------|-----|
|           | Pin #        | Name      |                                                      |      | 0           | 1           |     |
| Bit 7     | 38           | 48MHz_DOT | Output control                                       | RW   | Disable     | Enable      | 1   |
| Bit 6     | 39           | 48MHz_USB | Output control                                       | RW   | Disable     | Enable      | 1   |
| Bit 5     | 7            | PCICLK_F2 | Allow control of output with assertion of PCI_STOP#. | RW   | Freerun     | Not Freerun | 0   |
| Bit 4     | 6            | PCICLK_F1 | Allow control of output with assertion of PCI_STOP#. | RW   | Freerun     | Not Freerun | 0   |
| Bit 3     | 5            | PCICLK_F0 | Allow control of output with assertion of PCI_STOP#. | RW   | Freerun     | Not Freerun | 0   |
| Bit 2     | 7            | PCICLK_F2 | Output control                                       | RW   | Disable     | Enable      | 1   |
| Bit 1     | 6            | PCICLK_F1 | Output control                                       | RW   | Disable     | Enable      | 1   |
| Bit 0     | 5            | PCICLK_F0 | Output control                                       | RW   | Disable     | Enable      | 1   |

| BYTE<br>4 | Affected Pin |                | Control Function | Type | Bit Control |        | PWD |
|-----------|--------------|----------------|------------------|------|-------------|--------|-----|
|           | Pin #        | Name           |                  |      | 0           | 1      |     |
| Bit 7     | -            | -              | (Reserved)       | RW   | Disable     | Enable | 0   |
| Bit 6     | -            | -              | (Reserved)       | RW   | Disable     | Enable | 0   |
| Bit 5     | 33           | 3V66_0         | Output control   | RW   | Disable     | Enable | 1   |
| Bit 4     | 35           | 3V66_1/VCH_CLK | Output control   | RW   | Disable     | Enable | 1   |
| Bit 3     | 24           | 3V66_5         | Output control   | RW   | Disable     | Enable | 1   |
| Bit 2     | 23           | 3V66_4         | Output control   | RW   | Disable     | Enable | 1   |
| Bit 1     | 22           | 3V66_3         | Output control   | RW   | Disable     | Enable | 1   |
| Bit 0     | 21           | 3V66_2         | Output control   | RW   | Disable     | Enable | 1   |




| BYTE<br>5 | Affected Pin |      | Control Function | Type | Bit Control |   | PWD |
|-----------|--------------|------|------------------|------|-------------|---|-----|
|           | Pin #        | Name |                  |      | 0           | 1 |     |
| Bit 7     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 6     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 5     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 4     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 3     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 2     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 1     | X            | -    | (Reserved)       | -    | -           | - | 0   |
| Bit 0     | X            | -    | (Reserved)       | -    | -           | - | 0   |

| BYTE<br>6 | Affected Pin |                   | Control Function | Type | Bit Control |   | PWD |
|-----------|--------------|-------------------|------------------|------|-------------|---|-----|
|           | Pin #        | Name              |                  |      | 0           | 1 |     |
| Bit 7     | X            | Revision ID Bit 3 | (Reserved)       | R    | -           | - | 1   |
| Bit 6     | X            | Revision ID Bit 2 | (Reserved)       | R    | -           | - | 1   |
| Bit 5     | X            | Revision ID Bit 1 | (Reserved)       | R    | -           | - | 1   |
| Bit 4     | X            | Revision ID Bit 0 | (Reserved)       | R    | -           | - | 1   |
| Bit 3     | X            | Vendor ID Bit 3   | (Reserved)       | R    | -           | - | 1   |
| Bit 2     | X            | Vendor ID Bit 2   | (Reserved)       | R    | -           | - | 1   |
| Bit 1     | X            | Vendor ID Bit 1   | (Reserved)       | R    | -           | - | 1   |
| Bit 0     | X            | Vendor ID Bit 0   | (Reserved)       | R    | -           | - | 1   |



## 3V66 & PCI Phase Relationship

All 3V66 clocks are to be in pphase with each other. In the case where 3V66\_1 is configured as 48MHz VCH clock, there is no defined phase relationship between 3V66\_1/VCH and other 3V66 clocks. The PCI group should lag 3V66 by the standard skew described below as Tpci.



## Skews at Common Transition Edges

| GROUP       | SYMBOL          | CONDITIONS                 | MIN | TYP | MAX | UNITS |
|-------------|-----------------|----------------------------|-----|-----|-----|-------|
| PCI         | PCI $t_{sk}^1$  | $V_T = 1.5 \text{ V}$      |     | 127 | 500 | ps    |
| 3V66        | 3V66 $t_{sk}^1$ | $V_T = 1.5 \text{ V}$      |     | 67  | 250 | ps    |
| 3V66 to PCI | $S_{3V66-PCI}$  | 3V66 (5:0) leads 33MHz PCI | 1.5 |     | 3.5 | ns    |


<sup>1</sup>Guarenteed by design, not 100% tested in production.



### CPU\_STOP# - Assertion (transition from logic "1" to logic "0")

The impact of asserting the CPU\_STOP# pin is all CPU outputs that are set in the I<sup>2</sup>C configuration to be stoppable via assertion of CPU\_STOP# are to be stopped after their next transition. When the I<sup>2</sup>C Bit 6 of Byte 1 is programmed to '0' the final state of the stopped CPU signals is CPU = High and CPU# = Low. There is to be no change to the output drive current values. The CPU will be driven high with a current value equal to (Mult 0 'select') x (Iref), the CPU# signal will not be driven. When the I<sup>2</sup>C Bit 6 of Byte 1 is programmed to '1' then final state of the stopped CPU signals is Low, both CPU and CPU# outputs will not be driven.

#### Assertion of CPU\_STOP# Waveforms




### CPU\_STOP# Functionality

| CPU_STOP# | CPUT        | CPUC   |
|-----------|-------------|--------|
| 1         | Normal      | Normal |
| 0         | iref * Mult | Float  |

### CPU\_STOP# - De-assertion (transition from logic "0" to logic "1")

All CPU outputs that were stopped are to resume normal operation in a glitch free manner. The maximum latency from the de-assertion to active outputs is to be defined to be between 2 - 6 CPU clock periods (2 clocks are shown). If the I<sup>2</sup>C Bit 6 of Byte 1 is programmed to "1" then the stopped CPU outputs will be driven High within 3 nS of CPU\_Stop# de-assertion.

#### De-assertion of CPU\_STOP# Waveforms






## PD# - Assertion (transition from logic "1" to logic "0")

When PWRDWN# is sampled low by two consecutive rising edges of CPU clock, then all clock outputs except CPU clocks must be held low on their next high to low transitions. When the I<sup>2</sup>C Bit 6 of Byte 0 is programmed to '0' CPU clocks must be held with the CPU clock pin driven high with a value of  $2 \times I_{ref}$ , and CPU# undriven. If Bit 6 of Byte 0 is '1' then both CPU and CPU# are undriven. Note the example below shows CPU = 133 MHz and Bit 6 of Byte 0 = '0', this diagram and description is applicable for all valid CPU frequencies 66, 100, 133, 200 MHz.


Due to the state of the internal logic, stopping and holding the REF clock outputs in the LOW state may require more than one clock cycle to complete.

### Power Down Assertion of Waveforms



## Power Down De-Assertion Mode

The power-up latency needs to be less than 1.8mS. this is the time from the de-assertion of the powerdown of the ramping of the power supply until the time that stable clocks are output from the clock chip. If the I<sup>2</sup>C Bit 6 of Byte 0 is programmed to "1" then the stopped CPU outputs will be driven high within 3 nS of PD# de-assertion.







## PCI\_STOP# - Assertion (transition from logic "1" to logic "0")

The impact of asserting the PCI\_STOP# signal will be the following. All PCI[6:0] and stoppable PCI\_F[2,0] clocks will latch low in their next high to low transition. The PCI\_STOP# setup time  $t_{su}$  is 10 ns, for transitions to be recognized by the next rising edge.

Assertion of PCI\_STOP# Waveforms





300 mil SSOP Package

| SYMBOL | In Millimeters<br>COMMON DIMENSIONS |       | In Inches<br>COMMON DIMENSIONS |       |
|--------|-------------------------------------|-------|--------------------------------|-------|
|        | MIN                                 | MAX   | MIN                            | MAX   |
| A      | 2.41                                | 2.80  | .095                           | .110  |
| A1     | 0.20                                | 0.40  | .008                           | .016  |
| b      | 0.20                                | 0.34  | .008                           | .0135 |
| c      | 0.13                                | 0.25  | .005                           | .010  |
| D      | SEE VARIATIONS                      |       | SEE VARIATIONS                 |       |
| E      | 10.03                               | 10.68 | .395                           | .420  |
| E1     | 7.40                                | 7.60  | .291                           | .299  |
| e      | 0.635 BASIC                         |       | 0.025 BASIC                    |       |
| h      | 0.38                                | 0.64  | .015                           | .025  |
| L      | 0.50                                | 1.02  | .020                           | .040  |
| N      | SEE VARIATIONS                      |       | SEE VARIATIONS                 |       |
| α      | 0°                                  | 8°    | 0°                             | 8°    |

VARIATIONS


| N  | D mm. |       | D (inch) |      |
|----|-------|-------|----------|------|
|    | MIN   | MAX   | MIN      | MAX  |
| 56 | 18.31 | 18.55 | .720     | .730 |


Reference Doc.: JEDEC Publication 95, MO-118  
10-0034

Ordering Information

ICS950810yFLF-T

Example:





6.10 mm. Body, 0.50 mm. pitch TSSOP  
(240 mil) (20 mil)

| SYMBOL   | In Millimeters |      | In Inches      |      |
|----------|----------------|------|----------------|------|
|          | MIN            | MAX  | MIN            | MAX  |
| A        | --             | 1.20 | --             | .047 |
| A1       | 0.05           | 0.15 | .002           | .006 |
| A2       | 0.80           | 1.05 | .032           | .041 |
| b        | 0.17           | 0.27 | .007           | .011 |
| c        | 0.09           | 0.20 | .0035          | .008 |
| D        | SEE VARIATIONS |      | SEE VARIATIONS |      |
| E        | 8.10 BASIC     |      | 0.319 BASIC    |      |
| E1       | 6.00           | 6.20 | .236           | .244 |
| e        | 0.50 BASIC     |      | 0.020 BASIC    |      |
| L        | 0.45           | 0.75 | .018           | .030 |
| N        | SEE VARIATIONS |      | SEE VARIATIONS |      |
| $\alpha$ | 0°             | 8°   | 0°             | 8°   |
| aaa      | --             | 0.10 | --             | .004 |

#### VARIATIONS

| N  | D mm. |       | D (inch) |      |
|----|-------|-------|----------|------|
|    | MIN   | MAX   | MIN      | MAX  |
| 56 | 13.90 | 14.10 | .547     | .555 |

Reference Doc.: JEDEC Publication 95, MO-153

10-0039

## Ordering Information

ICS950810yGLF-T

Example:

ICS XXXX y G LF- T

Designation for tape and reel packaging

Lead Free (Optional)

Package Type

G = TSSOP

Revision Designator (will not correlate with datasheet revision)

Device Type

Prefix

ICS = Standard Device