






LOC		DIST		REVISIONS					
HM		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A	RLSD; ECO-09-027567	14DEC2009	GG	RA


- ALL DIMENSIONS SHOWN ARE NOMINAL
UNLESS OTHERWISE SPECIFIED.
- MATERIAL:
SHIELDED CASE - COPPER C2680, T=0.25MM, 30u" NICKEL PLATED
COUPLER HOUSING - ABS HIGH-IMPACT UL94V-0 THERMOPLASTIC
SPRING WIRE - PHOSPHOR BRONZE 5100W TEMPER WIRE,
Ø=0.45MM, 50u" GOLD OVER 100u" NICKEL UNDERCOAT.
3. MOUNTING PANEL THICKNESS .062 [1.57] NOMINAL.



SCALE 4:1



SINGLE PANEL CUTOUT



SUGGESTED FLUSH MOUNT
PANEL APPLICATION CUTOUT

2111124-1				PART NUMBER			
DWN G. GARRETT 18NOV2009				Tyco Electronics Harrisburg, PA 17105-3608			
CHK R. ASHRY 18NOV2009				NAME COUPLER, SL, INLINE, CAT6, SHIELDED			
APVD R. ASHRY 18NOV2009				SIZE A100779			
PRODUCT SPEC				DRAWING NO C=2111124			
APPLICATION SPEC				RESTRICTED TO -			
WEIGHT -				SCALE 6:1			
CUSTOMER DRAWING				SHEET 1			
				REV A			