





CONSTRUCTION:

BODY ----- ZINC ALLOY
HOUSING ----- POLYESTER BUTYLENE
TEREPHTHALATE (BLACK)
CENTER CONTACT -- PHOSPHOR BRONZE
DIELECTRIC ----- POLYPROPYLENE (94V2)
MOUNTING POST --- BRASS
SOLDER TAIL ----- COPPER OVER STEEL WIRE
LOCK WASHER ----- PHOSPHOR BRONZE
NUT ----- BRASS

FINISH:

BODY ----- NICKEL
CENTER CONTACT -- TIN
SOLDER TAIL ----- TIN
MOUNTING POST --- TIN
LOCK WASHER ----- NICKEL
NUT ----- NICKEL

PACKAGING ----- TRAY




LOCKWASHER



15.90
.626 REF


0.50
.020 REF



JAM NUT

14.00
.551 HEX

2.50
.098



RECOMMENDED MOUNTING HOLE
MAX PANEL THICKNESS: 5.5MM
RECOMMENDED MOUNTING TORQUE:
5 INCH-POUNDS MAX

CHG: CHANGE TITLE FROM R/A TO VERTICAL D2	EC NO: URF2008-0292 DRWN: JWEENER 2007/11/29 CHKD: SSSHAH 2007/11/29 APPR: JWEENER 2007/11/29	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
							DRAWN BY DATE IRIS WANG 1991/01/21		TITLE BNC, JACK PCB VERTICAL 50 OHM BNC-JACK			
							CHECKED BY DATE					
							APPROVED BY DATE		 MOLEX INCORPORATED			
					ANGULAR ± 2 °		MATERIAL NO.					DOCUMENT NO. SD-73131-5005
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

73131-5005