

MOS FET Relays

G3VM-201AY/DY

Compact, General-purpose, Analog-switching MOS FET Relays, with Dielectric Strength of 5 kVAC between I/O Using Optical Isolation.

- Trigger LED forward current of 2 mA (maximum) facilitates power saving designs.
- Switches minute analog signals.
- Continuous load current of 250 mA.

RoHS compliant

⚠ Refer to "Common Precautions".

Application Examples

- Power meter
- Measurement devices
- Security systems
- Industrial equipment

List of Models


Contact form	Terminals	Load voltage (peak value) (See the note.)	Model	Number per stick	Number per tape
SPST-NO	PCB terminals	200 V	G3VM-201AY	100	---
	Surface-mounting terminals		G3VM-201DY		
			G3VM-201DY(TR)	---	1,500

Note: The AC peak and DC value are given for the load voltage.


Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-201AY




G3VM-201DY





Terminal Arrangement/Internal Connections (Top View)

G3VM-201AY




G3VM-201DY



Note: The actual product is marked differently from the image shown here.


PCB Dimensions (Bottom View)

G3VM-201AY



Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-201DY



■ Absolute Maximum Ratings (Ta = 25°C)


Item	Symbol	Rating	Unit	Measurement Conditions
Input	LED forward current	I_F	30	mA
	Repetitive peak LED forward current	I_{FP}	1	A
	LED forward current reduction rate	$\Delta I_F/^{\circ}\text{C}$	-0.3	mA/ $^{\circ}\text{C}$
	LED reverse voltage	V_R	5	V
	Connection temperature	T_j	125	$^{\circ}\text{C}$
Output	Load voltage (AC peak/DC)	V_{OFF}	200	V
	Continuous load current (AC peak/DC)	I_O	250	mA
	ON current reduction rate	$\Delta I_{ON}/^{\circ}\text{C}$	-2.5	mA/ $^{\circ}\text{C}$
	Pulse ON current	I_{op}	0.75	A
	Connection temperature	T_j	125	$^{\circ}\text{C}$
Dielectric strength between input and output (See note 1.)		V_{I-O}	5,000	Vrms
Operating temperature		T_a	-40 to +85	$^{\circ}\text{C}$
Storage temperature		T_{stg}	-55 to +125	$^{\circ}\text{C}$
Soldering temperature (10 s)		---	260	$^{\circ}\text{C}$

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
Input	LED forward voltage	V_F	1.45	1.63	1.75	V
	Reverse current	I_R	---	---	10	μA
	Capacity between terminals	C_T	---	40	---	pF
	Trigger LED forward current	I_{FT}	---	0.3	2	mA
Output	Maximum resistance with output ON	R_{ON}	---	5	8	Ω
	Current leakage when the relay is open	I_{LEAK}	---	---	1.0	μA
	Capacity between terminals	C_{OFF}	---	90	---	pF
Capacity between I/O terminals		C_{I-O}	---	0.8	---	pF
Insulation resistance		R_{I-O}	1,000	---	---	M Ω
Turn-ON time		t_{ON}	---	0.5	1	ms
Turn-OFF time		t_{OFF}	---	0.2	1	ms

Note: 2. Turn-ON and Turn-OFF Times



■ Recommended Operating Conditions


Use the G3VM under the following conditions so that the Relay will operate properly.

Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	160	V
Operating LED forward current	I_F	3	5	20	mA
Continuous load current (AC peak/DC)	I_O	---	---	250	mA
Operating temperature	T_a	-20	---	65	$^{\circ}\text{C}$

■ Engineering Data

Load Current vs. Ambient Temperature

G3VM-201AY(DY)



■ Safety Precautions

Refer to "Common Precautions" for all G3VM models.