






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REV PER ECO 18-010457	7-24-18	CT	CJ





DETAIL T
SCALE 20:1

- ⚠ MATERIAL: HOUSINGS; LCP, COLOR-NATURAL
CONTACT; BERYLLIUM COPPER
SOLDER BALL; SEE TABLE
TAPE, FILM; KAPTON WITH SILICON ADHESIVE
- ⚠ FINISH: CONTACT; GOLD (SEE TABLE) ON MATING AREA OVER
NICKEL ON ENTIRE CONTACT.



DETAIL X
SCALE 16:1



PCB LAYOUT (CONNECTOR SIDE)
SCALE 8:1

SUPERSEDED BY 2102080-4	2102079-4	12	0.76 μ m	8	LEAD FREE PER SAC405	2102080-8
SUPERSEDED BY 2102080-3	2102079-3	12	0.76 μ m	8	TIN LEAD	2102080-7
SUPERSEDED BY 2102080-2	2102079-4	10	0.76 μ m	6	LEAD FREE PER SAC405	2102080-6
SUPERSEDED BY 2102080-1	2102079-3	10	0.76 μ m	6	TIN LEAD	2102080-5
	2102079-2	12	1.27 μ m	8	LEAD FREE PER SAC405	2102080-4
	2102079-1	12	1.27 μ m	8	TIN LEAD	2102080-3
	2102079-2	10	1.27 μ m	6	LEAD FREE PER SAC405	2102080-2
	2102079-1	10	1.27 μ m	6	TIN LEAD	2102080-1
MATING PART NUMBER	MATED STACK HEIGHT (mm)	GOLD PLATING THICKNESS	H MAX REF	SOLDER BALL MATERIAL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. DOWDY 23JUL2009	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK K. DOWHOWER 23JUL2009				
DIMENSIONS:		APVD K. DOWHOWER	NAME ASSEMBLY, SOCKET, 60 POSITION, MEZALOK STACKING CONNECTOR			
mm		PRODUCT SPEC	SIZE -			
		APPLICATION SPEC	CAGE CODE -			
		ANGLES	DRAWING NO -			
MATERIAL		FINISH	A100779C=2102080			
		WEIGHT	CUSTOMER DRAWING			
		SCALE	10:1			
		SHEET	1 OF 1			
		REV	E			