




HONEYWELL
PART NUMBER
11SX21-H58
PRODUCT CODE
VDJ1995

REV	DOCUMENT	CHANGED BY	CHECK
9	0038448	VS 28APR08	BLR

B

A

A



- NOTES
- (1) MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188 ± .002 CENTERS
 - (2) PLATED TERMINALS WILL ACCEPT "AMP INC".058 DIA PIN RECEPTACLES.
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.
PR-4206
REPLACES

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ±			DRAWN	SPK	08FEB08		Honeywell				
OPERATING FORCE — — — 2.5 - 5 OZ		CONTACT ARRANGEMENT S P D T							CHECK	RJ	08FEB08						
RELEASE FORCE— — — — — 1 OZ MIN			28 VOLTS DC RATING		115 VOLTS AC, 60 CPS		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE							
			SEA LEVEL	50,000 FT	SEA LEVEL					SWITCH - BASIC							
DIFFERENTIAL TRAVEL— — — .002 MAX		INDUCTIVE	3 AMP	2 AMP	5 AMP												
OVERTRAVEL — — — — — .004 MIN		RESISTIVE	5 AMP	4 AMP	5 AMP												
		—				THIRD ANGLE PROJECTION 			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV	
		APPROVALS	KEMA, CE	5A 250 V ~ T125 5E4					UL, CSA	5A 250 VAC		BRAND	L4L	B	I	11SX21-H58	
									RASTER			SCALE	-	WEIGHT:.003 LB MAX		SHEET 1 OF 1	