



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Customer Specification

PART NO. 6450

Construction

			Diameters (In)				
1) Component 1		2 X 1 COND					
a) Conductor		18 (7/26) AWG TC			0.046		
b) Insulation		0.025" Wall, Nom. FRPP			0.096		
(1) Color(s)							
Cond	Color	Cond	Color	Cond	Color		
1	BLUE	2	WHITE				
2) Cable Assembly		2 Components Cabled					
a) Twists:		6.9 Twists/foot (min)					
3) Shield:		Alum/Mylar Tape, 25% Overlap, Min.					
a) Foil Direction		Foil Facing Out					
b) Drain Wire		20 (7/28) AWG TC					
c) Braid		TC,55% Coverage, Min.					
4) Jacket		0.053" Wall, Nom.,PVC		0.324+- 0.006			
a) Color(s)		BLUE					
b) Print		ALPHA WIRE-* P/N 6450 EXXXXX 1PR18 SHIELDED (UL) 600V 75C DRY SUN RES TYPE TC OR PLTC OR ITC OR CMG OR C(UL) CMG --- P-MSHA (MSHA #) (seq footage every 2 ft) * = Factory Code					
<i>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]</i>							

Applicable Specifications

1) UL	TC	75°C / 600 V _{RMS}
	PLTC	75°C
	ITC	75°C
	CMG	75°C
	SUN RES	
2) CSA International	CMG	75°C
	FT4	
3) Other	PMSHA Specification	

Environmental

1) EU Directive 2002/95/EC(RoHS):

	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
--	--

Properties

Physical & Mechanical Properties	
1) Temperature Range	-40 to 75°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	40 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	600 V _{RMS}
2) Characteristic Impedance	78 Ω +/- 5
3) Inductance	0.12 μH/ft, Nominal
4) Mutual Capacitance	19.5 pF/ft @ 1 kHz, Nominal
5) Velocity of Propagation	65 %
6) Conductor DCR	6.9 Ω/1000ft @ 20°C, Nominal
7) OA Shield DCR	3.2 Ω/1000ft @ 20°C, Nominal
8) Attenuation, Max dB/100ft	0.5 @ 1 MHz
	2 @ 10 MHz
	3.8 @ 50 MHz
	5.4 @ 100 MHz
	7.6 @ 200 MHz
	10.7 @ 400 MHz

Other

1) Packaging	
a) 1000 FT	
b) 500 FT	
c) 100 FT	

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
 Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:6450

6450 , RoHS-Compliant Commencing With 7/1/2008 Production

*This document certifies that the Alpha part numbers cited above are manufactured in accordance with Directive 2002/95/EC of the European Parliament and of the Council of 27 January 2003, better known as the RoHS Directives, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. **No Exemptions are required for RoHS Compliance on this item.***

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE)	0.1% by weight (1000 ppm)
Including Deca-BDE	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire Company:



Dave Watson, Director of Engineering & QA

11/1/2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[6450 BL002](#)