




RED INDICATES ORIGINAL

DASH NO	MODEL NO	LTR CODE	A DIM	B DIM	C DIM	D DIM
-1	CBJR70	—	.24	.050	.090	.0625
-2	CBJR70A	A	.34	.058	.090	.070



INCH	MM
.0010	0.03
.0015	0.04
.005	0.13
.030	0.76
.040	1.02
.050	1.27
.058	1.47
.060	1.52
.0625	1.59
.070	1.78
.090	2.29
.100	2.54
.13	3.30
.24	6.10
.258	6.55
.34	8.64
.380	9.65
1.042	26.47
1.216	30.89

- 6 PRE-TINNED, .0015 MAXIMUM THICKNESS WITH SN63 OR EQUIV SOLDER, PER QQ-S-571, TO WITHIN .060 MAXIMUM OF SHOULDER, AFTER PLATING

- 5 LTR CODE "A" SHOWN IN PHANTOM

- #### 4. EXAMPLE OF COMPLETE MODEL NO:

- CBJR70 A LTR CODE (SEE TABLE) 5
BASIC MODEL NO (SEE TABLE)

3. FINISH: TFS-1A (NICKEL)

- ## 2. CONCENTRIC TWINAX/TRIAX RIGHT ANGLE CIRCUIT BOARD MOUNT TRB SERIES RECEPTACLE

1. ALL DIM ARE IN INCHES

DISK #	DWG SIZE	DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.	REVISIONS			3-0280		SH 1
H12	C		REV	EO	DESCRIPTION	DWN	APPROVED	DATE

QTY	DESCRIPTION				PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ± .005 .XXXX ± .0010 ANGLES ±		TROMPETER ELECTRONICS, INC.			CBJR70 / A	
DWN	J S	4/20/92	MATERIAL	CODE IDENT	DRAWING NO.	REV
CHK	BW	4/22/92	_____	14949	3-0280	
ENGR						
APPR	OT	4-23-92	SCALE 4/1	DATE 4-23-92	SHEET 1 OF 2	

NEXT ASSY