

GT5Y Series — ON Delay Timers



Key features of the GT5Y series include:

- 4PDT, 3A or DPDT, 5A contacts
- 4 time ranges
- Repeat error $\pm 0.2\%$ maximum
- Control settings by hand or screwdriver
- Power ON and timing out LED indicators
- Uses the same sockets and hold-down clips as IDEC's RY4S and RU series relays



UL, c-uL Listed

File No. E55996



		GT5Y-2	GT5Y-4	
Specifications	Rated Operating Voltage		100 to 120V AC (50/60Hz) 200 to 240V AC (50/60Hz) 24V DC 24V AC 12V DC	
	Contact Form		DPDT	4PDT
	Rated Load	Resistive Load	220V AC, 5A 30V DC, 5A	220V AC, 3A 30V DC, 3A
		Inductive Load	220V AC, 2A 30V DC, 2.5A	220V AC, 0.8A 30V DC, 1.5A
	Allowable Contact Power	Resistive Load	1100VA AC 150W DC	660VA AC 90W DC
		Inductive Load Cos Ø = 0.3 L/r = 7msec	440VA AC 75W DC	176VA AC 45W DC
	Allowable Voltage		250V AC, 125V DC	
	Allowable Current		5A	3A
	Temperature Error		±3% maximum (over -10 to 50°C, reference temperature 20°C)	
	Setting Error		±10% maximum	
	Reset Time		When turning power off <u>after</u> time up: 0.1 second maximum When turning power off <u>before</u> time up: 1 second maximum	
	Insulation Resistance		100MΩ minimum	
	Dielectric Strength		2,000V AC, 1 minute (except between contacts of the same pole)	
	Vibration Resistance		100N (approximate 10G)	
	Shock Resistance		Operating extremes: 100N (approximate 10G) Damage limits: 500N (approximate 50G)	
	Power Consumption		100V AC type: 1.5VA (at 50Hz) 200V AC type: 1.6VA (at 50Hz) 24V DC type: 0.9W	
	Electrical Life		500,000 operations minimum (220V AC, 5A)	200,000 operations minimum (110V AC, 3A)
Mechanical Life		50,000,000 operations minimum	50,000,000 operations minimum	
Operating Temperature		-10 to +50°C		
Operating Humidity		45 to 85% RH		



1. Minimum applicable load: GT5Y-2: 5V DC, 20mA (reference value); GT5Y-4: 5V DC, 10mA (reference value).
2. Inductive load: $\cos\theta = .3$, $L/R = 7\text{msec}$.

GT5Y Table of Contents

Part Number List — G-64

Timing Diagrams — G-65

GT5Y Accessories — G-66

GT5Y Dimensions — G-67

Part Numbering List

Mode of Operation	Contact	Output	Rated Voltage	Time Range	Complete Part No.
ON-Delay	DPDT	220V AC/ 30V DC, 5A	100 to 120V AC	1S/10S/1M/10M	GT5Y-2SN1A100
				3S/30S/3M/30M	GT5Y-2SN3A100
				6S/60S/6M/60M	GT5Y-2SN6A100
			200 to 240V AC	1S/10S/1M/10M	GT5Y-2SN1A200
				3S/30S/3M/30M	GT5Y-2SN3A200
				6S/60S/6M/60M	GT5Y-2SN6A200
			12V DC	1S/10S/1M/10M	GT5Y-2SN1D12
				3S/30S/3M/30M	GT5Y-2SN3D12
				6S/60S/6M/60M	GT5Y-2SN6D12
			24V DC	1S/10S/1M/10M	GT5Y-2SN1D24
				3S/30S/3M/30M	GT5Y-2SN3D24
				6S/60S/6M/60M	GT5Y-2SN6D24
			24V AC	1S/10S/1M/10M	GT5Y-2SN1A24
				3S/30S/3M/30M	GT5Y-2SN3A24
				6S/60S/6M/60M	GT5Y-2SN6A24
	4PDT	220V AC/ 30V DC, 3A	100 to 120V AC	1S/10S/1M/10M	GT5Y-4SN1A100
				3S/30S/3M/30M	GT5Y-4SN3A100
				6S/60S/6M/60M	GT5Y-4SN6A100
			200 to 240V AC	1S/10S/1M/10M	GT5Y-4SN1A200
				3S/30S/3M/30M	GT5Y-4SN3A200
				6S/60S/6M/60M	GT5Y-4SN6A200
			12V DC	1S/10S/1M/10M	—
				3S/30S/3M/30M	GT5Y-4SN3D12
				6S/60S/6M/60M	—
			24V DC	1S/10S/1M/10M	GT5Y-4SN1D24
				3S/30S/3M/30M	GT5Y-4SN3D24
				6S/60S/6M/60M	GT5Y-4SN6D24
			24V AC	1S/10S/1M/10M	GT5Y-4SN1A24
				3S/30S/3M/30M	GT5Y-4SN3A24
				6S/60S/6M/60M	GT5Y-4SN6A24



1. For sockets and accessories, see page G-66.



Timing Ranges

Code	Scale	Time Range Indication		Time Range
1S	0 to 10	x 0.1	S	0.1 second to 1 second
10S		x 1	S	0.2 second to 10 seconds
1M		x 0.1	M	1.2 seconds to 1 minute
10M		x 1	M	12 seconds to 10 minutes
3S	0 to 3	x 1	S	0.1 second to 3 seconds
30S		x 10	S	0.5 second to 30 seconds
3M		x 1	M	3 seconds to 3 minutes
30M		x 10	M	30 seconds to 30 minutes
6S	0 to 6	x 1	S	0.1 second to 6 seconds
60S		x 10	S	1 second to 60 seconds
6M		x 1	M	6 seconds to 6 minutes
60M		x 10	M	1 minute to 60 minutes

Timing Diagram/Schematics/Electrical Life Curves

	GT5Y-2	GT5Y-4																		
	DPDT	4PDT																		
Internal Connections (bottom view)																				
Operation Mode: ON-Delay	<table border="1"> <thead> <tr> <th>Item</th><th>Terminal No.</th><th>Operation</th></tr> </thead> <tbody> <tr> <td>Power (Power)</td><td>13-14</td><td>Set Time</td></tr> <tr> <td>Delayed Contact (NC)</td><td>1-9, 2-10, 3-11, 4-12</td><td></td></tr> <tr> <td>(NO)</td><td>5-9, 6-10, 7-11, 8-12</td><td></td></tr> <tr> <td>Indicator</td><td>POWER</td><td></td></tr> <tr> <td></td><td>OUT</td><td></td></tr> </tbody> </table> For an explanation of timing modes, see page E-4.		Item	Terminal No.	Operation	Power (Power)	13-14	Set Time	Delayed Contact (NC)	1-9, 2-10, 3-11, 4-12		(NO)	5-9, 6-10, 7-11, 8-12		Indicator	POWER			OUT	
Item	Terminal No.	Operation																		
Power (Power)	13-14	Set Time																		
Delayed Contact (NC)	1-9, 2-10, 3-11, 4-12																			
(NO)	5-9, 6-10, 7-11, 8-12																			
Indicator	POWER																			
	OUT																			

Electrical Life Curves



Dimensions

GT5Y Timer, Blade with SY4S-05

