





PRODUCT NO.
SEE TABLE



mat'l. code				surface	tolerance	projection	product family
—				ISO 1302	ISO 406 ISO 1101	ISO 1000	CARD CONN
lir	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM	title
J	V61635	MDF	11/21/96	angles	linear		
K	V70999	LSS	12/11/97				
L	V02386	AZ	10/05/00	0° $\pm 2^\circ$	xxxx $\pm .0020/.05$	scale 4:1	
M	M05-0181	MHT	8/22/05	dr	L. SANDERS	12/11/97	
N	M06-0117	AEA	6/26/06	eng	H. SUNDY	12/11/97	
P	M07-0137	MHT	2/26/07	chr	H. SUNDY	12/11/97	
R	M09-0093	MHT	6/22/09	appd	H. SUNDY	12/11/97	
sheet	revision	R	R	R	R	R	
index	sheet	1	2	3	4	5	6



dwg no 67477
sheet 1 of 6
size A3
type Product Customer Drawing



1. HOUSING MATERIAL.
 FILLED HIGH TEMPERATURE NYLON
 NOTES. PER UL 94V-0
 COLOR. BLACK
2. TERMINAL MATERIAL.
 BODY. BRASS. .010/.25 THICK.
 SPRING. BE-CU. HEAT TREATED
 BODY PLATING.
 40 MICROINCH / 1.02 MICRON GOLD
 OVER 50 MICROINCH / 1.27 MICRON NICKEL IN CONTACT AREA.
 SOLDER TAIL. 100u"/2.54u" PURE TIN (MOTE 8) OVER 50u"/1.27 Ni.
 SPRING PLATING. GOLD FLASH
3. APPLICATION INFORMATION.
 A. RECOMMENDED MOUNTING HOLE PATTERN IS SHOWN IN FIG. 1.
 B. ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA.
 C. SUGGESTED MATING PIN LENGTH .350±.020/8.89±.51.
- ④ TERMINAL MATERIAL:
 BODY. BRASS. .010/.25 THICK.
 SPRING. BE-CU. HEAT TREATED
 BODY PLATING.
 40 MICROINCH / 1.02 MICRON GOLD
 OVER 50 MICROINCH / 1.27 MICRON NICKEL IN CONTACT AREA.
 SOLDER TAIL: GOLD FLASH OVER 50u"/1.27u Ni.1.27 Ni.
 SPRING PLATING. GOLD FLASH
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑥ THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- ⑧ THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WISKER GROWTH IN ALL INTERCONNECT REQUIREMENTS

FCI
 FCconnect.com
 Copyright FCI

mat'l. code		surface	tolerance	projection	product family
-		ISO 1302	ISO 406		CARD CONN
ISO 1101		ISO 1101	ISO 1101		
ltr	ecr no	dr	date	title	
R				GUIDE PIN	
				CARD CONNECTOR	
				dwg no	sheet 2 of 6 size
				67477	A3
				type Product Customer Drawing	
sheet	revision				
index	sheet				

PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION
67477-041	2X41	4.00/101.6	4.358/110.69	NO	NOTE 6,7
-042	2X42	4.10/104.1	4.458/113.23		
-043	2X43	4.20/106.6	4.558/115.77		
-044	2X44	4.30/109.2	4.658/118.31		
-045	2X45	4.40/111.7	4.758/120.85		
-046	2X46	4.50/114.3	4.858/123.39		
-047	2X47	4.60/116.8	4.958/125.93		
-048	2X48	4.70/119.3	5.058/128.47		
-049	2X49	4.80/121.9	5.158/131.01		
-050	2X50	4.90/124.4	5.258/133.55		
-051	2X51	5.00/127.0	5.358/136.09		
-052	2X52	5.10/129.5	5.458/138.63		
-053	2X53	5.20/132.0	5.558/141.17		
-054	2X54	5.30/134.6	5.658/143.71		
-055	2X55	5.40/137.1	5.758/146.25		
-056	2X56	5.50/139.7	5.858/148.79		
-057	2X57	5.60/142.2	5.958/151.33		
-058	2X58	5.70/144.7	6.058/153.87		
-059	2X59	5.80/147.3	6.158/156.41		
-060	2X60	5.90/149.8	6.258/158.95		
-061	2X61	6.00/152.4	6.358/161.49		
-062	2X62	6.10/154.9	6.458/164.03		
-063	2X63	6.20/157.4	6.558/166.57		
-064	2X64	6.30/160.0	6.658/169.11		
67477-065	2X65	6.40/162.5	6.758/171.65	NO	
-066 THRU					NOTE 6,7
-100					

OBSOLETE

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN	
ltr	ecr no	dr	date	tolerances unless otherwise specified							
R				angles	linear	.XX±.01/.3		INCH/MM 		title GUIDE PIN CARD CONNECTOR dwg no 67477 sheet 4 of 6 size A3 type Product Customer Drawing	
				0'±2'		.xxx ±.005/.13					
				dr	L. SANDERS	12/11/97		scale 4:1			
				engr	H. SUNDY	12/11/97		FCJ			
				chr	H. SUNDY	12/11/97					
				appd	H. SUNDY	12/11/97					
sheet index	revision sheet										

PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION
67477-501	2X1	.00/.0	.358/9.09	YES	NOTE 6,7
-502	2X2	.10/2.5	.458/11.63	YES	UNASSIGNED
-503	2X3	.20/5.0	.558/14.17	YES	OBSOLETE
-504	2X4	.30/7.6	.658/16.71	YES	OBSOLETE
-505	2X5	.40/10.1	.758/19.25		OBSOLETE
-506	2X6	.50/12.7	.858/21.79		
-507	2X7	.60/15.2	.958/24.33		
-508	2X8	.70/17.7	1.058/26.87		
-509	2X9	.80/20.3	1.158/29.41		
-510	2X10	.90/22.8	1.258/31.95		
-511	2X11	1.00/25.4	1.358/34.49		
-512	2X12	1.10/27.9	1.458/37.03		
-513	2X13	1.20/30.4	1.558/39.57		
-514	2X14	1.30/33.0	1.658/42.11		
-515	2X15	1.40/35.5	1.758/44.65		
-516	2X16	1.50/38.1	1.858/47.19		
-517	2X17	1.60/40.6	1.958/49.73		
-518	2X18	1.70/43.1	2.058/52.27		
-519	2X19	1.80/45.7	2.158/54.81		
-520	2X20	1.90/48.2	2.258/57.35		
-521	2X21	2.00/50.8	2.358/59.89		
-522	2X22	2.10/53.3	2.458/62.43		
-523	2X23	2.20/55.8	2.558/64.97		
-524	2X24	2.30/58.4	2.658/67.51		
-525	2X25	2.40/60.9	2.758/70.05		
-526	2X26	2.50/63.5	2.858/72.59		
-527	2X27	2.60/66.0	2.958/75.13		
-528	2X28	2.70/68.5	3.058/77.67		
-529	2X29	2.80/71.1	3.158/80.21		
-530	2X30	2.90/73.6	3.258/82.75		
-531	2X31	3.00/76.2	3.358/85.29		
-532	2X32	3.10/78.7	3.458/87.83		
-533	2X33	3.20/81.2	3.558/90.37		
-534	2X34	3.30/83.8	3.658/92.91		
-535	2X35	3.40/86.3	3.758/95.45		
-536	2X36	3.50/88.9	3.858/97.99		
-537	2X37	3.60/91.4	3.958/100.53		
-538	2X38	3.70/93.9	4.058/103.07		
-539	2X39	3.80/96.5	4.158/105.61		
67477-540	2X40	3.90/99.0	4.258/108.15	YES	NOTE 6,7

mat'l. code		surface ISO 1902 ☒ ISO 406 ☐ ISO 1901		tolerance ISO 406 ☐ ISO 1901		projection 		product family CARD CONN	
ltr	ec'n no	dr	date	tolerances unless otherwise specified				title	
R				angles	linear	.XXX ±.01/.3 .XXX ±.005/.13 O' ±2'		GUIDE PIN CARD CONNECTOR	
						scale 4:1		dwg no	
				dr	L. SANDERS	12/11/97			sheet 5 of 6
				engr	H. SUNDY	12/11/97			size
				chr	H. SUNDY	12/11/97			A3
				appd	H. SUNDY	12/11/97			
sheet	revision							type Product Customer Drawing	
index	sheet								

PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION
67477-541	2X41	4.00/101.6	4.358/110.69	YES	NOTE 6,7
-542	2X42	4.10/104.1	4.458/113.23		
-543	2X43	4.20/106.6	4.558/115.77		
-544	2X44	4.30/109.2	4.658/118.31		
-545	2X45	4.40/111.7	4.758/120.85		
-546	2X46	4.50/114.3	4.858/123.39		
-547	2X47	4.60/116.8	4.958/125.93		
-548	2X48	4.70/119.3	5.058/128.47		
-549	2X49	4.80/121.9	5.158/131.01		
-550	2X50	4.90/124.4	5.258/133.55		
-551	2X51	5.00/127.0	5.358/136.09		
-552	2X52	5.10/129.5	5.458/138.63		
-553	2X53	5.20/132.0	5.558/141.17		
-554	2X54	5.30/134.6	5.658/143.71		
-555	2X55	5.40/137.1	5.758/146.25		
-556	2X56	5.50/139.7	5.858/148.79		
-557	2X57	5.60/142.2	5.958/151.33		
-558	2X58	5.70/144.7	6.058/153.87		
-559	2X59	5.80/147.3	6.158/156.41		
-560	2X60	5.90/149.8	6.258/158.95		
-561	2X61	6.00/152.4	6.358/161.49		
-562	2X62	6.10/154.9	6.458/164.03		
-563	2X63	6.20/157.4	6.558/166.57		
-564	2X64	6.30/160.0	6.658/169.11		
67477-565	2X65	6.40/162.5	6.758/171.65	YES	
-566 THRU					NOTE 6,7
-600					

OBSOLETE



FCI
FCIconnect.com

Copyright FCI

mat'l. code		surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN	
ltr	ecr no	dr	date	tolerances unless otherwise specified				title	
R				angles	linear	INCH/MM		GUIDE PIN CARD CONNECTOR	
				0'±2"	xxxx ±.005/.13	scale 4:1		dwg no	
				dr	L. SANDERS 12/11/97			sheet 6 of 6 size	
				engr	H. SUNDY 12/11/97			67477 A3	
				chr	H. SUNDY 12/11/97			type	
				appd	H. SUNDY 12/11/97			Product Customer Drawing	
sheet	revision								
index	sheet								

form: A3