

SMD Choke Coils

Singapore

Series: **M**

Type: **ELL3GM**



Type ELL3GM

■ Features

- Magnetic shielded structure
- Low DC resistance and capable of corresponding
- Structure for withstanding fall shock
- Available on tape and reel for automatic insertion


■ Recommended Applications

- DC/DC converter circuit for Computer peripheral, Hand phone.
- Choke coils for Chopper circuit decoupling choked in DC/DC converter circuit


■ Standard Packing Quantity

- 2000 pcs./Reel


■ Explanation of Part Numbers



■ Dimensions in mm (not to scale)



■ Recommended land patterns in mm (not to scale)



Examples

Part Number	Inductance (100kHz)		DCR (at 20 °C)		*Rated Current (mA max.)	Marking
	(μH)	Tol.	(mΩ)	Tol.		
ELL3GM2R2N	2.2	±30%	100	±20%	1100	C
ELL3GM2R7N	2.7		110		1000	D
ELL3GM3R3N	3.3		130		980	E
ELL3GM3R9N	3.9		140		940	F
ELL3GM4R3N	4.3		220		720	H
ELL3GM5R1N	5.1		240		690	I
ELL3GM5R6N	5.6		260		670	J
ELL3GM6R8N	6.8		280		650	K
ELL3GM8R2N	8.2	±20%	310		620	L
ELL3GM100M	10.0		350		550	M
ELL3GM120M	12.0		400		530	N
ELL3GM150M	15.0		560		440	O
ELL3GM180M	18.0		640		420	P
ELL3GM220M	22.0		770		360	R
ELL3GM270M	27.0		1050		330	S
ELL3GM330M	33.0		1200		310	T

* Current: This indicates the value of current when the inductance is 70% more than nominal value and temperature rising $\Delta t=45^{\circ}\text{C}$ lower at D.C superposition.(at 20°C)

Embossed Carrier Tape Dimensions in mm (not to scale)

