


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CE	16		C	REV PER ECN 0A10-0101-01	09-21-01	JAB CB
			D	REL PER EC 0A00-0858-02	12-11-02	LGE CB
			E	REL PER EC 0A00-0304-03	8-7-03	LGE CB



NOMINAL ATTENUATION VALUE (dB)	PART NUMBER	
1	209597-1	
2	209597-2	
3	209597-3	
4	209597-4	
5	209597-5	
6	209597-6	
7	209597-7	OBSOLETE
8	209597-8	OBSOLETE
9	209597-9	
10	1-209597-0	
11	1-209597-1	OBSOLETE
12	1-209597-2	
13	1-209597-3	OBSOLETE
14	1-209597-4	OBSOLETE
15	1-209597-5	
16	1-209597-6	OBSOLETE
17	1-209597-7	OBSOLETE
18	1-209597-8	
19	1-209597-9	OBSOLETE
20	2-209597-0	
25	2-209597-5	

TYCO LOGO, ATTENUATION VALUE, PART NUMBER, AND SERIAL NUMBER ARE PRINTED ON THE LABEL.

PERFORMANCE REQUIREMENTS:
OPERATING WAVELENGTH : 1310/1550 ±25nm
REFLECTANCE : ≤ -65dB
OPERATING TEMPERATURE : -40°C TO +75°C
ATTENUATION TOLERANCE, AMBIENT :
FOR ATTENUATORS ≥ 5dB : ±10% OF NOMINAL ATTENUATION VALUE
FOR ATTENUATORS < 5dB : ± 0.50dB
MEASURED WITH REFERENCE QUALITY LAUNCH LEADS

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN D. ERDMAN 7-20-00	AMP Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK S. MILLER 7-20-00		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		APVD S. BUCHTER 7-20-00	NAME ATTENUATOR, OPTICAL, BUILDOUT SC/APC 8 DEGREE, SM, DUAL WINDOW	
MATERIAL -		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
		APPLICATION SPEC -	DRAWING NO 209597	RESTRICTED TO -
		WEIGHT -	SCALE 4:1	SHEET 1 OF 1
		CUSTOMER DRAWING	REV E	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-209597-0](#)