



10	9	8	7	6	5	4	3	2	19193
MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO.	STUD SIZE	"S"	STOCK THICKNESS			
191930225	E-358-10	-----	-----	10	.198±.003	.057/(1.45) REF			
191930229	E-358-14	-----	-----	1/4	.265±.003				
191930232	E-358-56	-----	-----	5/16	.328±.003				
191930230	E-358-38	191930231	E-358-38T	3/8	.390±.003				
191930234	E-358-76	-----	-----	7/16	.453±.003				
191930226	E-358-12	191930228	E-358-12T	1/2	.515±.003				
191930233	E-358-58	-----	-----	5/8	.649 MIN.				



Ⓛ1



SALES DRAWING

- NOTE(S):
1. MATERIAL: COPPER
 2. PLATING: ELECTROPLATE TIN
 3. ALL DIMENSIONS IN INCHES/(MM).
 4. WIRE SIZE: 6 AWG
16 MM²
 5. PART IS ROHS COMPLIANT.

CHANGE 5/8 STUD DIM EC NO: IPG2016-1554 DRAWN: GROSAS01 2016/05/18 CHKD: JMACNEIL 2016/05/18 APPR: JMACNEIL 2016/05/31			DESCRIPTION	REV	D1	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 		
mm		INCH					DRAWN BY DLM		DATE 03/07/25		TITLE RING TONGUE TERMINAL VERSAKRIMP SERIES 6 AWG MOLEX INCORPORATED				
4 PLACES ± --- ± ---		CHECKED BY HEB					DATE 03/07/25								
3 PLACES ± --- ± .005		APPROVED BY RWD					DATE 03/07/25								
2 PLACES ± 0.13 ± .01		MATERIAL NO. SEE CHART					DOCUMENT NO. SD-19193-005								
1 PLACE ± 0.25 ± ---		ANGULAR ±1/2°					SHEET NO. 1 OF 1								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								