

DATA COMMUNICATIONS TRANSFORMERS

HDSL SERIES

FEATURES:

- Supports Industry Standard HDSL/HDSL2 Transceivers
- Conforms to ANSI, ITU and ETSI Standards Requirements
- Meets Standard Dielectric Withstanding Voltage Requirements
- Operating Temperature Range of -40 C to 85°C

STANDARD SPECIFICATIONS

Part Number*	LineRate (Kb/s)	Turns Ratio** (Chip / Line)	OCL (Line)	R _L @ Midband (dB)	l _L (dB)	Longitudinal Balance (dB)	THD (dB)	Pkg.	Cir.
AHDL-101 ²	784	1:1:1CT	3.0 mH	≥ 20 40 - 200 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	23x11	2
AHDL-102 ⁷	1168	1:1:1CT	2.0 mH	≥ 12 40 - 320 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	23x11	3
AHDL-103 ⁴	784	1:1:2CT	3.0 mH	≥ 20 40 - 200 KHz	< 1.0 40 KHz	≥ 55 5 - 196 KHz	≤ -75	23x11	3
AHDL-104 ³	1168	1:1:1CT	2.0 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -75	23x11	3
AHDL-105 ⁵	784	1.8CT:1CT	2.8 mH	≥ 20 40 - 200 KHz	< 1.0 40 KHz	≥ 50 5 - 196 KHz	≤ -75	23x11	1
AHDL-106 ⁶	1168	1:1:1CT	2.0 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	23x11	2
AHDL-107 ⁶	1168	1.8CT:1CT	2.06 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 50 40 - 320 KHz	≤ -70	23x11	4
AHDL-108 ⁸	1552	2.3:1	2.0 mH	≥ 18 40 - 320 KHz	< 1.0 40 KHz	≥ 65 40 - 320 KHz	≤ -70	23x11	2
AHDL-109 ⁵	1168	3:1	2.0 mH	≥ 12 40 - 320 KHz	< 1.0 40 KHz	≥ 65 40 - 320 KHz	≤ -70	23x11	2
AHDL-110 ⁸	272	1:1:1CT	8.0 mH	≥ 15 9 - 40 KHz	< 1.0 40 KHz	≥ 65 40 - 320 KHz	≤ -70	23x11	3
AHDL-111 ⁸	416	1:1:1CT	5.0 mH	≥ 16.5 20 - 80 KHz	< 1.0 40 KHz	≥ 65 40 - 320 KHz	≤ -70	23x11	3
AHDL-112 ⁸	528	1:1:1CT	3.5 mH	≥ 16.5 33 - 200 KHz	< 1.0 40 KHz	≥ 65 40 - 320 KHz	≤ -70	23x11	3
AHDL-201 ¹⁰	1168	4:1	2.0 mH	≥ 15.5 40 - 500 KHz	< 1.0 40 KHz	≥ 50 40 - 500 KHz	≤ -80	EP13	2
AHDL-202 ²	784	1:1:1	3.0 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	EP13	2
AHDL-203 ⁴	1168	1:1:1	2.0 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	EP13	2
AHDL-204 ⁵	1168	2.3:1	2.0 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	EP13	2
AHDL-205 ⁵	784	1.8:1CT	3.0 mH	≥ 16.5 40 - 320 KHz	< 1.0 40 KHz	≥ 50 40 - 320 KHz	≤ -70	EP13	2
AHDL-206 ⁷	2320	1:1:1	1.0 mH	≥ 16.5 80 - 580 KHz	< 1.0 40 KHz	≥ 55 40 - 320 KHz	≤ -70	EP13	2
AHDL-207 ⁵	1552	2.3:1CT	1.6 mH	≥ 16.5 20 - 560 KHz	< 1.0 40 KHz	≥ 55 20 - 320 KHz	≤ -70	EP13	2
AHDL-211	784	1:3.7	3.0 mH	≥ 14 20 - 500 KHz	< 0.5 40 KHz	≥ 50 40 - 300 KHz	≤ -80	EP13	5

NOTES: See facing page




29 Journey • Aliso Viejo, CA 92656 • USA
(949) 448-7070 • FAX: (949) 448-8484

E-MAIL: abinfo@abracon.com • INTERNET ADDRESS: www.abracon.com

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED

DATA COMMUNICATIONS TRANSFORMERS

HDSL SERIES



Test Conditions:

- A. OCL: 100 mVRMS @ 10 KHz with appropriate I_{DC}
 B. THD: 6 Vp-p @ 5 KHz with 135 Ω


- C. Longitudinal Balance: frequency range specified with 135 Ω
 D. DWV: 1,500 VRMS, greater voltage isolation available

Notes:


- * P/Ns with "S" as suffix are configured for surface mountable applications meeting standard industry reflow criteria
 **"CT" indicates a center-tapped winding, otherwise readings are intended to be across entire winding segment

1. Supports Level One SK70704/20/21 with DCR $\leq 3.2/6.0 \Omega$ I_{DC} @ 75 mA
2. Supports Conexant BT8921/70 with DCR $\leq 2.0/2.0 \Omega$, I_{DC} @ 70 mA
3. Supports Conexant BT8952 with DCR $\leq 2.2/4.4 \Omega$, I_{DC} @ 160 mA
4. Supports Conexant BT8952 with DCR $\leq 2.2/4.4 \Omega$, I_{DC} @ 160 mA
5. Supports Level One SK70740/70741/70742 with DCR $\leq 2.2/2.2 \Omega$, I_{DC} @ 70mA
6. Supports Level One SK70704 with DCR $\leq 3.2/2.0 \Omega$, IDC @ 75 mA, assumes pins 7-9 shorted externally
7. Supports Broadcom BCM6010 and Conexant BT8921/70, assumes pins 2 - 3, 7 - 9 are tied externally
8. Supports Conexant BT8960
9. Supports Conexant BT8970/RS8973
10. Supports M/SHDSL Globespan chip set
11. Dimensions: inches / mm; see spec sheet for tolerance limits
12. Specifications subject to change without notice

PHYSICAL CHARACTERISTICS ¹¹



CIRCUITS



ABRACON IS
 ISO 9001 / QS 9000
 CERTIFIED

29 Journey • Aliso Viejo, CA 92656 • USA
 (949) 448-7070 • Fax: (949) 448-8484
 E-MAIL: abinfo@abracon.com • INTERNET ADDRESS: www.abracon.com

ABRACON

 CORPORATION