





spec ref	* PART NO. DIM "A" DESCRIPTION			dr	MAGGIE WU	02/17/03	projection	MM	size	A4	scale	0.500
tolerance	10023061-5	4.00	1.8V	Su-Hua Miao	2010/11/03				ecn no			
	10023061-2	3.00	1.8V	Nickor Zuo	2011/08/25				rel level			
	10023061-3	5.00	1.8V	Pei-Ming Zheng	2011/08/25		product family		Released ELX-DG-005343-1			
surface	linear	0.X	±		www.fci.com cat. no.			dwg no	10025001		N	
		0.XX	±									
		0.XXX	±									
	angular	0°	±°	Product - Customer Drw				sheet 1 of				



spec ref *				dr MAGGIE WU		02/17/03		projection 		MM		size A4		scale 1.000	
tolerance std				Su-Hua Miao - 2010/11/03								ecn no *			
TOLERANCES UNLESS OTHERWISE SPECIFIED				Nickor Zuo - 2011/08/25								rel level		Released ELX-DG-005343-1	
surface ✓				Pei-Ming Zheng - 2011/08/25				product family		dwg no		10025001		N	
linear															
0.X ±															
0.XX ±															
0.XXX ±															
angular 0° ±0				www.fci.com		cat. no.		*		Product - Customer Drw		sheet 2 of			



Copyright FCI.

10023061 - □ □ □ □ □

STYLE : MECHANICAL KEYING

1 : 1.8 VOLT. W/ CENTER KEY#1
2 : 2.5 VOLT. W/ LEFT KEY#1
3 : X.X VOLT. W/ RIGHT KEY#1

COLOR OF HOUSING

0 : BLACK HOUSING
1 : BLUE HOUSING

TAIL LENGTH

CODE	DIM "B"
0	2.54
1	2.67
2	3.18

PLATING

CODE	CONTACT	SOLDERTAIL	UNDERPLATE
1	10u" (0.25um) MIN. GOLD	100u" (2.54um) MIN. TIN/LEAD	50u" (1.27um) MIN. NICKEL OVERALL
2	15u" (0.38um) MIN. GOLD		
3	30u" (0.76um) MIN. GOLD		
4	3u" (0.076um) MIN. GOLD		
6LF	10u" (0.25um) MIN. GOLD	100u" (2.54um) MIN. 100% TIN	50u" (1.27um) MIN. NICKEL OVERALL
7LF	15u" (0.38um) MIN. GOLD		
8LF	30u" (0.76um) MIN. GOLD		
9LF	3u" (0.076um) MIN. GOLD		

COLOR OF EJECTOR


0 : IVORY EJECTOR
2 : BLACK EJECTOR

NOTES:

1. MATERIAL:
HOUSING: HIGH PERFORMANCE RESINS, GLASS FILLED UL94V-0 RATED.
EJECTOR: HIGH PERFORMANCE RESINS, GLASS FILLED UL94V-0 RATED.
TERMINAL: PHOSPHOR BRONZE
2. FCI LOGO TO BE APPROXIMATELY LOCATED AS SHOWN ON PRINT.
3. PRODUCT SPECIFICATION: GS-12-251.
4. PACKAGING SPECIFICATION: GS-14-899.
5. THE DATE CODE IS SHOWN "MM-DD-YY".
6. DIMENSION MARKED "■" NEED CPK>1.5

spec ref	*	dr	MAGGIE WU	02/17/03	projection	MM	size	A4	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	Su-Hua Miao	2010/11/03				ecn no	*	rel level	
		Nickor Zuo	2011/08/25							
surface	linear	0.X	±	Pei-Ming Zheng	2011/08/25	dwg no	10023061	Released		
		0.XX	±					N		
		0.XXX	±					N		
angular	0°	±°		www.fci.com	cat. no.	*	Product - Customer Drw		sheet 3 of	

Print File - REV C - 2009-06-09



Copyright FCI.

PRODUCT NO.	DIM "B"	HOUSING PART NO.	HOUSING COLOR	TERMINAL PART NO.	EJECTOR PART NO.	EJECTOR COLOR	DESCRIPTION
10023061-1000*	2.54	10023062-10040	BLACK	10023056-200*	10023057-001	IVORY	FOR 1.8 VOLT.
10023061-1010*	2.67			10023056-201*			
10023061-1020*	3.18			10023056-203*			
10023061-1002*	2.54			10023056-200*	10023057-002	BLACK	
10023061-1012*	2.67			10023056-201*			
10023061-1022*	3.18			10023056-202*			
10023061-1100*	2.54	10023062-10140	BLUE	10023056-200*	10023057-001	IVORY	
10023061-1110*	2.67			10023056-201*			
10023061-1120*	3.18			10023056-202*			
10023061-2000*	2.54	10023062-20040	BLACK	10023056-200*	10023057-001	IVORY	FOR 2.5 VOLT.
10023061-2010*	2.67			10023056-201*			
10023061-2020*	3.18			10023056-202*			
10023061-2002*	2.54			10023056-200*	10023057-001	BLACK	
10023061-2012*	2.67			10023056-201*			
10023061-2022*	3.18			10023056-202*			
10023061-2100*	2.54	10023062-20140	BLUE	10023056-200*	10023057-002	IVORY	
10023061-2110*	2.67			10023056-201*			
10023061-2120*	3.18			10023056-202*			
10023061-3000*	2.54	10023062-30040	BLACK	10023056-200*	10023057-001	IVORY	FOR X.X VOLT.
10023061-3010*	2.67			10023056-201*			
10023061-3020*	3.18			10023056-202*			
10023061-3002*	2.54			10023056-200*	10023057-001	BLACK	
10023061-3012*	2.67			10023056-201*			
10023061-3022*	3.18			10023056-202*			
10023061-3100*	2.54	10023062-30140	BLUE	10023056-200*	10023057-002	IVORY	
10023061-3110*	2.67			10023056-201*			
10023061-3120*	3.18			10023056-202*			

REMARK: spec ref. PROD. NO. MARK "*" SEE ABOVE PART NO. PLATING CODE DESCR. 021/10N/03 2. TERMINAL PART NO. MARK "*" SHOULD BE THE SAME AS IN PRODUCT PART NO..				projection 		MM 		size A4		scale 1.000	
TOLERANCES UNLESS OTHERWISE SPECIFIED				Su-Hua Miao 2010/11/03 Nickor Zuo 2011/08/25		product family		ecn no *		rel level	
surface ✓	linear	0.X	±		2011/08/25	dwg no	10023000				
		0.XX	±				Released				
		0.XXX	±				N				
angular	0°	±°	www.fci.com		cat. no.	*		Product - Customer Drw		sheet 4 of	

Print File - REV C - 2009-06-09