

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - By -				ALL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
G		86		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A2	REVISED PER ECO-11-004917	11MAR11	RK	HMR

AMP
WIRE RANGE

22-16 AWG
SOLID OR STRANDED

SERRATIONS

INSULATION

SLEEVE

.031 MIN

.094

1.125 MAX

.484 MIN

.033 MAX


3

1 BODY - COPPER PER ASTM B-152
SLEEVE - COPPER PER ASTM B-152
INSULATION - NYLON

2 BODY - TIN PLATE PER ASTM B-545
SLEEVE - TIN PLATE PER ASTM B-545
INSULATION - COLOR , RED

3 DIMENSION APPLIES FROM EDGE OF
METAL WIRE BBL TO FLANGE

4 WIRE INSULATION DIA .080 TO .125

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 24FEB10		 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300V MAX		DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:					CHK TOM MICHELUTTI 24FEB10
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 0.26-1.65mm²[509-3,260] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± .008 3 PLC ± - 4 PLC ± - ANGLES ± 5°		APVD TOM MICHELUTTI 24FEB10		NAME TERMINAL, TAB, PIDG, WIRE SIZE 22-16	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL		FINISH		PRODUCT SPEC			
						1		2		APPLICATION SPEC		A300779C-150730	
										WEIGHT -		CUSTOMER DRAWING SCALE 5:1 SHEET 1 OF 1 REV A2	