




No. OF CCTS.	C	D	No. OF CCTS.	C	D
14	(51.51 ± 0.36) $2.028 \pm .014$	(55.37 ± 0.36) $2.180 \pm .014$	2	(3.96 ± 0.13) $.156 \pm .005$	(7.82 ± 0.25) $.308 \pm .010$
15	(55.47 ± 0.36) $2.184 \pm .014$	(59.33 ± 0.36) $2.336 \pm .014$	3	(7.92 ± 0.13) $.312 \pm .005$	(11.79 ± 0.25) $.464 \pm .010$
16	(59.44 ± 0.36) $2.340 \pm .014$	(63.30 ± 0.36) $2.492 \pm .014$	4	(11.89 ± 0.13) $.468 \pm .005$	(15.75 ± 0.25) $.620 \pm .010$
17	(63.40 ± 0.36) $2.496 \pm .014$	(67.26 ± 0.36) $2.648 \pm .014$	5	(15.85 ± 0.13) $.624 \pm .005$	(19.71 ± 0.25) $.776 \pm .010$
18	(67.36 ± 0.36) $2.652 \pm .014$	(71.22 ± 0.36) $2.804 \pm .014$	6	(19.81 ± 0.13) $.780 \pm .005$	(23.67 ± 0.25) $.932 \pm .010$
19	(71.32 ± 0.36) $2.808 \pm .014$	(75.18 ± 0.36) $2.960 \pm .014$	7	(23.77 ± 0.13) $.936 \pm .005$	(27.64 ± 0.31) $1.088 \pm .012$
20	(75.29 ± 0.36) $2.964 \pm .014$	(79.15 ± 0.46) $3.116 \pm .018$	8	(27.74 ± 0.25) $1.092 \pm .010$	(31.60 ± 0.31) $1.244 \pm .012$
			9	(31.70 ± 0.25) $1.248 \pm .010$	(35.56 ± 0.31) $1.400 \pm .012$
			10	(35.66 ± 0.25) $1.404 \pm .010$	(39.52 ± 0.31) $1.556 \pm .012$
			11	(39.62 ± 0.25) $1.560 \pm .010$	(43.48 ± 0.31) $1.712 \pm .012$
			12	(43.59 ± 0.25) $1.716 \pm .010$	(47.45 ± 0.31) $1.868 \pm .012$
			13	(47.55 ± 0.31) $1.872 \pm .012$	(51.41 ± 0.36) $2.024 \pm .014$

- NOTES:
- 1) SIMILAR TO 2139-N EXCEPT WITH POLARIZING PEG.
 - 2) FOR USE WITH TERMINAL No. 2478 OR 2578
 - 3) ASSEMBLED CONNECTOR MATES WITH (.14)/.045 SQUARE OR ROUND PIN.
 - 4) EXTENDED PIN ENTRY WINDOWS ARE POSSIBLE.

ENG. No. DESIGNATION

3069 - A N 2 P

"A" DESIGNATES NYLON 6/6, 94V-0 COLOUR RED
"BLANK" DESIGNATES NYLON 6/6
"B" DESIGNATES NYLON 6/6, 94V-0 COLOUR WHITE

"P" INDICATES HOUSING WITH PEG
"BLANK" INDICATES HOUSING WITHOUT PEG.

"2" INDICATES HOUSING WITHOUT RAMP
"BLANK" INDICATES HOUSING WITH RAMP

NO. OF CKT'S

CORRECT TEXT LOC EC NO: E2007-0720 DRAWN: DWASZK LEW CZ 2007/03/28 CHK'D: D. MORIARTY 2007/03/29 APPR: J. DENNEY 2007/04/04	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY SM	DATE 1990/04/06	TITLE HOUSING, KK CONNECTOR (3.96)/.156 CRIMP PEG/VOID OPTIONAL MOLEX INCORPORATED			
			4 PLACES	± ---	± ---	CHECKED BY E. FOLAN	DATE 2000/08/30				
			3 PLACES	± ---	± .010	APPROVED BY MWILHITE	DATE 2000/08/30				
			2 PLACES	± 0.25	± .014	DOCUMENT NO. SD-3069-N***					
			1 PLACE	± 0.35	± ---	SHEET NO. 1 OF 2					
			ANGULAR ± 2 °			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								

