



Contact assignment:

- 1 brown
- 3 blue
- 4 black



Contact assignment:

- 1 brown
- 2 white
- 3 blue
- 4 black



Technical specification:


Rated voltage: IEC 61076-2-104	3pos 4pos 60 V 30V
Current rating: IEC 61076-2-104	3pos 4pos 3A at 40°C 3A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PA6, UL 94
Sealing:	NBR
Socket housing:	CuZn, nickel plated
Grouting:	Polyurethane-resin, UL 94

Installation specification:

Recommended torque:	0,6 - 0,8 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 10: 36-000270



Minimum wall thickness
1,5mm, alternativ panel
cut-out d=8,2

Part no:	Description:	Pos	Length L:	Wire:
42-01034	SAL - 8 - FSH3 - 0,2	3	0,2m	AWG 24 PVC, UL
42-xxxxx	SAL - 8 - FSH3 - ...	3	x	
42-01035	SAL - 8 - FSH4 - 0,2	4	0,2m	
42-xxxxx	SAL - 8 - FSH4 - ...	4	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: c 20.12.11 dbu Ä4186 data sheet revised		 dim. in mm		title: Male socket M8x1 with wire, backmounting
			date	name	
	tolerance of wire: L <= 0,5m: L + 20mm L > 0,5m: L + 4%	drawn	27.10.09	Burschik	dwg no: 42K1A153
		appd.	27.10.09	Schmidt	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					