




features

- Flameproof coating is available (specify "CFP")
- Reduced body size (specify "CFS/CFPS")
- Suitable for automatic machine insertion
- Marking: Venetian red with color-coded bands on CF
Green body color with color-coded bands on CFP
Ivory body color with color-coded bands on CFS1/4
- Products with lead-free terminations meet EU RoHS and China RoHS requirements

dimensions and construction



Type	Dimensions inches (mm)				I**	
	L	C (max.)	D	d (nom.)	Standard	Long
CFS1/4 CFPS1/4	.126±.008 (3.2±0.2)	.134 (3.4)	.067±.008 (1.7±0.2)	.018 (0.45)	.551 Min.* (14.0 Min.)	.787 Min.*** (20.0 Min.)
CF1/4 CFP1/4	.240±0.2 (6.1±0.5)	.280 (7.1)	.092±.012 (2.3±0.3)	.024 (0.6)	.787 Min. (20.0 Min.)	—
CFS1/2 CFPS1/2	.248±.02 (6.3±0.5)	.280 (7.1)	.112±.012 (2.85±0.3)	.024 (0.6)		

* Forming code S is applied for bulk type.

** Lead length changes depending on taping and forming type.

*** Long type is custom-made

ordering information

New Part #	CF	1/4	C	T52	R	103	J
	Type	Power Rating	Termination Material	Taping and Forming	Packaging	Nominal Resistance	Tolerance
	CF CFP	S1/4: 0.25W 1/4: 0.25W S1/2: 0.5W	C: SnCu	Axial: T26, T52, L52 Radial: VT, MT, MHT, VTP, VTE U Forming: U, UCL M Forming: M5, M10, M12.5 L Forming: L10, L12.5	A: Ammo R: Reel	2 significant figures + 1 multiplier "R" indicates decimal on value <10Ω	G: ±2% J: ±5%

For further information
on packaging, please refer
to Appendix C.


applications and ratings

Part Designation	Power Rating @ 70°C	Minimum Dielectric Withstanding Voltage	T.C.R. (ppm/°C)				Resistance Range E-24 (G±2%)	Resistance Range E-24 (J±5%)	Absolute Maximum Working Voltage	Absolute Maximum Overload Voltage
			+350 to -450	0 to -700	0 to -1000	0 to -1300				
CFS1/4	0.25W	300V	2.2Ω - 47kΩ	51kΩ - 100kΩ	110kΩ - 330kΩ	360kΩ - 1MΩ	10Ω - 330kΩ	2.2Ω - 1MΩ	250V	500V
CFPS1/4			2.2Ω - 47kΩ	51kΩ - 100kΩ	110kΩ - 330kΩ	360kΩ - 1MΩ	10Ω - 100kΩ	2.2Ω - 1MΩ		
CF1/4		500V	2.2Ω - 100kΩ	110kΩ - 330kΩ	360kΩ - 1MΩ	1.1MΩ - 5.1MΩ	10Ω - 1MΩ	2.2Ω - 5.1MΩ	300V	600V
CFP1/4			2.2Ω - 100kΩ	110kΩ - 330kΩ	360kΩ - 1MΩ	—		2.2Ω - 1MΩ		
CFS1/2	0.50W	700V	1.0Ω - 91kΩ	100kΩ - 1MΩ	1.1MΩ - 2.2MΩ	2.4MΩ - 5.1MΩ		1.0Ω - 5.1MΩ	350V	700V
CFPS1/2			2.2Ω - 91kΩ		—	—		2.2Ω - 1MΩ		

Operating temperature: -55°C ~ +155°C


environmental applications

Derating Curve




For resistors operated at an ambient temperature of 70°C or above, a power rating shall be derated in accordance with the above derating curve.

Surface Temperature Rise



Load Life @ 70°C, 1000 Hr



Performance Characteristics

Parameter	Requirement Limit	Δ R ±(% + 0.05Ω) Typical	Test Method
Resistance	Within specified tolerance	—	Measuring points are at 10mm ±1mm from the end cap.
T.C.R.	Within specified T.C.R.	—	Room temperature +100°C
Overload (Short time)	±1%	±0.5%	Rated voltage x 2.5 or max. overload voltage for 5 seconds, whichever is lower
Resistance to Solder Heat	±1%	±0.5%	260°C ±5°C, 10 seconds ± 1 second
Terminal Strength	No lead-coming off and loose terminals	—	Twist 360°C, 5 times
Rapid Change of Temperature	±1%	±0.5%	-55°C (30 minutes), +125°C (30 minutes), 5 cycles
Moisture Resistance	±5%	±2.5%	40°C ± 2°C, 90 - 95% RH, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 70°C	±3%	±1.5%	70°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Resistance to Solvent (CFS & CFPS only)	No abnormality in appearance. Marking shall be easily legible.	—	Ultrasonic washing with Isopropyl alcohol for 2 minutes. Power: 0.3W/cm², f: 28kHz, temp: 35°C±5°C
Flame Retardant (CFS & CFPS only)	No evidence of flaming or self-flaming	—	Flame test: The test flame shall be applied and removed for each 15 seconds respectively to repeat the cycle 5 times. Overload flame retardant: Power (AC) corresponding to 2, 4, 8, 16 and 32 times the power rating shall be applied for each 1 minute until disconnection occurs. However the applied voltage shall not exceed 4 times the maximum operating voltage.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KOA Speer:

[CF1/2LT52R3R3J](#) [CF1/2L201J](#) [CF1/2L204J](#) [CF1/2L203J](#) [CF1/2L3R0J](#) [CF1/2L200J](#) [CF1/2L205J](#) [CF1/2L202J](#)
[CF1/2L915J](#) [CF1/2LT52R183J](#) [CF1/2L911J](#) [CF1/2L913J](#) [CF1/2L912J](#) [CF1/2L910J](#) [CF1/2LT52R122J](#)
[CF1/2LT52R1R1J](#) [CF1/2L5R6J](#) [CF1/2LT52R1R5J](#) [CF1/2LT52R124J](#) [CF1/2LT52R913J](#) [CF1/2L165J](#)
[CF1/2LT52R911J](#) [CF1/2LT52R7R5J](#) [CF1/2LT52R165J](#) [CF1/2LT52R163J](#) [CF1/2L161J](#) [CF1/2L182J](#) [CF1/2L5R1J](#)
[CF1/2L180J](#) [CF1/2L184J](#) [CF1/2L113J](#) [CF1/2LT52R750J](#) [CF1/2LT52R752J](#) [CF1/2LT52R754J](#) [CF1/2LT52R751J](#)
[CF1/2LT52R755J](#) [CF1/2L434J](#) [CF1/2L430J](#) [CF1/2L132J](#) [CF1/2L130J](#) [CF1/2L754J](#) [CF1/2L752J](#) [CF1/2L750J](#)
[CF1/2LT52R5R6J](#) [CF1/2LT52R391J](#) [CF1/2LT52R390J](#) [CF1/2LT52R393J](#) [CF1/2LT52R392J](#) [CF1/2LT52R270J](#)
[CF1/2LT52R395J](#) [CF1/2LT52R394J](#) [CF1/2LT52R274J](#) [CF1/2LT52R273J](#) [CF1/2LT52R275J](#) [CF1/2LT52R272J](#)
[CF1/2LT52R271J](#) [CF1/2L206J](#) [CF1/2LT52R153J](#) [CF1/2LT52R153G](#) [CF1/2LT52R155J](#) [CF1/2LT52R150J](#)
[CF1/2LT52R151J](#) [CF1/2L515J](#) [CF1/2LT52R152J](#) [CF1/2L511J](#) [CF1/2LT52R156J](#) [CF1/2LR50J](#) [CF1/2L225J](#)
[CF1/2L2R0J](#) [CF1/2L221J](#) [CF1/2L2R2J](#) [CF1/2L223J](#) [CF1/2L824J](#) [CF1/2LT52R130J](#) [CF1/2LT52R132J](#)
[CF1/2LT52R134J](#) [CF1/2L820J](#) [CF1/2L822J](#) [CF1/2L105J](#) [CF1/2L103J](#) [CF1/2L101J](#) [CF1/2L183J](#) [CF1/2L186J](#)
[CF1/2L562J](#) [CF1/2LT52R565J](#) [CF1/2L160J](#) [CF1/2L564J](#) [CF1/2LT52R563J](#) [CF1/2L164J](#) [CF1/2LT52R512J](#)
[CF1/2LT52R514J](#) [CF1/2LT52R511J](#) [CF1/2LT52R824J](#) [CF1/2L152J](#) [CF1/2LT52R510J](#) [CF1/2LT52R513J](#)
[CF1/2LT52R515J](#) [CF1/2LT52R226J](#) [CF1/2LT52R225J](#) [CF1/2LT52R223J](#)