

## FEATURES:

- **Organized as 128K x8 / 256K x8 / 512K x8**
- **2.7-3.6V Read Operation**
- **Superior Reliability**
  - Endurance: At least 1000 Cycles
  - Greater than 100 years Data Retention
- **Low Power Consumption:**
  - Active Current: 10 mA (typical)
  - Standby Current: 2  $\mu$ A (typical)
- **Fast Read Access Time:**
  - 70 ns
- **Latched Address and Data**
- **Fast Byte-Program Operation:**
  - Byte-Program Time: 15  $\mu$ s (typical)
  - Chip Program Time:
    - 2 seconds (typical) for GLS37VF010
    - 4 seconds (typical) for GLS37VF020
    - 8 seconds (typical) for GLS37VF040
- **Electrical Erase Using Programmer**
  - Does not require UV source
  - Chip-Erase Time: 100 ms (typical)
- **CMOS I/O Compatibility**
- **JEDEC Standard Byte-wide Flash EEPROM Pinouts**
- **Packages Available**
  - 32-lead PLCC
  - 32-lead TSOP (8mm x 14mm)
  - 32-pin PDIP
  - Non-Pb (lead-free) packages available

## PRODUCT DESCRIPTION

The GLS37VF010/020/040 devices are 128K x8 / 256K x8 / 512K x8 CMOS, Many-Time Programmable (MTP), low cost flash, manufactured with high performance Super-Flash technology. The split-gate cell design and thick-oxide tunneling injector attain better reliability and manufacturability compared with alternate approaches. The GLS37VF010/020/040 can be electrically erased and programmed at least 1000 times using an external programmer, e.g., to change the contents of devices in inventory. The GLS37VF010/020/040 have to be erased prior to programming. These devices conform to JEDEC standard pinouts for byte-wide flash memories.

Featuring high performance Byte-Program, the GLS37VF010/020/040 provide a typical Byte-Program time of 15  $\mu$ s. Designed, manufactured, and tested for a wide spectrum of applications, these devices are offered with an endurance of at least 1000 cycles. Data retention is rated at greater than 100 years.

The GLS37VF010/020/040 are suited for applications that require infrequent writes and low power nonvolatile storage. These devices will improve flexibility, efficiency, and performance while matching the low cost in nonvolatile applications that currently use UV-EPROMs, OTPs, and mask ROMs.

To meet surface mount and conventional through hole requirements, the GLS37VF010/020/040 are offered in 32-lead PLCC, 32-lead TSOP, and 32-pin PDIP packages. See Figures 2, 3, and 4 for pin assignments.

## Device Operation

The GLS37VF010/020/040 devices are nonvolatile memory solutions that can be used instead of standard flash devices if in-system programmability is not required. It is functionally (Read) and pin compatible with industry standard flash products. The device supports electrical Erase operation via an external programmer.

## Read

The Read operation of the GLS37VF010/020/040 is controlled by CE# and OE#. Both CE# and OE# have to be low for the system to obtain data from the outputs. Once the address is stable, the address access time is equal to the delay from CE# to output ( $T_{CE}$ ). Data is available at the output after a delay of TOE from the falling edge of OE#, assuming the CE# pin has been low and the addresses have been stable for at least  $T_{CE}-T_{OE}$ . When the CE# pin is high, the chip is deselected and a standby current of only 2  $\mu$ A (typical) is consumed. OE# is the output control and is



### Data Sheet

used to gate data from the output pins. The data bus is in high impedance state when either CE# or OE# is  $V_{IH}$ . Refer to Figure 5 for the timing diagram.

### Byte-Program Operation

The GLS37VF010/020/040 are programmed by using an external programmer. The programming mode is activated by asserting 11.4-12V on OE# pin and  $V_{IL}$  on CE# pin. The device is programmed using a single pulse (WE# pin low) of 15  $\mu$ s per byte. Using the MTP programming algorithm, the Byte-Program process continues byte-by-byte until the entire chip has been programmed. Refer to Figure 11 for the flowchart and Figure 7 for the timing diagram.

### Chip-Erase Operation

The only way to change a data from a “0” to “1” is by electrical erase that changes every bit in the device to “1”. The GLS37VF010/020/040 use an electrical Chip-Erase operation. The entire chip can be erased in 100 ms (WE# pin low). In order to activate erase mode, the 11.4-12V is applied to OE# and  $A_9$  pins while CE# is low. All other address and data pins are “don’t care”. The falling edge of WE# will start the Chip-Erase operation. Once the chip has been erased, all bytes must be verified for FFH. Refer to Figure 10 for the flowchart and Figure 6 for the timing diagram.

### Product Identification Mode

The Product Identification mode identifies the devices as GLS37VF010, GLS37VF020, and GLS37VF040 and manufacturer as Greenliant. This mode may be accessed by the hardware method. To activate this mode, the programming equipment must force  $V_H$  (11.4-12V) on address  $A_9$ . Two identifier bytes may then be sequenced from the device outputs by toggling address line  $A_0$ . For details, see Table 3 for hardware operation.

**TABLE 1: Product Identification**


|                   | Address | Data |
|-------------------|---------|------|
| Manufacturer's ID | 0000H   | BFH  |
| Device ID         |         |      |
| GLS37VF010        | 0001H   | C5H  |
| GLS37VF020        | 0001H   | C6H  |
| GLS37VF040        | 0001H   | C2H  |

T1.2 1151

### Design Considerations

The GLS37VF010/020/040 should have a 0.1  $\mu$ F ceramic high frequency, low inductance capacitor connected between  $V_{DD}$  and GND. This capacitor should be placed as close to the package terminals as possible.

OE# and  $A_9$  must remain stable at  $V_H$  for the entire duration of an Erase operation. OE# must remain stable at  $V_H$  for the entire duration of the Program operation.



**FIGURE 1: Functional Block Diagram**




FIGURE 2: Pin Assignments for 32-lead PLCC





FIGURE 3: Pin Assignments for 32-lead TSOP (8mm x 14mm)



### Data Sheet



**FIGURE 4: Pin Assignments for 32-pin PDIP**

**TABLE 2: Pin Description**

| Symbol         | Pin Name          | Functions                                                                                                                             |
|----------------|-------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| $A_{MS}^1-A_0$ | Address Inputs    | To provide memory addresses.                                                                                                          |
| $DQ_7-DQ_0$    | Data Input/output | To output data during Read cycles and receive input data during Program cycles. The outputs are in tri-state when OE# or CE# is high. |
| CE#            | Chip Enable       | To activate the device when CE# is low.                                                                                               |
| WE#            | Write Enable      | To program or erase (WE# = $V_{IL}$ pulse during Program or Erase)                                                                    |
| OE#            | Output Enable     | To gate the data output buffers during Read operation when low                                                                        |
| $V_{DD}$       | Power Supply      | To provide 3.0V supply (2.7-3.6V)                                                                                                     |
| $V_{SS}$       | Ground            |                                                                                                                                       |
| NC             | No Connection     | Unconnected pins.                                                                                                                     |

T2.1 1151

1.  $A_{MS}$  = Most significant address

$A_{MS}$  =  $A_{16}$  for GLS37VF010,  $A_{17}$  for GLS37VF020, and  $A_{18}$  for GLS37VF040

**TABLE 3: Operation Modes Selection**

| Mode                   | CE#      | WE#      | $A_9$    | OE#                  | DQ                                                | Address                                                                                  |
|------------------------|----------|----------|----------|----------------------|---------------------------------------------------|------------------------------------------------------------------------------------------|
| Read                   | $V_{IL}$ | $V_{IH}$ | $A_{IN}$ | $V_{IL}$             | $D_{OUT}$                                         | $A_{IN}$                                                                                 |
| Output Disable         | $V_{IL}$ | X        | X        | $V_{IH}$             | High Z                                            | $A_{IN}$                                                                                 |
| Standby                | $V_{IH}$ | X        | X        | X                    | High Z                                            | X                                                                                        |
| Chip-Erase             | $V_{IL}$ | $V_{IL}$ | $V_H$    | $V_H$                | High Z                                            | X                                                                                        |
| Byte-Program           | $V_{IL}$ | $V_{IL}$ | $A_{IN}$ | $V_H$                | $D_{IN}$                                          | $A_{IN}$                                                                                 |
| Program/Erase Inhibit  | X        | $V_{IH}$ | X        | X                    | High Z                                            | X                                                                                        |
|                        | X        | X        | X        | $V_{IL}$ or $V_{IH}$ | High Z/ $D_{OUT}$                                 | X                                                                                        |
| Product Identification | $V_{IL}$ | $V_{IH}$ | $V_H$    | $V_{IL}$             | Manufacturer's ID (BFH)<br>Device ID <sup>1</sup> | $A_{MS}^2 - A_1 = V_{IL}$ , $A_0 = V_{IL}$<br>$A_{MS}^2 - A_1 = V_{IL}$ , $A_0 = V_{IH}$ |

T3.2 1151

1. Device ID = C5H for GLS37VF020, C6H for GLS37VF020, and C2H for GLS37VF040

2.  $A_{MS}$  = Most significant address

$A_{MS}$  =  $A_{16}$  for GLS37VF010,  $A_{17}$  for GLS37VF020, and  $A_{18}$  for GLS37VF040

**Note:** X =  $V_{IL}$  or  $V_{IH}$  (or  $V_H$  in case of OE# and  $A_9$ )

$V_H$  = 11.4-12V

**Absolute Maximum Stress Ratings** (Applied conditions greater than those listed under “Absolute Maximum Stress Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these conditions or conditions greater than those defined in the operational sections of this data sheet is not implied. Exposure to absolute maximum stress rating conditions may affect device reliability.)

Temperature Under Bias . . . . . -55°C to +125°C  
 Storage Temperature . . . . . -65°C to +150°C  
 D. C. Voltage on Any Pin to Ground Potential . . . . . -0.5V to  $V_{DD}+0.5V$   
 Transient Voltage (<20 ns) on Any Pin to Ground Potential . . . . . -2.0V to  $V_{DD}+2.0V$   
 Voltage on  $A_9$  Pin to Ground Potential . . . . . -0.5V to 13.2V  
 Package Power Dissipation Capability ( $T_A = 25^\circ C$ ) . . . . . 1.0W  
 Through Hole Lead Soldering Temperature (10 Seconds) . . . . . 300°C  
 Surface Mount Solder Reflow Temperature: . . . . . “with-Pb” units<sup>1</sup>: 240°C for 3 seconds  
 . . . . . “non-Pb” units: 260°C for 3 seconds  
 Output Short Circuit Current<sup>2</sup> . . . . . 50 mA

1. Certain “with-Pb” package types are capable of 260°C for 3 seconds; please consult the factory for the latest information.
2. Outputs shorted for no more than one second. No more than one output shorted at a time.

#### OPERATING RANGE

| Range      | Ambient Temp | $V_{DD}$ |
|------------|--------------|----------|
| Commercial | 0°C to +70°C | 2.7-3.6V |

#### AC CONDITIONS OF TEST

|                                |                |
|--------------------------------|----------------|
| Input Rise/Fall Time . . . . . | 5 ns           |
| Output Load . . . . .          | $C_L = 100$ pF |
| See Figures 8 and 9            |                |

**TABLE 4: Read Mode DC Operating Characteristics  $V_{DD}=2.7-3.6V$  ( $T_A = 0^\circ C$  to +70°C (Commercial))**

| Symbol    | Parameter                      | Limits       |     |         | Test Conditions                                                                                                                 |
|-----------|--------------------------------|--------------|-----|---------|---------------------------------------------------------------------------------------------------------------------------------|
|           |                                | Min          | Max | Units   |                                                                                                                                 |
| $I_{DD}$  | $V_{DD}$ Read Current          |              | 12  | mA      | Address input= $V_{ILT}/V_{IHT}$ , at $f=1/T_{RC}$ Min<br>$V_{DD}=V_{DD}$ Max<br>$CE\#=V_{IL}$ , $OE\#=V_{IHT}$ , all I/Os open |
| $I_{SB}$  | Standby $V_{DD}$ Current       |              | 15  | $\mu A$ | $CE\#=V_{IHC}$ , $V_{DD}=V_{DD}$ Max                                                                                            |
| $I_{LI}$  | Input Leakage Current          |              | 1   | $\mu A$ | $V_{IN}=GND$ to $V_{DD}$ , $V_{DD}=V_{DD}$ Max                                                                                  |
| $I_{LO}$  | Output Leakage Current         |              | 10  | $\mu A$ | $V_{OUT}=GND$ to $V_{DD}$ , $V_{DD}=V_{DD}$ Max                                                                                 |
| $V_{IL}$  | Input Low Voltage              |              | 0.8 | V       | $V_{DD}=V_{DD}$ Min                                                                                                             |
| $V_{IH}$  | Input High Voltage             | 0.7 $V_{DD}$ |     | V       | $V_{DD}=V_{DD}$ Max                                                                                                             |
| $V_{IHC}$ | Input High Voltage (CMOS)      | $V_{DD}-0.3$ |     | V       | $V_{DD}=V_{DD}$ Max                                                                                                             |
| $V_{OL}$  | Output Low Voltage             |              | 0.2 | V       | $I_{OL}=100$ $\mu A$ , $V_{DD}=V_{DD}$ Min                                                                                      |
| $V_{OH}$  | Output High Voltage            | $V_{DD}-0.3$ |     | V       | $I_{OH}=-100$ $\mu A$ , $V_{DD}=V_{DD}$ Min                                                                                     |
| $I_H$     | Supervoltage Current for $A_9$ |              | 200 | $\mu A$ | $CE\#=OE\#=V_{IL}$ , $A_9=V_H$ Max                                                                                              |

T4.6 1151



### Data Sheet

**TABLE 5: Program/Erase DC Operating Characteristics  $V_{DD}=2.7-3.6V$  ( $T_A = 25^\circ C \pm 5^\circ C$ )**

| Symbol      | Parameter                         | Limits |     |         | Test Conditions                                                                                                                                                                     |
|-------------|-----------------------------------|--------|-----|---------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|             |                                   | Min    | Max | Units   |                                                                                                                                                                                     |
| $I_{DD}$    | $V_{DD}$ Erase or Program Current |        | 20  | mA      | $CE\#=V_{IL}$ , $OE\#=V_H$ , $V_{DD}=V_{DD} \text{ Max}$ , $WE\#=V_{IL}$                                                                                                            |
| $I_{LI}$    | Input Leakage Current             |        | 1   | $\mu A$ | $V_{IN}=GND$ to $V_{DD}$ , $V_{DD}=V_{DD} \text{ Max}$                                                                                                                              |
| $I_{LO}$    | Output Leakage Current            |        | 10  | $\mu A$ | $V_{OUT}=GND$ to $V_{DD}$ , $V_{DD}=V_{DD} \text{ Max}$                                                                                                                             |
| $V_H$       | Supervoltage for $A_9$ and $OE\#$ | 11.4   | 12  | V       | $OE\#=V_H \text{ Max}$ , $A_9=V_H \text{ Max}$ ,<br>$V_{DD}=V_{DD} \text{ Max}$ , $CE\#=V_{IL}$<br>$CE\#=V_{IL}$ , $OE\#=11.4-12V$ ,<br>$V_{DD}=V_{DD} \text{ Max}$ , $WE\#=V_{IL}$ |
| $I_{HA9}$   | Supervoltage Current for $A_9$    |        | 200 | $\mu A$ |                                                                                                                                                                                     |
| $I_{HOE\#}$ | Supervoltage Current for $OE\#$   |        | 3   | mA      |                                                                                                                                                                                     |

T5.2 1151

**TABLE 6: Recommended System Power-up Timings**

| Symbol           | Parameter                   | Minimum | Units   |
|------------------|-----------------------------|---------|---------|
| $T_{PU-READ}^1$  | Power-up to Read Operation  | 100     | $\mu s$ |
| $T_{PU-WRITE}^1$ | Power-up to Write Operation | 100     | $\mu s$ |

T6.1 1151

1. This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

**TABLE 7: Capacitance ( $T_A = 25^\circ C$ ,  $f=1 \text{ Mhz}$ , other pins open)**

| Parameter   | Description         | Test Condition | Maximum |
|-------------|---------------------|----------------|---------|
| $C_{I/O}^1$ | I/O Pin Capacitance | $V_{I/O} = 0V$ | 12 pF   |
| $C_{IN}^1$  | Input Capacitance   | $V_{IN} = 0V$  | 6 pF    |

T7.0 1151

1. This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

**TABLE 8: Reliability Characteristics**

| Symbol      | Parameter      | Minimum Specification | Units  | Test Method         |
|-------------|----------------|-----------------------|--------|---------------------|
| $N_{END}^1$ | Endurance      | 10,000                | Cycles | JEDEC Standard A117 |
| $T_{DR}^1$  | Data Retention | 100                   | Years  | JEDEC Standard A103 |
| $I_{LTH}^1$ | Latch Up       | $100 + I_{DD}$        | mA     | JEDEC Standard 78   |

T8.3 1151

1. This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

## AC CHARACTERISTICS

**TABLE 9: Read Cycle Timing Parameters  $V_{DD} = 2.7-3.6V$  ( $T_A = 0^\circ C$  to  $+70^\circ C$  (Commercial))**

| Symbol      | Parameter                       | GLS37VF010-70<br>GLS37VF020-70<br>GLS37VF040-70 |     | Units |
|-------------|---------------------------------|-------------------------------------------------|-----|-------|
|             |                                 | Min                                             | Max |       |
| $T_{RC}$    | Read Cycle Time                 | 70                                              |     | ns    |
| $T_{CE}$    | Chip Enable Access Time         |                                                 | 70  | ns    |
| $T_{AA}$    | Address Access Time             |                                                 | 70  | ns    |
| $T_{OE}$    | Output Enable Access Time       |                                                 | 35  | ns    |
| $T_{CLZ}^1$ | CE# Low to Active Output        | 0                                               |     | ns    |
| $T_{OLZ}^1$ | OE# Low to Active Output        | 0                                               |     | ns    |
| $T_{CHZ}^1$ | CE# High to High-Z Output       |                                                 | 25  | ns    |
| $T_{OHZ}^1$ | OE# High to High-Z Output       |                                                 | 25  | ns    |
| $T_{OH}^1$  | Output Hold from Address Change | 0                                               |     | ns    |

T9.3 1151


1. This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

**TABLE 10: Program/Erase Cycle Timing Parameters  $V_{DD} = 2.7-3.6V$  ( $T_A = 25^\circ C \pm 5^\circ C$ )**


| Symbol    | Parameter                                    | Min | Max | Units   |
|-----------|----------------------------------------------|-----|-----|---------|
| $T_{BP}$  | Byte-Program Time                            |     | 20  | $\mu s$ |
| $T_{CES}$ | CE# Setup Time                               | 1   |     | $\mu s$ |
| $T_{CEH}$ | CE# Hold Time                                | 1   |     | $\mu s$ |
| $T_{AS}$  | Address Setup Time                           | 1   |     | $\mu s$ |
| $T_{AH}$  | Address Hold Time                            | 1   |     | $\mu s$ |
| $T_{DS}$  | Data Setup Time                              | 1   |     | $\mu s$ |
| $T_{DH}$  | Data Hold Time                               | 1   |     | $\mu s$ |
| $T_{PRT}$ | OE# Rise Time for Program and Erase          | 50  |     | ns      |
| $T_{VPS}$ | OE# Setup Time for Program and Erase         | 1   |     | $\mu s$ |
| $T_{VPH}$ | OE# Hold Time for Program and Erase          | 1   |     | $\mu s$ |
| $T_{PW}$  | WE# Program Pulse Width                      | 15  | 25  | $\mu s$ |
| $T_{EW}$  | WE# Erase Pulse Width                        | 100 | 200 | ms      |
| $T_{VR}$  | OE#/A <sub>9</sub> Recovery Time for Erase   | 1   |     | $\mu s$ |
| $T_{ART}$ | A <sub>9</sub> Rise Time to 12V during Erase | 50  |     | ns      |
| $T_{A9S}$ | A <sub>9</sub> Setup Time during Erase       | 1   |     | $\mu s$ |
| $T_{A9H}$ | A <sub>9</sub> Hold Time during Erase        | 1   |     | $\mu s$ |

T10.1 1151

## Data Sheet



**FIGURE 5: Read Cycle Timing Diagram**



### FIGURE 6: Chip-Erase Timing Diagram







FIGURE 7: Byte-Program Timing Diagram




Data Sheet




AC test inputs are driven at  $V_{IHT}$  ( $0.9 V_{DD}$ ) for a logic “1” and  $V_{ILT}$  ( $0.1 V_{DD}$ ) for a logic “0”. Measurement reference points for inputs and outputs are  $V_{IT}$  ( $0.5 V$ ) and  $V_{OT}$  ( $0.5 V_{DD}$ ). Input rise and fall times ( $10\% \leftrightarrow 90\%$ ) are  $<5$  ns.

**Note:**  $V_{IT}$  -  $V_{INPUT}$  Test  
 $V_{OT}$  -  $V_{OUTPUT}$  Test  
 $V_{IHT}$  -  $V_{INPUT}$  HIGH Test  
 $V_{ILT}$  -  $V_{INPUT}$  LOW Test

**FIGURE 8: AC Input/Output Reference Waveforms**




**FIGURE 9: A Test Load Example**



**FIGURE 10: Chip-Erase Algorithm**



Data Sheet




1151 F09.2

\*See Figure 10

**FIGURE 11: Byte-Program Algorithm**

## PRODUCT ORDERING INFORMATION



1. Environmental suffix "E" denotes non-Pb solder.  
 Greenliant non-Pb solder devices are "RoHS Compliant".

### Valid combinations for GLS37VF010

GLS37VF010-70-3C-NHE   GLS37VF010-70-3C-WHE   GLS37VF010-70-3C-PHE

### Valid combinations for GLS37VF020

GLS37VF020-70-3C-NHE   GLS37VF020-70-3C-WHE   GLS37VF020-70-3C-PHE

### Valid combinations for GLS37VF040

GLS37VF040-70-3C-NHE   GLS37VF040-70-3C-WHE   GLS37VF040-70-3C-PHE


**Note:** Valid combinations are those products in mass production or will be in mass production. Consult your Greenliant sales representative to confirm availability of valid combinations and to determine availability of new combinations.

\* Not recommended for new designs.




Data Sheet

**PACKAGING DIAGRAMS**




**FIGURE 12: 32-lead Plastic Lead Chip Carrier (PLCC)**  
**Greenliant Package Code: NH**



**FIGURE 13: 32-lead Thin Small Outline Package (TSOP) 8mm x 14mm**  
**Greenliant Package Code: WH**



Data Sheet



**FIGURE 14: 32-pin Plastic Dual In-line Pins (PDIP)**  
**Greenliant Package Code: PH**



**TABLE 11: Revision History**

| Number | Description                                                                                                                                                                                                                                                                                                                                                                                             | Date     |
|--------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| 02     | <ul style="list-style-type: none"> <li>2002 Data Book</li> </ul>                                                                                                                                                                                                                                                                                                                                        | Feb 2002 |
| 03     | <ul style="list-style-type: none"> <li>Part number changes - see page 13 for additional information</li> <li>Clarified the Test Conditions for <math>V_{DD}</math> Read Current parameter in Table 4 on page 5                             <ul style="list-style-type: none"> <li>Address input = <math>V_{ILT}/V_{IHT}</math></li> <li><math>CE\#=OE\#=V_{ILT}</math></li> </ul> </li> </ul>           | Mar 2003 |
| 04     | <ul style="list-style-type: none"> <li>2004 Data Book</li> <li>Added non-Pb MPNs and removed footnote (See page 13)</li> </ul>                                                                                                                                                                                                                                                                          | Nov 2003 |
| 05     | <ul style="list-style-type: none"> <li>Removed 90 ns parts, related footnote, and MPNs (See page 13)</li> <li>Added 70 ns parts and MPNs for the PH package</li> <li>Changed Byte-Program time from 10 <math>\mu</math>s to 15 <math>\mu</math>s</li> <li>Updated chip program times</li> <li>Separated Supervoltage Current for <math>A_9</math> and <math>OE\#</math> in Table 5 on page 6</li> </ul> | May 2004 |
| 06     | <ul style="list-style-type: none"> <li>Added non-Pb 32-PDIP MPNs for 1, 2, and 4 Mbit devices</li> <li>Clarified the solder temperature profile under "Absolute Maximum Stress Ratings" on page 5</li> </ul>                                                                                                                                                                                            | Dec 2004 |
| 07     | <ul style="list-style-type: none"> <li>Changed program voltage from 12.6V to 12V globally</li> </ul>                                                                                                                                                                                                                                                                                                    | Aug 2006 |
| 08     | <ul style="list-style-type: none"> <li>EOLed all valid combinations of SST37VF512, See S71151(03).</li> <li>Removed 64K x 8 organization and leaded parts</li> </ul>                                                                                                                                                                                                                                    | Apr 2007 |
| 09     | <ul style="list-style-type: none"> <li>File name correction</li> </ul>                                                                                                                                                                                                                                                                                                                                  | Apr 2008 |
| 10     | <ul style="list-style-type: none"> <li>Fixed mistake in document status by removing "EOL"</li> </ul>                                                                                                                                                                                                                                                                                                    | May 2008 |
| 11     | <ul style="list-style-type: none"> <li>Transferred from SST to Greenliant</li> </ul>                                                                                                                                                                                                                                                                                                                    | May 2010 |

© 2010 Greenliant Systems, Ltd. All rights reserved.

Greenliant, the Greenliant logo and NANDrive are trademarks of Greenliant Systems, Ltd.

All trademarks and registered trademarks are the property of their respective owners.

These specifications are subject to change without notice.

MTP is a trademark and SuperFlash is a registered trademark of Silicon Storage Technology, Inc., a wholly owned subsidiary of Microchip Technology Inc.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Greenliant:

[GLS37VF010-70-3C-NHE](#) [GLS37VF010-70-3C-WHE](#) [GLS37VF020-70-3C-NHE](#) [GLS37VF020-70-3C-WHE](#)  
[GLS37VF040-70-3C-NHE](#) [GLS37VF040-70-3C-PHE](#) [GLS37VF040-70-3C-WHE](#) [SST37VF010-70-3C-WHE](#)  
[SST37VF020-70-3C-NHE](#) [SST37VF040-70-3C-NHE](#) [SST37VF010-70-3C-NHE](#) [SST37VF040-70-3C-WHE](#)  
[SST37VF040-70-3C-PHE](#) [SST37VF020-70-3C-WHE](#) [SST37VF010-90-3C-NH](#) [SST37VF020-90-3C-NH](#) [SST37VF010-](#)  
[90-3C-WH](#) [SST37VF020-70-3C-WH](#) [SST37VF020-90-3C-WH](#) [SST37VF040-90-3C-NH](#) [SST37VF040-70-3C-WH](#)  
[SST37VF020-70-3C-NH](#) [SST37VF040-90-3C-WH](#) [SST37VF010-70-3C-NH](#) [SST37VF010-70-3C-WH](#) [SST37VF040-](#)  
[90-3C-PH](#) [SST37VF010-90-3C-PH](#) [SST37VF040-70-3C-NH](#) [SST37VF020-90-3C-PH](#) [GLS37VF010-70-3C-NHE-T](#)  
[GLS37VF020-70-3C-WHE-T](#) [GLS37VF010-70-3C-WHE-T](#) [GLS37VF020-70-3C-NHE-T](#)