

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [45985-4131](#)
Status: **Active**
Overview: [EXTreme LPHPower™](#)
Description: EXTreme LPH Power™ Header, Right Angle, 4 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, for 3.18mm Thick PC Board

Documents:
[3D Model](#) [Product Specification PS-45984-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [45985](#)
Application Board-to-Board, Power
Overview [EXTreme LPHPower™](#)
Product Name EXTreme LPHPower™
UPC 822350777018

Physical

(p)ower-(s)ignal Configuration 4p - 20s
Breakaway No
Circuits (Loaded) 24
Circuits (maximum) 24
Color - Resin Black
Durability (mating cycles max) 250
First Mate / Last Break Yes
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part No
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 6.174/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 4.50mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 3.18mm
Packaging Type Tray
Pitch - Mating Interface 1.27mm, 12.00mm
Plating min - Mating 0.762µm
Plating min - Termination 3.810µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40°C to +105°C



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[45985Series](#)

Mates With
[45984 EXTreme LPHPower™ PCB Receptacles](#)

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	30A
Voltage - Maximum	250V AC (RMS)/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	20
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-45984-001
Sales Drawing	SD-45985-400

This document was generated on 10/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION