



Home > Products > Stainless Steel Media Isolated > ST > Product Page

### ST0R4BG1SPGF



**ST Series Stainless Steel Pressure Sensor with Silicon Diaphragm, Amplified Output, Gage, 0 bar to 0.4 bar**

*Actual product appearance may vary.*

#### Features

High value and outstanding performance  
Wide choice of pressure ranges available  
Amplified outputs  
Reverse polarity protection  
Less than 500 microseconds response time  
Industrial housing  
Exceeds CE Heavy Industrial EMC  
Excellent OEM value  
Eliminates cost of external amplifiers  
Not damaged by reversed excitation  
Accurate high speed measurements  
Protected from harsh environments

#### Potential Applications

Pneumatic equipment  
Air compressors  
Air filtration monitoring  
Industrial controls

#### Description

The model ST pressure transducer combines Honeywell's proven silicon pressure sensing with the latest in ASIC technology in a rugged, industrial package. High value, coupled with outstanding performance, make this an ideal transducer for industrial control applications such as air compressors and pneumatic equipment. Temperature compensated, calibrated, and amplified, the ST has pressure ranges from 0 psi to 1.0 psi to 0 psi to 259 psi. The ST offers three standard output options for user flexibility, which are as follows: a 0.50 Vdc to 4.50 Vdc ratiometric output from 5.0 Vdc excitation, a 0.50 Vdc to 4.50 Vdc regulated output from 7.0 Vdc to 35.0 Vdc excitation, or a 4 mA to 20 mA output from 9.5 Vdc to 35.0 Vdc. The ST transducer delivers 1.0 % full scale accuracy (BFSL) over a wide temperature range of -40 °C to 100 °C and utilizes a proven industry standard connector for high reliability.

#### Supporting Documentation

[Dimensions and Circuity](#) [Documentation](#)

Product Specifications	
Measurement Type	Gage
Signal Conditioning	Amplified
Pressure Range	0 bar to 0.4 bar
Supply Voltage	9.5 Vdc to 35.0 Vdc
Maximum Overpressure	1.2 bar
Burst Pressure	2 bar
Port Style	1/8-27 NPT
Temperature Compensation	Yes
Output Type	4 mA to 20 mA
Protection Circuitry	Reverse Polarity
Accuracy	0.25% full scale BFSL
Response Time	less than 500 µs
Output Impedance	25 ohms max.
Output Calibration	Yes
Termination Type	Packard Metri-Pack™ Connector
Weight	57 grams [2.0 ounces]
Full Scale Span	16 mA
Compensated Temperature Range	-40 °C to 100 °C [-40 °F to 212 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Limited only to those media which will not attack a 300 Series stainless, internal seal, silicon, polyetherimide
Approvals	CE
UNSPSC Code	4111121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	ST

#### My Links

[Login to iCOM](#)  
[Login as Rep/AD](#)  
[Login as Guest](#)  
[Login to Digital University](#)

#### Keyword Search

Search for product and support information.

All Sensing and Control

#### Product Search

Part number search:

Use (\*) to expand search

#### Specification Search

#### ▼ Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- RoHS Product List
- Customer Feedback