

SAFETY DATA SHEET

SCC3 CONFORMAL COATING

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND THE COMPANY:

PRODUCT NAME: SCC3 CONFORMAL COATING

PART No.: EDCA200H

SUPPLIER: ELECTROLUBE. A division of HK WENTWORTH LTD
KINGSBURY PARK, MIDLAND ROAD
MIDLAND ROAD, SWADLINCOTE
DERBYSHIRE. DE11 0AN
Tel: +44 (0) 1283 222111
Fax: +44 (0) 1283 550177

2. COMPOSITION/INFORMATION ON INGREDIENTS:

NAME		CLASSIFICATION	CONTENT
CAS No.:	EINECS Nr.:		
CYCLOHEXANE 110-82-7	203-806-2	Xn ,F ,N R-11, 38, 50/53, 65, 67	10-30 %
1-METHOXY-2-PROPANOL 107-98-2	203-539-1	- R-10	5-10 %
HEXANE MIXTURE OF ISOMERS (MAX 5% n-HEXANE (203-777-6))		Xn ,F ,N R-11, 38, 51/53, 65, 67	1-5 %
n-HEPTANE 142-82-5	205-562-2	Xn ,F ,N R-11, 38, 50/53, 65, 67	1-5 %
n-HEXANE 110-54-3	203-777-6	Xn ,F ,N R-11, 38, 48/20, 51/53, 62, 65, 67 Rep3	0-1 %
XYLENE 1330-20-7	215-535-7	Xn R-10, 20/21, 38	10-30 %
2-BUTOXYETHANOL 111-76-2	203-905-0	Xn R-20/21/22, 36/38	1-5 %
DIMETHYL ETHER 115-10-6	204-065-8	Fx R-12	30-60 %

The Full Text for all R-Phrases are Displayed in Section 16

3. HAZARDS IDENTIFICATION:

Extremely flammable. Harmful by inhalation and in contact with skin. Irritating to skin. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

4. FIRST AID MEASURES:

INHALATION: Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION:	Rinse mouth thoroughly. Provide rest, warmth and fresh air.
SKIN:	Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.
EYES:	Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5. FIRE FIGHTING MEASURES:

EXTINGUISHING MEDIA:	Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.
SPECIAL FIRE FIGHTING PROCEDURES:	Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.
UNUSUAL FIRE & EXPLOSION HAZARDS:	Aerosol cans may explode in fires.

6. ACCIDENTAL RELEASE MEASURES:

SPILL CLEANUP METHODS:	Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers.
-------------------------------	---

7. HANDLING AND STORAGE:

USAGE PRECAUTIONS:	Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact.
STORAGE PRECAUTIONS:	Aerosol cans: Must not be exposed for direct sunlight or temperatures above 50°C.

8. EXPOSURE CONTROLS AND PERSONAL PROTECTION:

INGREDIENT NAME:	CAS No.:	STD	LT EXP 8 Hrs	ST EXP 15 Min
1-METHOXY-2-PROPANOL	107-98-2	OES	100 ppm(Sk)	150 ppm(Sk)
CYCLOHEXANE	110-82-7	OES	100 ppm	300 ppm
n-HEPTANE	142-82-5	OES	500 ppm	
n-HEXANE	110-54-3	OES	20 ppm	No std.
XYLENE	1330-20-7	OES	50 ppm(Sk)	100 ppm(Sk)
2-BUTOXYETHANOL	111-76-2	OES	25 ppm(Sk)	50 ppm(Sk)

INGREDIENT COMMENTS: OES = Occupational Exposure Standard. MEL = Maximum Exposure Limit.

PROTECTIVE EQUIPMENT:



VENTILATION: All handling to take place in well ventilated area.

RESPIRATORS: No specific recommendation made, but respiratory protection must be used if the general level exceeds the Occupational Exposure Level (OEL).

PROTECTIVE GLOVES: Use protective gloves.

EYE PROTECTION: Use eye protection.

OTHER PROTECTION: Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENIC WORK PRACTICES: DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. No eating or drinking while working with this

material.

9. PHYSICAL AND CHEMICAL PROPERTIES:

APPEARANCE:	Aerosol. Liquid.		
COLOUR:	Colourless.		
ODOUR/TASTE:	Solvent.		
BOILING POINT (°C, interval):	137 - 143	Pressure:	
MELT./FREEZ. POINT (°C, interval):	-24		
DENSITY/SPECIFIC GRAVITY (g/ml):	0.780	Temperature (°C):	
VOLATILITY DESCRIPTION:	Volatile.		
SOLUBILITY DESCRIPTION:	Insoluble in water.		
FLASH POINT (°C):	25	Method:	OC (Open cup).
AUTO IGNITION TEMP. (°C):	480		
FLAMMABILITY LIMIT - LOWER(%):	1.1		
FLAMMABILITY LIMIT - UPPER(%):	7		

10. STABILITY AND REACTIVITY:

STABILITY:	Normally stable.
CONDITIONS TO AVOID:	Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.
HAZARDOUS DECOMP. PRODUCTS:	Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

11. TOXICOLOGICAL INFORMATION:

INHALATION:	Harmful by inhalation. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting. Solvent vapours are hazardous and may cause nausea, sickness and headaches. Prolonged inhalation of high concentrations may damage respiratory system.
SKIN:	Harmful in contact with skin. Irritating to skin. May cause allergic contact eczema. Product has a defatting effect on skin. Prolonged or repeated contact leads to drying of skin.
EYES:	Irritating to eyes.
OTHER HEALTH EFFECTS:	This substance has no evidence of carcinogenic properties.
ROUTE OF ENTRY:	Inhalation.

12. ECOLOGICAL INFORMATION:

ECOLOGICAL INFORMATION:	Dangerous for the environment if discharged into watercourses.
-------------------------	--

13. DISPOSAL CONSIDERATIONS:

DISPOSAL METHODS: Empty containers must not be burned because of explosion hazard. Dispose of in accordance with Local Authority requirements.

14. TRANSPORT INFORMATION:

LABEL FOR CONVEYANCE:



UN No. ROAD:	1950
UK ROAD TRANSPORT CLASS:	2.1
UK ROAD PACK GR.:	Not Applicable
ADR CLASS No.:	2.1
ADR CLASS:	Division 2.1: Flammable gases.
ADR ITEM No.:	Not Applicable
ADR MARGINAL:	2201
ADR LABEL No.:	2.1
CEFIC TEC(R) No.:	20G5F
PROPER SHIPPING NAME I:	AEROSOLS
RID CLASS No.:	2.1
RID ITEM No.:	Not Applicable
UN No. SEA:	1950
IMDG CLASS:	2.1
IMDG PACK GR.:	Not Applicable
EmS No.:	F-D; S-U
MFAG TABLE No.:	See Guide
MARINE POLLUTANT:	No.
UN No., AIR:	1950
ICAO CLASS:	2.1
AIR PACK GR.:	Not Applicable

15. REGULATORY INFORMATION:

LABEL FOR SUPPLY:



RISK PHRASES: R-12 Extremely flammable.

R-20/21 Harmful by inhalation and in contact with skin.
R-38 Irritating to skin.
R-51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

SAFETY PHRASES:

S-16 Keep away from sources of ignition - No Smoking.
S-23A Do not breathe gas/fumes/vapour/spray.
S-24 Avoid contact with skin.
S-36/37 Wear suitable protective clothing and gloves.
S-51 Use only in well ventilated areas.

UK REGULATORY REFERENCES:

Petroleum (Consolidation) Act, as amended 1984 SI 1244. Highly Flammable Liquid Regulations 1972.

ENVIRONMENTAL LISTING:

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980.

EU DIRECTIVES:

System of specific information relating to Dangerous Preparations. 91/155.

APPROVED CODE OF PRACTICE:

Classification and Labelling of Substances and Preparations Dangerous for Supply.

GUIDANCE NOTES:

Occupational Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37. CHIP for everyone HSG(108).

16. OTHER INFORMATION:

USER NOTES: CN No 32089091

REVISION COMMENTS: Revised in accordance with CHIP3 and EU Directive 1999/45/EC

ISSUED BY: Helen O'Reilly

REVISION DATE: MAY 2003

REV. No./REPL. SDS GENERATED: 0

SDS No.: 10666

DISCLAIMER: This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process unless specified in the text. The information contained in this safety data sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as guidance for the safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification.

R-PHRASES (Full Text):

R-10 Flammable. R-11 Highly flammable. R-38 Irritating to skin. R-50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R-65 Harmful: may cause lung damage if swallowed. R-67 Vapours may cause drowsiness and dizziness. R-51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R-48/20 Harmful: danger of serious damage to health by prolonged exposure through inhalation. R-62 Possible risk of impaired fertility. R-20/21 Harmful by inhalation and in contact with skin. R-20/21/22 Harmful by inhalation, in contact with skin and if swallowed. R-36/38 Irritating to eyes and skin. R-12 Extremely flammable.