

Ultra-low ESR HC49/US (AT49)SMD MICROPROCESSOR CRYSTAL

ABLS-LR



RoHS
Compliant



11.5 x 4.8 x 4.2 mm

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- Ultra low ESR as low as 20 ohms for 4MHz, 85% lower than typical SMD Low Profile HC49S Crystals
- Low negative resistance(-R) IC design can ensure high oscillation margin
- Tight stability and automotive grade temperature available
- Hermetically resistance weld sealed

APPLICATIONS:

- Low negative resistance u-controller design for low frequency
- Wide range of automotive applications
- Industrial applications


STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	3		36	MHz	
Operation Mode	Fundamental				
Operating Temperature	0		+70	°C	See options
Storage Temperature	-55		+125	°C	
Frequency Tolerance @+25°C	-50		+50	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)	3.0~3.579545MHz	-100	+100	ppm	Standard only
	3.579545~36MHz	-50	+50		See options
Equivalent series resistance (R1)	See table 1 below			Ω	
Shunt capacitance (C0)			7	pF	
Load capacitance (CL)	18			pF	See options
Drive Level		100	1000	μW	
Aging	-5		+5	ppm	@25°C±3°C First year
Insulation Resistance	500			MΩ	@ 100Vdc ± 15V
Spurious Response			-3	dB	
Drive level dependency (DLD)	Minimum 7 points tested: from 1μW to 500μW. Change in frequency (Maximum - Minimum) over DLD range < ±10ppm Change in ESR (Maximum - Minimum) over DLD range < 25% of Max ESR value. Maximum ESR over DLD range < Max ESR value.				

TABLE 1: ESR


FREQUENCY (MHz)	ESR (Ω) Max.
3.000000	100
3.072000	100
3.276800	75
3.500000 ~ 4.000000MHz	40
4.000001 ~ 4.500000MHz	30
4.500001 ~ 5.999999MHz	25
6.000000 ~ 7.499999MHz	20
7.500000 ~ 12.999999MHz	15
13.000000 ~ 36.000000MHz	10

OPTIONS & PART IDENTIFICATION: (Left blank if standard)







OUTLINE DRAWING:



TAPE & REEL: T = tape and reel (1000pcs/reel)

REFLOW PROFILE:



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ABLS-LR-24.000MHZ-B-1-G-T](#) [ABLS-LR-3.000MHZ-T](#) [ABLS-LR-3.072MHZ-T](#) [ABLS-LR-3.2768MHZ-T](#) [ABLS-LR-3.579545MHZ-T](#) [ABLS-LR-3.6864MHZ-T](#) [ABLS-LR-4.000MHZ-T](#) [ABLS-LR-4.194304MHZ-T](#) [ABLS-LR-4.433619MHZ-T](#) [ABLS-LR-4.500MHZ-T](#) [ABLS-LR-4.9152MHZ-T](#) [ABLS-LR-5.000MHZ-T](#) [ABLS-LR-6.000MHZ-T](#) [ABLS-LR-6.144MHZ-T](#) [ABLS-LR-6.7458MHZ-T](#) [ABLS-LR-7.3728MHZ-T](#) [ABLS-LR-8.000MHZ-T](#) [ABLS-LR-9.216MHZ-T](#) [ABLS-LR-9.8304MHZ-T](#) [ABLS-LR-10.000MHZ-T](#) [ABLS-LR-10.240MHZ-T](#) [ABLS-LR-11.0592MHZ-T](#) [ABLS-LR-12.000MHZ-T](#) [ABLS-LR-12.288MHZ-T](#) [ABLS-LR-13.000MHZ-T](#) [ABLS-LR-13.500MHZ-T](#) [ABLS-LR-14.31818MHZ-T](#) [ABLS-LR-14.7456MHZ-T](#) [ABLS-LR-15.000MHZ-T](#) [ABLS-LR-15.360MHZ-T](#) [ABLS-LR-16.000MHZ-T](#) [ABLS-LR-16.384MHZ-T](#) [ABLS-LR-16.9344MHZ-T](#) [ABLS-LR-18.000MHZ-T](#) [ABLS-LR-18.432MHZ-T](#) [ABLS-LR-19.6608MHZ-T](#) [ABLS-LR-20.000MHZ-T](#) [ABLS-LR-24.000MHZ-T](#) [ABLS-LR-24.576MHZ-F-T](#) [ABLS-LR-25.000MHZ-F-T](#) [ABLS-LR-27.000MHZ-F-T](#) [ABLS-LR-28.63636MHZ-T](#) [ABLS-LR-30.000MHZ-T](#)